

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931250

Luminaire Tested: DFN2DS-TR2F0-030DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-030DS840-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2552.5 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 27.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931250

CATALOG NUMBER: DFN2DS-TR2F0-030DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931250

CATALOG NUMBER: DFN2DS-TR2F0-030DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2768	2768	2768
5°	2779	2734	2749
10°	2757	2689	2666
15°	2726	2609	2534
20°	2682	2495	2370
25°	2637	2366	2211
30°	2575	2233	2008
35°	2514	2089	1829
40°	2453	1939	1622
45°	2381	1772	1435
50°	2308	1602	1251
55°	2232	1419	1075
60°	2144	1228	892
65°	2045	1031	812
70°	1926	849	747
75°	1780	775	697
80°	1572	692	635
85°	1234	545	545

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2381 cd/sqm

TEST NUMBER: P931250

CATALOG NUMBER: DFN2DS-TR2F0-030DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	4.6
10°-20°	319.3	12.5
20°-30°	448.3	17.6
30°-40°	488.7	19.1
40°-50°	449.2	17.6
50°-60°	352.7	13.8
60°-70°	229.6	9.0
70°-80°	118.2	4.6
80°-90°	30.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	884.0	34.6
0°-40°	1372.7	53.8
0°-60°	2174.6	85.2
0°-90°	2552.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2552.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1241	1241	1241	1241	1241	
5°	1241	1236	1221	1231	1228	118
15°	1180	1168	1130	1109	1097	333
25°	1072	1036	962	915	898	493
35°	923	866	767	696	672	578
45°	755	680	562	482	455	583
55°	574	486	365	298	276	513
65°	388	296	195	157	154	384
75°	207	128	90	82	81	219
85°	48	25	21	21	21	58
90°	0	0	0	0	0	

TEST NUMBER: P931250

CATALOG NUMBER: DFN2DS-TR2F0-030DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1241.1	1241.1	1241.1	1241.1	1241.1
2.5°	1246.7	1241.1	1228.7	1240.0	1237.8
5°	1241.1	1235.5	1220.9	1231.0	1227.6
7.5°	1231.0	1224.3	1208.6	1213.0	1207.4
10°	1217.5	1209.7	1187.3	1183.8	1177.2
12.5°	1200.7	1190.6	1160.3	1153.6	1141.1
15°	1180.5	1168.1	1129.9	1108.6	1097.4
17.5°	1156.9	1138.9	1091.7	1067.1	1049.0
20°	1129.9	1107.4	1051.3	1023.3	998.5
22.5°	1100.8	1074.9	1009.7	971.6	954.8
25°	1071.6	1035.5	961.5	915.4	898.5
27.5°	1036.7	998.5	916.5	863.8	837.8
30°	999.7	957.0	867.1	809.9	779.5
32.5°	963.7	912.0	820.0	752.6	724.4
35°	923.3	866.0	767.2	696.4	671.7
37.5°	884.0	822.1	717.7	640.1	612.2
40°	842.4	775.1	666.1	586.3	557.2
42.5°	799.7	727.9	614.4	531.2	503.2
45°	754.9	679.5	561.7	481.8	454.9
47.5°	712.1	632.4	511.1	431.2	406.6
50°	665.0	585.2	461.7	384.1	360.6
52.5°	618.8	534.6	414.5	340.3	319.0
55°	573.9	486.3	365.0	297.7	276.4
57.5°	527.9	438.0	321.3	258.4	240.3
60°	480.7	390.9	275.2	217.9	200.0
62.5°	434.7	344.8	235.8	182.0	173.1
65°	387.5	296.5	195.4	157.3	153.9
67.5°	342.6	251.6	157.3	138.1	134.7
70°	295.4	207.8	130.2	119.0	114.5
72.5°	250.5	167.3	108.9	100.0	97.7
75°	206.6	128.0	89.9	82.0	80.9
77.5°	162.9	90.9	70.8	66.3	64.0
80°	122.4	65.2	53.9	49.4	49.4
82.5°	85.3	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931250

CATALOG NUMBER: DFN2DS-TR2F0-030DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.77	16.29	15.14	16.61	16.92	10.73	12.26	11.10	12.57	12.88
	3H	16.54	17.90	16.92	18.23	18.59	12.00	13.36	12.38	13.69	14.05
	4H	17.20	18.48	17.60	18.83	19.21	12.50	13.78	12.90	14.13	14.51
	6H	17.69	18.88	18.10	19.24	19.63	12.88	14.06	13.29	14.43	14.82
	8H	17.86	18.98	18.28	19.37	19.78	13.00	14.13	13.43	14.52	14.92
	12H	17.96	19.04	18.39	19.42	19.85	13.09	14.16	13.52	14.55	14.98
4H	2H	14.88	16.16	15.28	16.50	16.88	11.43	12.71	11.83	13.06	13.44
	3H	16.81	17.87	17.22	18.27	18.67	12.87	13.93	13.28	14.33	14.73
	4H	17.56	18.52	17.99	18.93	19.37	13.47	14.43	13.90	14.84	15.28
	6H	18.15	18.98	18.61	19.43	19.88	13.96	14.79	14.42	15.23	15.69
	8H	18.36	19.14	18.83	19.59	20.05	14.12	14.90	14.58	15.34	15.81
	12H	18.52	19.21	19.00	19.69	20.16	14.24	14.93	14.72	15.41	15.88
8H	4H	17.58	18.36	18.05	18.80	19.27	13.82	14.60	14.29	15.05	15.51
	6H	18.22	18.86	18.72	19.35	19.83	14.41	15.05	14.91	15.54	16.02
	8H	18.47	19.05	18.98	19.56	20.05	14.63	15.21	15.15	15.72	16.21
	12H	18.67	19.18	19.18	19.68	20.24	14.81	15.32	15.32	15.81	16.38
12H	4H	17.57	18.26	18.05	18.74	19.21	13.87	14.56	14.35	15.04	15.51
	6H	18.20	18.78	18.72	19.29	19.78	14.47	15.05	14.99	15.56	16.05
	8H	18.49	19.00	19.00	19.49	20.05	14.75	15.26	15.26	15.75	16.31