

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931272

Luminaire Tested: DFN2DS-TR2F0-040DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-040DS927-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2692.8 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931272

CATALOG NUMBER: DFN2DS-TR2F0-040DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931272

CATALOG NUMBER: DFN2DS-TR2F0-040DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2920	2920	2920
5°	2931	2884	2900
10°	2909	2837	2813
15°	2876	2752	2673
20°	2829	2632	2500
25°	2782	2496	2333
30°	2716	2356	2118
35°	2652	2204	1929
40°	2588	2046	1711
45°	2512	1869	1514
50°	2434	1690	1320
55°	2355	1498	1134
60°	2262	1295	941
65°	2158	1088	857
70°	2033	896	788
75°	1879	817	736
80°	1658	730	670
85°	1303	576	576

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2512 cd/sqm

TEST NUMBER: P931272

CATALOG NUMBER: DFN2DS-TR2F0-040DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	4.6
10°-20°	336.9	12.5
20°-30°	473.0	17.6
30°-40°	515.5	19.1
40°-50°	473.8	17.6
50°-60°	372.1	13.8
60°-70°	242.2	9.0
70°-80°	124.7	4.6
80°-90°	31.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.5	34.6
0°-40°	1448.1	53.8
0°-60°	2294.1	85.2
0°-90°	2692.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2692.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1309	1303	1288	1299	1295	124
15°	1245	1232	1192	1170	1158	351
25°	1130	1092	1014	966	948	520
35°	974	914	809	735	708	610
45°	796	717	592	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	61
90°	0	0	0	0	0	

TEST NUMBER: P931272

CATALOG NUMBER: DFN2DS-TR2F0-040DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.3	1309.3	1309.3	1309.3	1309.3
2.5°	1315.3	1309.3	1296.3	1308.2	1305.8
5°	1309.3	1303.4	1288.0	1298.6	1295.2
7.5°	1298.6	1291.6	1275.0	1279.6	1273.8
10°	1284.5	1276.1	1252.5	1248.8	1241.9
12.5°	1266.7	1256.0	1224.0	1216.9	1203.8
15°	1245.3	1232.3	1192.0	1169.5	1157.7
17.5°	1220.5	1201.5	1151.6	1125.7	1106.7
20°	1192.0	1168.3	1109.0	1079.5	1053.4
22.5°	1161.2	1134.0	1065.2	1024.9	1007.3
25°	1130.4	1092.5	1014.2	965.8	947.9
27.5°	1093.8	1053.4	966.9	911.2	883.9
30°	1054.6	1009.5	914.7	854.3	822.3
32.5°	1016.7	962.1	865.0	793.9	764.2
35°	974.1	913.6	809.3	734.7	708.5
37.5°	932.6	867.3	757.2	675.3	645.8
40°	888.7	817.7	702.7	618.6	587.7
42.5°	843.6	767.8	648.2	560.4	530.9
45°	796.3	716.8	592.5	508.3	479.9
47.5°	751.3	667.2	539.2	455.0	428.9
50°	701.5	617.4	487.0	405.2	380.4
52.5°	652.8	564.0	437.3	359.0	336.5
55°	605.5	513.1	385.1	314.0	291.5
57.5°	556.9	462.1	338.9	272.5	253.6
60°	507.1	412.3	290.3	229.9	211.0
62.5°	458.6	363.8	248.8	192.0	182.6
65°	408.8	312.8	206.2	165.9	162.3
67.5°	361.5	265.4	165.9	145.7	142.2
70°	311.7	219.2	137.4	125.6	120.8
72.5°	264.3	176.5	114.9	105.5	103.1
75°	218.0	135.0	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.7	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931272

CATALOG NUMBER: DFN2DS-TR2F0-040DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.96	16.48	15.32	16.79	17.11	10.92	12.44	11.28	12.75	13.07
	3H	16.72	18.09	17.10	18.42	18.78	12.18	13.55	12.56	13.88	14.24
	4H	17.39	18.67	17.79	19.02	19.40	12.69	13.97	13.09	14.31	14.69
	6H	17.88	19.06	18.29	19.43	19.82	13.07	14.25	13.48	14.62	15.01
	8H	18.04	19.17	18.47	19.56	19.96	13.19	14.32	13.62	14.71	15.11
	12H	18.15	19.23	18.58	19.61	20.04	13.27	14.35	13.70	14.73	15.16
4H	2H	15.06	16.34	15.46	16.69	17.07	11.61	12.89	12.01	13.24	13.62
	3H	17.00	18.06	17.41	18.46	18.86	13.06	14.12	13.47	14.52	14.92
	4H	17.74	18.70	18.18	19.12	19.56	13.66	14.61	14.09	15.03	15.47
	6H	18.34	19.17	18.79	19.61	20.07	14.15	14.98	14.60	15.42	15.88
	8H	18.55	19.33	19.01	19.77	20.24	14.31	15.08	14.77	15.53	16.00
	12H	18.70	19.40	19.19	19.88	20.35	14.42	15.12	14.91	15.60	16.07
8H	4H	17.77	18.55	18.23	18.99	19.46	14.01	14.79	14.47	15.23	15.70
	6H	18.41	19.05	18.90	19.54	20.02	14.60	15.24	15.09	15.73	16.21
	8H	18.66	19.23	19.17	19.74	20.23	14.82	15.40	15.33	15.90	16.39
	12H	18.86	19.37	19.37	19.86	20.43	15.00	15.51	15.51	16.00	16.56
12H	4H	17.75	18.45	18.24	18.93	19.40	14.05	14.75	14.54	15.23	15.70
	6H	18.39	18.96	18.90	19.47	19.96	14.66	15.24	15.17	15.75	16.24
	8H	18.67	19.18	19.18	19.67	20.24	14.93	15.44	15.44	15.94	16.50

END OF REPORT