

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334345

Luminaire Tested: **S125DS-S375D840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P334345  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DS-S375D840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER  
PENDANT/SURFACE/WALL MOUNT, 375 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1450.6 lumens  
Efficiency: N/A  
Efficacy: 125.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334345

CATALOG NUMBER: S125DS-S375D840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P334345

CATALOG NUMBER: S125DS-S375D840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3599	3599	3599
5°	3608	3573	3596
10°	3586	3548	3568
15°	3546	3506	3520
20°	3491	3445	3452
25°	3431	3375	3371
30°	3357	3298	3281
35°	3278	3216	3170
40°	3197	3126	3081
45°	3109	3044	2984
50°	3012	2946	2857
55°	2920	2835	2755
60°	2808	2723	2626
65°	2674	2587	2500
70°	2547	2432	2347
75°	2321	2243	2168
80°	2068	2034	1986
85°	1801	1830	1734



TEST NUMBER: P334345

CATALOG NUMBER: S125DS-S375D840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.6	3.6
10°-20°	148.6	10.2
20°-30°	219.3	15.1
30°-40°	255.9	17.6
40°-50°	257.0	17.7
50°-60°	225.6	15.6
60°-70°	168.0	11.6
70°-80°	96.0	6.6
80°-90°	27.7	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.5	29.0
0°-40°	676.3	46.6
0°-60°	1158.9	79.9
0°-90°	1450.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	556	551	555	555	53
15°	530	529	524	526	526	150
25°	482	479	474	474	473	222
35°	416	414	408	406	402	260
45°	340	339	333	328	327	262
55°	259	258	252	248	245	231
65°	175	174	169	165	164	174
75°	93	92	90	89	87	99
85°	24	25	25	24	23	28
90°	0	0	0	0	0	



TEST NUMBER: P334345

CATALOG NUMBER: S125DS-S375D840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	557.3	557.3	557.3	557.3	557.3
2.5°	559.1	557.8	553.4	557.8	557.3
5°	556.5	555.6	551.2	555.1	554.7
7.5°	552.5	551.6	546.8	550.7	550.3
10°	546.8	545.9	541.0	544.5	544.1
12.5°	539.7	537.9	533.5	536.2	536.2
15°	530.4	529.1	524.3	526.5	526.5
17.5°	520.7	518.5	513.7	516.3	514.1
20°	508.0	507.1	501.3	504.4	502.2
22.5°	495.2	493.4	488.1	489.9	488.6
25°	481.5	479.3	473.6	474.4	473.1
27.5°	465.6	464.3	458.6	459.0	457.7
30°	450.2	448.9	442.3	441.4	440.0
32.5°	433.4	431.2	425.5	423.7	421.1
35°	415.8	414.0	407.9	405.7	402.1
37.5°	397.7	395.5	389.8	386.7	384.5
40°	379.2	377.0	370.8	366.9	365.5
42.5°	359.4	357.6	351.4	347.9	345.7
45°	340.4	338.6	333.3	328.1	326.7
47.5°	319.7	320.1	313.5	308.2	305.1
50°	299.8	298.5	293.2	287.5	284.4
52.5°	279.6	278.7	272.9	268.1	264.6
55°	259.3	257.9	251.8	247.8	244.7
57.5°	237.7	237.2	231.9	226.6	225.3
60°	217.4	215.6	210.8	206.4	203.3
62.5°	196.2	194.9	190.9	186.1	183.9
65°	175.0	174.2	169.3	165.3	163.6
67.5°	154.3	152.6	149.0	145.5	144.6
70°	134.9	132.7	128.8	126.1	124.3
72.5°	113.8	112.4	110.2	107.1	105.4
75°	93.0	92.2	89.9	88.6	86.9
77.5°	73.6	73.2	71.9	71.0	69.7
80°	55.6	55.6	54.7	54.2	53.4
82.5°	39.7	38.8	38.8	37.9	37.9
85°	24.3	24.7	24.7	24.3	23.4
87.5°	11.9	11.9	11.5	11.5	10.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)