

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931273

Luminaire Tested: DFN2DS-TR2F0-040DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-040DS930-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3227.4 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931273

CATALOG NUMBER: DFN2DS-TR2F0-040DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931273

CATALOG NUMBER: DFN2DS-TR2F0-040DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2829	2829	2829
5°	2840	2799	2816
10°	2823	2771	2785
15°	2788	2735	2732
20°	2739	2681	2678
25°	2689	2615	2615
30°	2626	2554	2532
35°	2567	2481	2444
40°	2493	2408	2362
45°	2420	2335	2278
50°	2340	2260	2179
55°	2258	2173	2092
60°	2165	2068	1992
65°	2067	1963	1874
70°	1941	1837	1750
75°	1766	1692	1650
80°	1567	1520	1441
85°	1280	1218	1093

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2420 cd/sqm

TEST NUMBER: P931273

CATALOG NUMBER: DFN2DS-TR2F0-040DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	3.7
10°-20°	335.9	10.4
20°-30°	493.7	15.3
30°-40°	573.4	17.8
40°-50°	572.7	17.7
50°-60°	499.3	15.5
60°-70°	369.1	11.4
70°-80°	208.8	6.5
80°-90°	55.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	949.0	29.4
0°-40°	1522.3	47.2
0°-60°	2594.3	80.4
0°-90°	3227.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3227.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1268	1268	1268	1268	1268	
5°	1268	1264	1250	1260	1258	120
15°	1208	1200	1184	1189	1183	340
25°	1093	1083	1062	1065	1062	503
35°	943	931	911	904	898	589
45°	767	759	740	727	722	592
55°	581	573	559	544	538	519
65°	392	384	372	361	355	387
75°	205	202	196	189	192	219
85°	50	49	48	44	43	59
90°	0	0	0	0	0	

TEST NUMBER: P931273

CATALOG NUMBER: DFN2DS-TR2F0-040DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.5	1268.5	1268.5	1268.5	1268.5
2.5°	1275.9	1269.8	1256.3	1268.5	1266.2
5°	1268.5	1263.7	1250.2	1259.9	1257.6
7.5°	1259.9	1252.7	1239.2	1249.1	1246.6
10°	1246.6	1238.1	1223.5	1233.2	1229.5
12.5°	1228.2	1221.0	1206.4	1212.5	1209.9
15°	1207.5	1200.3	1184.4	1189.2	1183.2
17.5°	1181.9	1174.7	1158.8	1164.8	1158.8
20°	1153.8	1146.5	1129.5	1133.1	1128.4
22.5°	1125.8	1114.8	1098.9	1098.9	1096.5
25°	1092.8	1083.1	1062.4	1064.8	1062.4
27.5°	1056.2	1047.7	1032.0	1028.3	1022.3
30°	1019.7	1009.9	991.7	988.0	983.1
32.5°	980.7	973.4	953.9	946.5	941.6
35°	942.9	930.7	911.2	903.8	897.7
37.5°	900.2	889.2	869.6	861.1	855.0
40°	856.3	846.5	826.9	816.1	811.2
42.5°	813.6	803.8	784.4	772.0	764.8
45°	767.2	758.8	740.3	727.1	722.1
47.5°	722.1	713.5	694.1	680.6	673.4
50°	674.5	668.4	651.3	634.2	628.1
52.5°	628.1	619.6	603.8	590.4	581.8
55°	580.7	573.3	558.7	544.0	538.0
57.5°	533.0	527.0	511.0	496.4	491.5
60°	485.4	480.6	463.6	450.1	446.5
62.5°	439.1	430.6	418.4	406.2	401.3
65°	391.6	384.2	372.0	361.0	355.0
67.5°	342.8	336.6	325.8	317.2	312.3
70°	297.6	292.7	281.7	273.2	268.4
72.5°	251.3	246.4	240.3	231.8	228.1
75°	204.9	202.5	196.3	189.1	191.5
77.5°	163.4	158.5	156.1	152.4	148.8
80°	122.0	120.7	118.3	114.7	112.2
82.5°	83.0	83.0	81.8	76.9	76.9
85°	50.0	48.8	47.6	43.8	42.7
87.5°	22.0	19.6	17.1	13.4	12.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931273

CATALOG NUMBER: DFN2DS-TR2F0-040DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.90	16.51	15.26	16.82	17.14	14.45	16.06	14.82	16.38	16.69
	3H	16.65	18.10	17.02	18.43	18.79	16.15	17.61	16.53	17.94	18.30
	4H	17.29	18.66	17.69	19.01	19.39	16.80	18.17	17.20	18.51	18.89
	6H	17.76	19.03	18.17	19.39	19.79	17.26	18.53	17.67	18.89	19.28
	8H	17.90	19.12	18.33	19.50	19.90	17.40	18.61	17.83	19.00	19.40
	12H	17.99	19.15	18.42	19.54	19.97	17.48	18.64	17.91	19.02	19.45
4H	2H	15.46	16.83	15.85	17.17	17.55	15.10	16.47	15.50	16.82	17.20
	3H	17.43	18.58	17.84	18.98	19.38	17.02	18.17	17.43	18.57	18.97
	4H	18.21	19.24	18.64	19.66	20.09	17.78	18.82	18.22	19.23	19.67
	6H	18.80	19.71	19.26	20.15	20.61	18.37	19.28	18.83	19.72	20.17
	8H	18.99	19.84	19.45	20.28	20.75	18.56	19.40	19.02	19.84	20.31
	12H	19.13	19.89	19.61	20.36	20.83	18.67	19.43	19.15	19.91	20.38
8H	4H	18.48	19.33	18.94	19.77	20.24	18.11	18.95	18.57	19.40	19.86
	6H	19.20	19.90	19.69	20.39	20.86	18.81	19.52	19.31	20.01	20.48
	8H	19.45	20.09	19.96	20.59	21.08	19.06	19.69	19.57	20.20	20.69
	12H	19.65	20.21	20.16	20.70	21.26	19.24	19.80	19.75	20.29	20.85
12H	4H	18.51	19.27	18.99	19.74	20.21	18.14	18.90	18.62	19.38	19.85
	6H	19.24	19.87	19.75	20.38	20.87	18.87	19.50	19.38	20.01	20.50
	8H	19.55	20.11	20.06	20.60	21.16	19.18	19.73	19.68	20.23	20.79