

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931309

Luminaire Tested: DFN2DS-TR2F0-060DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-060DS930-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4841.1 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931309

CATALOG NUMBER: DFN2DS-TR2F0-060DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931309

CATALOG NUMBER: DFN2DS-TR2F0-060DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4244	4244	4244
5°	4260	4199	4224
10°	4235	4156	4177
15°	4182	4102	4098
20°	4108	4021	4017
25°	4034	3922	3922
30°	3940	3831	3798
35°	3851	3722	3666
40°	3740	3612	3543
45°	3630	3503	3416
50°	3511	3390	3269
55°	3387	3259	3138
60°	3248	3102	2987
65°	3100	2945	2810
70°	2912	2756	2625
75°	2648	2538	2476
80°	2351	2279	2162
85°	1917	1827	1640

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3630 cd/sqm

TEST NUMBER: P931309

CATALOG NUMBER: DFN2DS-TR2F0-060DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	3.7
10°-20°	503.9	10.4
20°-30°	740.5	15.3
30°-40°	860.0	17.8
40°-50°	859.0	17.7
50°-60°	749.0	15.5
60°-70°	553.7	11.4
70°-80°	313.3	6.5
80°-90°	82.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1423.5	29.4
0°-40°	2283.5	47.2
0°-60°	3891.5	80.4
0°-90°	4841.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4841.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1875	1890	1886	181
15°	1811	1800	1776	1784	1775	510
25°	1639	1625	1594	1597	1594	754
35°	1414	1396	1367	1356	1346	883
45°	1151	1138	1110	1091	1083	888
55°	871	860	838	816	807	779
65°	587	576	558	542	532	581
75°	307	304	294	284	287	328
85°	75	73	71	66	64	88
90°	0	0	0	0	0	

TEST NUMBER: P931309

CATALOG NUMBER: DFN2DS-TR2F0-060DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1913.8	1904.7	1884.4	1902.7	1899.2
5°	1902.7	1895.5	1875.3	1889.9	1886.4
7.5°	1889.9	1879.1	1858.9	1873.6	1869.9
10°	1869.9	1857.1	1835.1	1849.7	1844.3
12.5°	1842.4	1831.5	1809.5	1818.7	1815.0
15°	1811.3	1800.4	1776.5	1784.0	1774.8
17.5°	1772.9	1762.0	1738.2	1747.2	1738.2
20°	1730.7	1719.9	1694.2	1699.7	1692.5
22.5°	1688.8	1672.3	1648.4	1648.4	1644.8
25°	1639.3	1624.8	1593.7	1597.2	1593.7
27.5°	1584.4	1571.6	1547.8	1542.5	1533.3
30°	1529.7	1514.8	1487.5	1482.1	1474.7
32.5°	1471.0	1460.2	1430.8	1419.7	1412.4
35°	1414.4	1396.1	1366.8	1355.7	1346.5
37.5°	1350.3	1333.7	1304.5	1291.6	1282.5
40°	1284.4	1269.7	1240.4	1224.1	1216.7
42.5°	1220.4	1205.6	1176.5	1158.1	1147.2
45°	1150.9	1138.1	1110.5	1090.6	1083.1
47.5°	1083.1	1070.3	1041.1	1020.9	1009.9
50°	1011.7	1002.6	977.0	951.3	942.2
52.5°	942.2	929.4	905.7	885.6	872.8
55°	871.0	859.9	838.0	816.1	806.9
57.5°	799.6	790.5	766.6	744.7	737.2
60°	728.1	720.9	695.4	675.1	669.7
62.5°	658.6	645.8	627.6	609.3	602.0
65°	587.4	576.4	558.1	541.6	532.4
67.5°	514.2	504.9	488.6	475.8	468.4
70°	446.5	439.1	422.6	409.8	402.6
72.5°	376.9	369.6	360.5	347.7	342.2
75°	307.3	303.8	294.5	283.6	287.3
77.5°	245.2	237.8	234.1	228.7	223.2
80°	183.0	181.1	177.4	172.0	168.3
82.5°	124.5	124.5	122.7	115.3	115.3
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.3	25.6	20.2	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931309

CATALOG NUMBER: DFN2DS-TR2F0-060DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.31	17.92	16.67	18.23	18.54	15.86	17.47	16.23	17.79	18.10
	3H	18.06	19.51	18.43	19.84	20.20	17.56	19.02	17.94	19.35	19.71
	4H	18.70	20.07	19.10	20.42	20.79	18.21	19.58	18.60	19.92	20.30
	6H	19.17	20.44	19.58	20.80	21.19	18.67	19.94	19.08	20.30	20.69
	8H	19.31	20.52	19.74	20.91	21.31	18.81	20.02	19.24	20.41	20.81
	12H	19.40	20.56	19.83	20.95	21.37	18.89	20.05	19.32	20.43	20.86
4H	2H	16.87	18.23	17.26	18.58	18.96	16.51	17.88	16.91	18.23	18.61
	3H	18.84	19.99	19.25	20.38	20.78	18.43	19.58	18.84	19.98	20.38
	4H	19.62	20.65	20.05	21.07	21.50	19.19	20.23	19.62	20.64	21.08
	6H	20.21	21.12	20.67	21.56	22.02	19.78	20.69	20.24	21.13	21.58
	8H	20.40	21.25	20.86	21.69	22.16	19.96	20.81	20.43	21.25	21.72
	12H	20.53	21.29	21.02	21.77	22.24	20.08	20.84	20.56	21.32	21.79
8H	4H	19.89	20.74	20.35	21.18	21.64	19.52	20.36	19.98	20.81	21.27
	6H	20.60	21.31	21.10	21.80	22.27	20.22	20.93	20.72	21.41	21.89
	8H	20.86	21.49	21.37	22.00	22.49	20.47	21.10	20.98	21.61	22.10
	12H	21.06	21.62	21.57	22.11	22.67	20.65	21.21	21.16	21.70	22.26
12H	4H	19.92	20.68	20.40	21.15	21.62	19.55	20.31	20.03	20.79	21.26
	6H	20.65	21.28	21.16	21.79	22.27	20.28	20.91	20.79	21.42	21.91
	8H	20.96	21.52	21.47	22.01	22.57	20.59	21.14	21.09	21.63	22.20