

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929860

Luminaire Tested: DFN2DS-4P3F0-030DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-030DS830-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2402.1 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 28.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929860
CATALOG NUMBER: DFN2DS-4P3F0-030DS830-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P929860

CATALOG NUMBER: DFN2DS-4P3F0-030DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1331	1331	1331
5°	1336	1314	1322
10°	1326	1293	1282
15°	1311	1254	1218
20°	1289	1200	1139
25°	1268	1138	1063
30°	1238	1074	965
35°	1209	1004	879
40°	1179	932	780
45°	1145	852	690
50°	1109	770	602
55°	1073	682	517
60°	1031	590	429
65°	983	496	390
70°	926	408	359
75°	856	372	335
80°	756	333	305
85°	594	263	263

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1145 cd/sqm



TEST NUMBER: P929860
 CATALOG NUMBER: DFN2DS-4P3F0-030DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	4.6
10°-20°	300.5	12.5
20°-30°	421.9	17.6
30°-40°	459.9	19.1
40°-50°	422.7	17.6
50°-60°	332.0	13.8
60°-70°	216.1	9.0
70°-80°	111.2	4.6
80°-90°	28.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.9	34.6
0°-40°	1291.8	53.8
0°-60°	2046.4	85.2
0°-90°	2402.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2402.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1168	1168	1168	1168	1168	
5°	1168	1163	1149	1158	1155	111
15°	1111	1099	1063	1043	1033	313
25°	1008	974	905	862	846	464
35°	869	815	722	655	632	544
45°	710	639	529	453	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	120	85	77	76	206
85°	45	23	20	20	20	54
90°	0	0	0	0	0	



TEST NUMBER: P929860

CATALOG NUMBER: DFN2DS-4P3F0-030DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.0	1168.0	1168.0	1168.0	1168.0
2.5°	1173.3	1168.0	1156.3	1166.9	1164.9
5°	1168.0	1162.7	1149.0	1158.5	1155.3
7.5°	1158.5	1152.2	1137.4	1141.5	1136.2
10°	1145.8	1138.4	1117.3	1114.0	1107.8
12.5°	1129.9	1120.4	1091.9	1085.6	1073.9
15°	1110.9	1099.2	1063.3	1043.3	1032.7
17.5°	1088.7	1071.8	1027.3	1004.2	987.2
20°	1063.3	1042.1	989.3	963.0	939.6
22.5°	1035.9	1011.5	950.2	914.3	898.5
25°	1008.4	974.5	904.8	861.5	845.5
27.5°	975.6	939.6	862.5	812.9	788.5
30°	940.8	900.6	816.0	762.2	733.5
32.5°	906.9	858.3	771.7	708.2	681.7
35°	868.9	814.9	721.9	655.3	632.1
37.5°	831.9	773.7	675.4	602.4	576.1
40°	792.8	729.4	626.8	551.7	524.3
42.5°	752.6	685.0	578.2	499.9	473.5
45°	710.4	639.4	528.6	453.4	428.0
47.5°	670.1	595.2	481.0	405.8	382.6
50°	625.8	550.7	434.5	361.4	339.3
52.5°	582.3	503.1	390.1	320.3	300.2
55°	540.0	457.6	343.5	280.2	260.1
57.5°	496.8	412.2	302.4	243.1	226.2
60°	452.3	367.9	259.0	205.1	188.2
62.5°	409.1	324.5	221.9	171.3	162.9
65°	364.6	279.0	183.9	148.0	144.8
67.5°	322.4	236.7	148.0	130.0	126.8
70°	278.0	195.6	122.6	112.0	107.8
72.5°	235.7	157.4	102.5	94.1	91.9
75°	194.4	120.5	84.6	77.1	76.1
77.5°	153.3	85.5	66.6	62.4	60.2
80°	115.2	61.3	50.7	46.5	46.5
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P929860
 CATALOG NUMBER: DFN2DS-4P3F0-030DS830-RLI

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.23	13.75	12.59	14.06	14.38	8.19	9.71	8.55	10.02	10.34
	3H	13.99	15.36	14.37	15.69	16.05	9.45	10.82	9.83	11.15	11.51
	4H	14.66	15.94	15.06	16.29	16.67	9.95	11.24	10.35	11.58	11.96
	6H	15.15	16.33	15.56	16.70	17.09	10.34	11.52	10.75	11.88	12.28
	8H	15.31	16.44	15.74	16.83	17.23	10.46	11.59	10.89	11.98	12.38
	12H	15.42	16.50	15.85	16.88	17.31	10.54	11.62	10.97	12.00	12.43
4H	2H	12.33	13.61	12.73	13.96	14.34	8.88	10.16	9.28	10.51	10.89
	3H	14.27	15.33	14.68	15.73	16.13	10.33	11.39	10.74	11.79	12.19
	4H	15.01	15.97	15.45	16.39	16.83	10.93	11.88	11.36	12.30	12.74
	6H	15.61	16.44	16.06	16.88	17.34	11.41	12.25	11.87	12.69	13.15
	8H	15.82	16.60	16.28	17.04	17.51	11.58	12.35	12.04	12.80	13.26
	12H	15.97	16.67	16.46	17.15	17.62	11.69	12.39	12.18	12.87	13.34
8H	4H	15.04	15.82	15.50	16.26	16.73	11.28	12.06	11.74	12.50	12.97
	6H	15.68	16.32	16.17	16.81	17.29	11.87	12.51	12.36	13.00	13.48
	8H	15.93	16.50	16.44	17.01	17.50	12.09	12.66	12.60	13.17	13.66
	12H	16.13	16.64	16.64	17.13	17.70	12.27	12.78	12.78	13.27	13.83
12H	4H	15.02	15.72	15.51	16.20	16.67	11.32	12.02	11.81	12.50	12.97
	6H	15.66	16.23	16.17	16.74	17.23	11.93	12.51	12.44	13.02	13.51
	8H	15.94	16.45	16.45	16.94	17.51	12.20	12.71	12.71	13.21	13.77