

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929895

Luminaire Tested: DFN2DS-4P3F0-050DS830-FLL

Issue Date: 11/20/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P929895  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)  
Test Lab: INNOVATION CENTER  
Issue Date: 11/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DS-4P3F0-050DS830-FLL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4662.9 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 51.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P929895  
CATALOG NUMBER: DFN2DS-4P3F0-050DS830-FLL

### Luminous Intensity Polar Plot





TEST NUMBER: P929895

CATALOG NUMBER: DFN2DS-4P3F0-050DS830-FLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	73	73	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	62	62	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	54	54	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	47	47	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	41	41	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	37	37	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	27	27	27	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2089	2089	2089
5°	2097	2066	2079
10°	2084	2046	2056
15°	2058	2019	2017
20°	2022	1979	1977
25°	1985	1930	1930
30°	1939	1885	1869
35°	1895	1831	1804
40°	1841	1777	1743
45°	1786	1724	1681
50°	1728	1668	1609
55°	1667	1604	1544
60°	1598	1527	1470
65°	1526	1449	1383
70°	1433	1356	1292
75°	1303	1249	1219
80°	1157	1122	1064
85°	944	900	807

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1786 cd/sqm



TEST NUMBER: P929895  
 CATALOG NUMBER: DFN2DS-4P3F0-050DS830-FLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.5	3.7
10°-20°	485.3	10.4
20°-30°	713.2	15.3
30°-40°	828.4	17.8
40°-50°	827.4	17.7
50°-60°	721.4	15.5
60°-70°	533.3	11.4
70°-80°	301.7	6.5
80°-90°	79.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.1	29.4
0°-40°	2199.4	47.2
0°-60°	3748.2	80.4
0°-90°	4662.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4662.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1826	1806	1820	1817	174
15°	1745	1734	1711	1718	1709	491
25°	1579	1565	1535	1538	1535	727
35°	1362	1345	1316	1306	1297	851
45°	1108	1096	1070	1050	1043	856
55°	839	828	807	786	777	750
65°	566	555	538	522	513	559
75°	296	293	284	273	277	316
85°	72	70	69	63	62	85
90°	0	0	0	0	0	



TEST NUMBER: P929895

CATALOG NUMBER: DFN2DS-4P3F0-050DS830-FLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1832.7	1832.7	1832.7	1832.7	1832.7
2.5°	1843.3	1834.5	1815.1	1832.7	1829.4
5°	1832.7	1825.8	1806.3	1820.3	1817.0
7.5°	1820.3	1809.9	1790.5	1804.7	1801.1
10°	1801.1	1788.8	1767.7	1781.6	1776.4
12.5°	1774.5	1764.1	1743.0	1751.7	1748.2
15°	1744.6	1734.1	1711.1	1718.3	1709.4
17.5°	1707.6	1697.1	1674.1	1682.9	1674.1
20°	1667.1	1656.6	1631.9	1637.1	1630.2
22.5°	1626.6	1610.7	1587.7	1587.7	1584.2
25°	1579.0	1564.9	1535.0	1538.4	1535.0
27.5°	1526.0	1513.7	1490.9	1485.6	1476.9
30°	1473.3	1459.2	1432.8	1427.5	1420.4
32.5°	1416.9	1406.4	1378.1	1367.5	1360.4
35°	1362.2	1344.7	1316.4	1305.8	1297.0
37.5°	1300.5	1284.7	1256.4	1244.1	1235.3
40°	1237.2	1223.0	1194.7	1179.0	1171.9
42.5°	1175.5	1161.3	1133.2	1115.4	1105.0
45°	1108.5	1096.2	1069.6	1050.4	1043.3
47.5°	1043.3	1030.9	1002.8	983.3	972.8
50°	974.5	965.7	941.1	916.4	907.5
52.5°	907.5	895.2	872.4	853.0	840.6
55°	838.9	828.3	807.1	786.0	777.2
57.5°	770.1	761.3	738.3	717.2	710.1
60°	701.3	694.4	669.8	650.3	645.1
62.5°	634.4	622.1	604.5	586.9	579.8
65°	565.8	555.1	537.5	521.7	512.8
67.5°	495.3	486.4	470.6	458.3	451.1
70°	430.0	423.0	407.0	394.7	387.8
72.5°	363.1	356.0	347.2	334.9	329.6
75°	296.0	292.6	283.6	273.2	276.8
77.5°	236.2	229.0	225.5	220.2	215.1
80°	176.3	174.5	170.9	165.7	162.1
82.5°	119.8	119.8	118.1	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.7	28.3	24.7	19.4	17.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P929895  
 CATALOG NUMBER: DFN2DS-4P3F0-050DS830-FLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.84	15.45	14.21	15.77	16.08	13.40	15.01	13.76	15.32	15.64
	3H	15.59	17.05	15.97	17.37	17.73	15.10	16.55	15.48	16.88	17.24
	4H	16.24	17.61	16.64	17.95	18.33	15.74	17.11	16.14	17.46	17.84
	6H	16.71	17.98	17.12	18.34	18.73	16.21	17.47	16.62	17.84	18.23
	8H	16.85	18.06	17.27	18.45	18.85	16.35	17.56	16.77	17.95	18.35
	12H	16.94	18.10	17.37	18.48	18.91	16.43	17.59	16.86	17.97	18.40
4H	2H	14.40	15.77	14.80	16.12	16.49	14.05	15.42	14.45	15.77	16.14
	3H	16.38	17.52	16.79	17.92	18.32	15.97	17.12	16.38	17.51	17.91
	4H	17.15	18.19	17.58	18.60	19.04	16.73	17.77	17.16	18.18	18.62
	6H	17.75	18.65	18.20	19.10	19.55	17.32	18.22	17.77	18.66	19.12
	8H	17.94	18.79	18.40	19.23	19.69	17.50	18.35	17.96	18.79	19.26
	12H	18.07	18.83	18.55	19.31	19.78	17.62	18.38	18.10	18.86	19.32
8H	4H	17.43	18.27	17.89	18.72	19.18	17.05	17.90	17.51	18.34	18.81
	6H	18.14	18.84	18.63	19.33	19.81	17.76	18.46	18.25	18.95	19.43
	8H	18.40	19.03	18.91	19.54	20.02	18.01	18.64	18.52	19.15	19.63
	12H	18.60	19.16	19.11	19.65	20.21	18.19	18.75	18.69	19.24	19.80
12H	4H	17.45	18.21	17.93	18.69	19.16	17.09	17.85	17.57	18.32	18.79
	6H	18.19	18.82	18.70	19.33	19.81	17.82	18.45	18.33	18.96	19.44
	8H	18.50	19.06	19.01	19.55	20.11	18.12	18.68	18.63	19.17	19.73