

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931260

Luminaire Tested: DFN2DS-TR2F0-030DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-030DS940-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2274.6 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 27.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931260

CATALOG NUMBER: DFN2DS-TR2F0-030DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931260

CATALOG NUMBER: DFN2DS-TR2F0-030DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2467	2467	2467
5°	2476	2436	2449
10°	2457	2396	2376
15°	2429	2325	2258
20°	2390	2224	2112
25°	2350	2109	1971
30°	2294	1990	1789
35°	2240	1861	1630
40°	2186	1728	1446
45°	2122	1579	1278
50°	2056	1428	1115
55°	1989	1265	958
60°	1911	1094	795
65°	1822	919	724
70°	1716	756	665
75°	1587	690	621
80°	1401	617	566
85°	1100	486	486

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2122 cd/sqm

TEST NUMBER: P931260

CATALOG NUMBER: DFN2DS-TR2F0-030DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.7	4.6
10°-20°	284.6	12.5
20°-30°	399.5	17.6
30°-40°	435.5	19.1
40°-50°	400.3	17.6
50°-60°	314.3	13.8
60°-70°	204.6	9.0
70°-80°	105.3	4.6
80°-90°	26.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.7	34.6
0°-40°	1223.2	53.8
0°-60°	1937.8	85.2
0°-90°	2274.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2274.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1106	1101	1088	1097	1094	105
15°	1052	1041	1007	988	978	296
25°	955	923	857	816	801	439
35°	823	772	684	621	598	515
45°	673	606	500	429	405	519
55°	511	433	325	265	246	457
65°	345	264	174	140	137	342
75°	184	114	80	73	72	195
85°	43	22	19	19	19	52
90°	0	0	0	0	0	

TEST NUMBER: P931260

CATALOG NUMBER: DFN2DS-TR2F0-030DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1106.0	1106.0	1106.0	1106.0	1106.0
2.5°	1111.0	1106.0	1094.9	1105.0	1103.0
5°	1106.0	1101.0	1088.0	1097.0	1093.9
7.5°	1097.0	1091.0	1077.0	1080.9	1075.9
10°	1084.9	1078.0	1058.0	1054.9	1049.0
12.5°	1070.0	1060.9	1033.9	1027.9	1016.9
15°	1051.9	1040.9	1006.9	987.9	977.9
17.5°	1030.9	1014.9	972.8	950.9	934.8
20°	1006.9	986.8	936.8	911.9	889.8
22.5°	980.9	957.8	899.8	865.8	850.8
25°	954.9	922.8	856.8	815.7	800.7
27.5°	923.8	889.8	816.7	769.7	746.6
30°	890.8	852.8	772.7	721.7	694.6
32.5°	858.7	812.7	730.7	670.6	645.5
35°	822.8	771.7	683.6	620.6	598.5
37.5°	787.7	732.6	639.6	570.4	545.5
40°	750.7	690.7	593.5	522.4	496.5
42.5°	712.6	648.7	547.5	473.4	448.4
45°	672.7	605.5	500.5	429.3	405.3
47.5°	634.6	563.6	455.5	384.3	362.3
50°	592.6	521.5	411.4	342.3	321.3
52.5°	551.4	476.4	369.4	303.3	284.3
55°	511.4	433.3	325.2	265.3	246.3
57.5°	470.4	390.3	286.3	230.2	214.2
60°	428.3	348.3	245.2	194.2	178.2
62.5°	387.4	307.3	210.2	162.2	154.2
65°	345.3	264.2	174.1	140.1	137.1
67.5°	305.3	224.2	140.1	123.1	120.1
70°	263.2	185.2	116.0	106.1	102.0
72.5°	223.2	149.1	97.0	89.1	87.1
75°	184.1	114.1	80.1	73.1	72.1
77.5°	145.1	81.0	63.1	59.1	57.0
80°	109.1	58.1	48.0	44.1	44.1
82.5°	76.0	39.1	33.0	31.0	31.0
85°	43.0	21.9	19.0	19.0	19.0
87.5°	16.1	7.9	7.9	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931260

CATALOG NUMBER: DFN2DS-TR2F0-030DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.37	15.89	14.74	16.21	16.52	10.33	11.85	10.70	12.17	12.48
	3H	16.14	17.50	16.51	17.83	18.19	11.60	12.96	11.98	13.29	13.65
	4H	16.80	18.08	17.20	18.43	18.81	12.10	13.38	12.50	13.73	14.11
	6H	17.29	18.47	17.70	18.84	19.23	12.48	13.66	12.89	14.03	14.42
	8H	17.46	18.58	17.88	18.97	19.37	12.60	13.73	13.03	14.12	14.52
	12H	17.56	18.64	17.99	19.02	19.45	12.69	13.76	13.12	14.15	14.58
4H	2H	14.47	15.76	14.87	16.10	16.48	11.03	12.31	11.43	12.66	13.03
	3H	16.41	17.47	16.82	17.87	18.27	12.47	13.53	12.88	13.93	14.33
	4H	17.16	18.11	17.59	18.53	18.97	13.07	14.03	13.50	14.44	14.88
	6H	17.75	18.58	18.21	19.02	19.48	13.56	14.39	14.02	14.83	15.29
	8H	17.96	18.74	18.43	19.19	19.65	13.72	14.50	14.18	14.94	15.41
	12H	18.12	18.81	18.60	19.29	19.76	13.84	14.53	14.32	15.01	15.48
8H	4H	17.18	17.96	17.65	18.40	18.87	13.42	14.20	13.89	14.65	15.11
	6H	17.82	18.46	18.32	18.95	19.43	14.01	14.65	14.51	15.15	15.62
	8H	18.07	18.65	18.58	19.16	19.64	14.23	14.81	14.75	15.32	15.81
	12H	18.27	18.78	18.78	19.28	19.84	14.41	14.92	14.92	15.41	15.98
12H	4H	17.17	17.86	17.65	18.34	18.81	13.47	14.16	13.95	14.64	15.11
	6H	17.80	18.38	18.31	18.89	19.38	14.07	14.65	14.59	15.16	15.65
	8H	18.09	18.59	18.59	19.09	19.65	14.35	14.86	14.86	15.35	15.91