

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929866

Luminaire Tested: DFN2DS-4P3F0-030DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-030DS850-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2827.9 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 28.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929866

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929866

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1567	1567	1567
5°	1573	1547	1556
10°	1561	1522	1509
15°	1543	1477	1434
20°	1518	1412	1342
25°	1493	1339	1252
30°	1457	1264	1136
35°	1423	1182	1035
40°	1388	1098	918
45°	1348	1003	812
50°	1306	907	708
55°	1263	803	608
60°	1214	695	505
65°	1158	584	460
70°	1091	481	423
75°	1008	439	395
80°	890	392	360
85°	700	309	309

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1348 cd/sqm

TEST NUMBER: P929866

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	4.6
10°-20°	353.8	12.5
20°-30°	496.7	17.6
30°-40°	541.4	19.1
40°-50°	497.6	17.6
50°-60°	390.8	13.8
60°-70°	254.4	9.0
70°-80°	130.9	4.6
80°-90°	33.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.3	34.6
0°-40°	1520.7	53.8
0°-60°	2409.2	85.2
0°-90°	2827.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2827.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	64
90°	0	0	0	0	0	

TEST NUMBER: P929866

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929866

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.80	14.32	13.16	14.63	14.94	8.76	10.28	9.12	10.59	10.91
	3H	14.56	15.93	14.94	16.25	16.62	10.02	11.39	10.40	11.71	12.08
	4H	15.23	16.51	15.63	16.86	17.23	10.52	11.80	10.92	12.15	12.53
	6H	15.72	16.90	16.13	17.26	17.66	10.90	12.09	11.32	12.45	12.84
	8H	15.88	17.01	16.31	17.40	17.80	11.03	12.15	11.45	12.54	12.95
	12H	15.98	17.06	16.41	17.44	17.87	11.11	12.19	11.54	12.57	13.00
4H	2H	12.90	14.18	13.30	14.53	14.91	9.45	10.73	9.85	11.08	11.46
	3H	14.83	15.90	15.24	16.29	16.70	10.89	11.96	11.30	12.36	12.76
	4H	15.58	16.54	16.01	16.95	17.39	11.49	12.45	11.93	12.87	13.30
	6H	16.17	17.01	16.63	17.45	17.91	11.98	12.81	12.44	13.26	13.72
	8H	16.39	17.17	16.85	17.61	18.08	12.14	12.92	12.61	13.37	13.83
	12H	16.54	17.24	17.02	17.71	18.19	12.26	12.96	12.74	13.43	13.90
8H	4H	15.61	16.38	16.07	16.83	17.29	11.85	12.62	12.31	13.07	13.54
	6H	16.24	16.89	16.74	17.38	17.85	12.43	13.08	12.93	13.57	14.04
	8H	16.49	17.07	17.01	17.58	18.07	12.66	13.23	13.17	13.74	14.23
	12H	16.70	17.21	17.21	17.70	18.26	12.83	13.34	13.34	13.84	14.40
12H	4H	15.59	16.28	16.07	16.76	17.23	11.89	12.58	12.37	13.06	13.53
	6H	16.22	16.80	16.74	17.31	17.80	12.50	13.07	13.01	13.58	14.07
	8H	16.51	17.02	17.02	17.51	18.07	12.77	13.28	13.28	13.77	14.34