

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929868

Luminaire Tested: DFN2DS-4P3F0-030DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-030DS927-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2019.6 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 28.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929868

CATALOG NUMBER: DFN2DS-4P3F0-030DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929868

CATALOG NUMBER: DFN2DS-4P3F0-030DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1119	1119	1119
5°	1123	1105	1111
10°	1115	1087	1078
15°	1102	1055	1024
20°	1084	1009	958
25°	1066	957	894
30°	1041	903	812
35°	1016	844	739
40°	992	784	656
45°	962	716	580
50°	933	648	506
55°	902	574	435
60°	867	496	361
65°	827	417	328
70°	779	343	302
75°	720	313	282
80°	636	280	257
85°	499	221	221

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 962 cd/sqm

TEST NUMBER: P929868

CATALOG NUMBER: DFN2DS-4P3F0-030DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	4.6
10°-20°	252.7	12.5
20°-30°	354.7	17.6
30°-40°	386.7	19.1
40°-50°	355.4	17.6
50°-60°	279.1	13.8
60°-70°	181.6	9.0
70°-80°	93.5	4.6
80°-90°	23.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.4	34.6
0°-40°	1086.1	53.8
0°-60°	1720.5	85.2
0°-90°	2019.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2019.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	982	978	966	974	971	93
15°	934	924	894	877	868	263
25°	848	819	761	724	711	390
35°	730	685	607	551	531	457
45°	597	538	444	381	360	461
55°	454	385	289	236	219	406
65°	307	235	155	124	122	304
75°	164	101	71	65	64	173
85°	38	20	17	17	17	46
90°	0	0	0	0	0	

TEST NUMBER: P929868

CATALOG NUMBER: DFN2DS-4P3F0-030DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.0	982.0	982.0	982.0	982.0
2.5°	986.4	982.0	972.2	981.1	979.4
5°	982.0	977.6	966.0	974.0	971.3
7.5°	974.0	968.7	956.3	959.7	955.3
10°	963.3	957.1	939.4	936.6	931.4
12.5°	950.0	942.0	918.0	912.7	902.9
15°	934.0	924.2	894.0	877.1	868.3
17.5°	915.3	901.1	863.8	844.3	830.0
20°	894.0	876.2	831.8	809.7	790.0
22.5°	871.0	850.4	798.9	768.7	755.4
25°	847.8	819.3	760.7	724.3	710.9
27.5°	820.3	790.0	725.2	683.4	662.9
30°	791.0	757.2	686.0	640.8	616.7
32.5°	762.5	721.6	648.8	595.4	573.2
35°	730.5	685.2	607.0	551.0	531.4
37.5°	699.4	650.5	567.9	506.5	484.4
40°	666.5	613.2	527.0	463.9	440.8
42.5°	632.7	575.9	486.1	420.3	398.1
45°	597.2	537.6	444.4	381.2	359.9
47.5°	563.4	500.4	404.4	341.2	321.7
50°	526.1	463.0	365.3	303.9	285.3
52.5°	489.6	423.0	328.0	269.3	252.4
55°	454.1	384.8	288.8	235.5	218.7
57.5°	417.7	346.6	254.2	204.4	190.2
60°	380.3	309.3	217.7	172.4	158.2
62.5°	344.0	272.8	186.6	144.0	136.9
65°	306.6	234.6	154.6	124.4	121.7
67.5°	271.1	199.0	124.4	109.3	106.6
70°	233.7	164.4	103.0	94.2	90.6
72.5°	198.2	132.3	86.2	79.1	77.3
75°	163.5	101.3	71.1	64.9	64.0
77.5°	128.9	71.9	56.0	52.4	50.6
80°	96.9	51.6	42.6	39.1	39.1
82.5°	67.5	34.7	29.3	27.6	27.6
85°	38.2	19.5	16.9	16.9	16.9
87.5°	14.3	7.0	7.0	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929868

CATALOG NUMBER: DFN2DS-4P3F0-030DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.63	13.15	11.99	13.46	13.78	7.59	9.11	7.95	9.42	9.74
	3H	13.39	14.76	13.77	15.08	15.45	8.85	10.22	9.23	10.54	10.91
	4H	14.06	15.34	14.46	15.69	16.06	9.35	10.63	9.75	10.98	11.36
	6H	14.55	15.73	14.96	16.10	16.49	9.73	10.92	10.15	11.28	11.67
	8H	14.71	15.84	15.14	16.23	16.63	9.86	10.98	10.28	11.37	11.78
	12H	14.81	15.89	15.25	16.28	16.70	9.94	11.02	10.37	11.40	11.83
4H	2H	11.73	13.01	12.13	13.36	13.74	8.28	9.56	8.68	9.91	10.29
	3H	13.66	14.73	14.07	15.13	15.53	9.72	10.79	10.13	11.19	11.59
	4H	14.41	15.37	14.84	15.78	16.22	10.32	11.28	10.76	11.70	12.13
	6H	15.00	15.84	15.46	16.28	16.74	10.81	11.64	11.27	12.09	12.55
	8H	15.22	16.00	15.68	16.44	16.91	10.97	11.75	11.44	12.20	12.66
	12H	15.37	16.07	15.85	16.55	17.02	11.09	11.79	11.57	12.26	12.74
8H	4H	14.44	15.21	14.90	15.66	16.13	10.68	11.46	11.14	11.90	12.37
	6H	15.07	15.72	15.57	16.21	16.69	11.26	11.91	11.76	12.40	12.87
	8H	15.32	15.90	15.84	16.41	16.90	11.49	12.06	12.00	12.57	13.06
	12H	15.53	16.04	16.04	16.53	17.10	11.67	12.18	12.18	12.67	13.23
12H	4H	14.42	15.12	14.90	15.59	16.06	10.72	11.42	11.20	11.89	12.36
	6H	15.05	15.63	15.57	16.14	16.63	11.33	11.90	11.84	12.41	12.90
	8H	15.34	15.85	15.85	16.34	16.91	11.60	12.11	12.11	12.60	13.17