

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930026

Luminaire Tested: DFN2DS-4P4F0-080DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-080DS840-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6806.8 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 86.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930026
CATALOG NUMBER: DFN2DS-4P4F0-080DS840-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P930026

CATALOG NUMBER: DFN2DS-4P4F0-080DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2147	2147	2147
5°	2155	2120	2132
10°	2139	2086	2068
15°	2114	2024	1965
20°	2080	1935	1838
25°	2045	1835	1715
30°	1997	1732	1557
35°	1950	1620	1418
40°	1902	1504	1258
45°	1847	1374	1113
50°	1790	1242	971
55°	1731	1101	833
60°	1663	952	692
65°	1586	800	630
70°	1494	659	579
75°	1381	601	541
80°	1219	536	492
85°	958	424	424

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1847 cd/sqm



TEST NUMBER: P930026
 CATALOG NUMBER: DFN2DS-4P4F0-080DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.2	4.6
10°-20°	851.5	12.5
20°-30°	1195.5	17.6
30°-40°	1303.2	19.1
40°-50°	1197.8	17.6
50°-60°	940.7	13.8
60°-70°	612.3	9.0
70°-80°	315.2	4.6
80°-90°	80.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2357.2	34.6
0°-40°	3660.4	53.8
0°-60°	5798.9	85.2
0°-90°	6806.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6806.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3310	3310	3310	3310	3310	
5°	3310	3295	3256	3283	3274	314
15°	3148	3115	3013	2956	2926	887
25°	2858	2762	2564	2441	2396	1314
35°	2462	2309	2046	1857	1791	1541
45°	2013	1812	1498	1285	1213	1554
55°	1530	1297	973	794	737	1368
65°	1033	791	521	420	410	1025
75°	551	341	240	219	216	583
85°	129	66	57	57	57	154
90°	0	0	0	0	0	



TEST NUMBER: P930026

CATALOG NUMBER: DFN2DS-4P4F0-080DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3309.7	3309.7	3309.7	3309.7	3309.7
2.5°	3324.6	3309.7	3276.7	3306.8	3300.8
5°	3309.7	3294.8	3255.7	3282.7	3273.8
7.5°	3282.7	3264.9	3222.9	3234.7	3219.7
10°	3246.7	3225.8	3166.1	3156.9	3139.0
12.5°	3202.0	3175.0	3093.9	3076.1	3043.0
15°	3147.9	3114.9	3013.2	2956.4	2926.4
17.5°	3085.0	3037.0	2911.2	2845.4	2797.4
20°	3013.2	2953.2	2803.5	2728.8	2662.7
22.5°	2935.3	2866.4	2692.6	2590.9	2546.0
25°	2857.5	2761.6	2563.9	2441.2	2396.1
27.5°	2764.7	2662.7	2444.0	2303.3	2234.3
30°	2665.9	2551.7	2312.2	2159.7	2078.6
32.5°	2569.9	2432.0	2186.7	2006.8	1931.8
35°	2462.2	2309.3	2045.8	1857.2	1791.0
37.5°	2357.3	2192.4	1914.0	1707.1	1632.4
40°	2246.4	2066.9	1776.1	1563.5	1485.6
42.5°	2132.6	1941.0	1638.4	1416.7	1341.9
45°	2012.8	1812.0	1497.7	1284.8	1213.0
47.5°	1899.1	1686.5	1363.0	1150.0	1084.3
50°	1773.2	1560.7	1231.1	1024.2	961.6
52.5°	1650.2	1425.5	1105.2	907.6	850.7
55°	1530.4	1296.9	973.4	793.8	736.9
57.5°	1407.8	1168.2	856.8	689.0	640.9
60°	1281.9	1042.3	733.7	581.2	533.2
62.5°	1159.3	919.6	628.9	485.3	461.5
65°	1033.4	790.6	521.1	419.5	410.2
67.5°	913.6	670.9	419.5	368.3	359.5
70°	787.8	554.3	347.3	317.4	305.4
72.5°	668.0	446.1	290.5	266.7	260.6
75°	551.1	341.3	239.6	218.6	215.8
77.5°	434.4	242.4	188.8	176.7	170.7
80°	326.3	173.9	143.6	131.8	131.8
82.5°	227.5	116.9	98.8	92.8	92.8
85°	128.7	65.8	56.9	56.9	56.9
87.5°	47.9	23.8	23.8	21.0	21.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930026
 CATALOG NUMBER: DFN2DS-4P4F0-080DS840-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.89	15.41	14.25	15.72	16.04	9.85	11.37	10.22	11.69	12.00
	3H	15.66	17.02	16.03	17.35	17.71	11.12	12.48	11.49	12.81	13.17
	4H	16.32	17.60	16.72	17.95	18.33	11.62	12.90	12.02	13.25	13.63
	6H	16.81	17.99	17.22	18.36	18.75	12.00	13.18	12.41	13.55	13.94
	8H	16.98	18.10	17.40	18.49	18.89	12.12	13.25	12.55	13.64	14.04
	12H	17.08	18.16	17.51	18.54	18.97	12.20	13.28	12.63	13.66	14.09
4H	2H	13.99	15.27	14.39	15.62	16.00	10.55	11.83	10.95	12.18	12.55
	3H	15.93	16.99	16.34	17.39	17.79	11.99	13.05	12.40	13.45	13.85
	4H	16.68	17.63	17.11	18.05	18.49	12.59	13.54	13.02	13.96	14.40
	6H	17.27	18.10	17.73	18.54	19.00	13.08	13.91	13.53	14.35	14.81
	8H	17.48	18.26	17.95	18.70	19.17	13.24	14.02	13.70	14.46	14.93
	12H	17.64	18.33	18.12	18.81	19.28	13.36	14.05	13.84	14.53	15.00
8H	4H	16.70	17.48	17.16	17.92	18.39	12.94	13.72	13.41	14.16	14.63
	6H	17.34	17.98	17.83	18.47	18.95	13.53	14.17	14.03	14.66	15.14
	8H	17.59	18.16	18.10	18.67	19.16	13.75	14.33	14.26	14.84	15.32
	12H	17.79	18.30	18.30	18.79	19.36	13.93	14.44	14.44	14.93	15.50
12H	4H	16.69	17.38	17.17	17.86	18.33	12.99	13.68	13.47	14.16	14.63
	6H	17.32	17.90	17.83	18.41	18.89	13.59	14.17	14.11	14.68	15.17
	8H	17.60	18.11	18.11	18.61	19.17	13.87	14.37	14.37	14.87	15.43