

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931315

Luminaire Tested: DFN2DS-TR2F0-060DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-060DS950-FLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.3 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931315

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931315

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4921	4921	4921
5°	4940	4868	4897
10°	4911	4819	4843
15°	4850	4757	4752
20°	4763	4663	4658
25°	4678	4548	4548
30°	4568	4442	4404
35°	4465	4315	4251
40°	4336	4188	4108
45°	4209	4062	3961
50°	4071	3931	3791
55°	3927	3778	3638
60°	3766	3597	3464
65°	3595	3415	3258
70°	3376	3195	3044
75°	3070	2942	2871
80°	2726	2642	2506
85°	2221	2119	1901

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4209 cd/sqm

TEST NUMBER: P931315

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	3.7
10°-20°	584.3	10.4
20°-30°	858.6	15.3
30°-40°	997.2	17.8
40°-50°	996.0	17.7
50°-60°	868.5	15.5
60°-70°	642.0	11.4
70°-80°	363.2	6.5
80°-90°	95.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1650.5	29.4
0°-40°	2647.7	47.2
0°-60°	4512.2	80.4
0°-90°	5613.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5613.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2206	2206	2206	2206	2206	
5°	2206	2198	2174	2191	2187	209
15°	2100	2088	2060	2068	2058	592
25°	1901	1884	1848	1852	1848	875
35°	1640	1619	1585	1572	1561	1024
45°	1334	1320	1288	1264	1256	1030
55°	1010	997	972	946	936	903
65°	681	668	647	628	617	673
75°	356	352	341	329	333	380
85°	87	85	83	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P931315

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2206.2	2206.2	2206.2	2206.2	2206.2
2.5°	2219.0	2208.5	2185.0	2206.2	2202.1
5°	2206.2	2197.9	2174.4	2191.4	2187.3
7.5°	2191.4	2178.8	2155.4	2172.5	2168.2
10°	2168.2	2153.4	2127.9	2144.8	2138.4
12.5°	2136.3	2123.6	2098.2	2108.8	2104.5
15°	2100.2	2087.6	2059.9	2068.5	2057.9
17.5°	2055.7	2043.1	2015.4	2025.9	2015.4
20°	2006.8	1994.2	1964.5	1970.8	1962.5
22.5°	1958.2	1939.0	1911.4	1911.4	1907.1
25°	1900.8	1884.0	1847.9	1851.9	1847.9
27.5°	1837.1	1822.2	1794.7	1788.5	1777.9
30°	1773.7	1756.5	1724.8	1718.5	1709.9
32.5°	1705.6	1693.1	1659.0	1646.2	1637.7
35°	1640.0	1618.8	1584.8	1571.9	1561.3
37.5°	1565.7	1546.5	1512.6	1497.6	1487.1
40°	1489.3	1472.2	1438.3	1419.4	1410.8
42.5°	1415.0	1397.9	1364.2	1342.8	1330.2
45°	1334.5	1319.6	1287.7	1264.5	1255.9
47.5°	1255.9	1241.1	1207.1	1183.7	1171.0
50°	1173.1	1162.5	1132.9	1103.1	1092.5
52.5°	1092.5	1077.7	1050.2	1026.8	1012.0
55°	1009.9	997.1	971.6	946.2	935.6
57.5°	927.1	916.6	888.9	863.4	854.8
60°	844.3	835.9	806.3	782.8	776.5
62.5°	763.7	748.8	727.6	706.5	698.0
65°	681.1	668.3	647.1	628.0	617.4
67.5°	596.2	585.4	566.5	551.7	543.1
70°	517.7	509.2	490.0	475.1	466.8
72.5°	437.1	428.6	418.0	403.1	396.8
75°	356.3	352.3	341.4	328.9	333.1
77.5°	284.3	275.8	271.4	265.2	258.8
80°	212.2	210.0	205.7	199.4	195.1
82.5°	144.3	144.3	142.2	133.7	133.7
85°	86.8	84.9	82.8	76.3	74.3
87.5°	38.3	34.0	29.7	23.4	21.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931315

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.82	18.43	17.18	18.74	19.06	16.37	17.99	16.74	18.30	18.61
	3H	18.57	20.02	18.95	20.35	20.71	18.08	19.53	18.45	19.86	20.22
	4H	19.22	20.58	19.61	20.93	21.31	18.72	20.09	19.12	20.44	20.81
	6H	19.68	20.95	20.10	21.32	21.71	19.18	20.45	19.59	20.82	21.21
	8H	19.83	21.04	20.25	21.43	21.83	19.32	20.54	19.75	20.92	21.32
	12H	19.92	21.08	20.35	21.46	21.89	19.41	20.57	19.83	20.95	21.38
4H	2H	17.38	18.75	17.78	19.10	19.47	17.03	18.40	17.42	18.74	19.12
	3H	19.35	20.50	19.76	20.90	21.30	18.95	20.09	19.36	20.49	20.89
	4H	20.13	21.17	20.56	21.58	22.02	19.71	20.74	20.14	21.16	21.59
	6H	20.73	21.63	21.18	22.07	22.53	20.30	21.20	20.75	21.64	22.10
	8H	20.92	21.76	21.38	22.21	22.67	20.48	21.33	20.94	21.77	22.23
	12H	21.05	21.81	21.53	22.28	22.75	20.60	21.36	21.08	21.83	22.30
8H	4H	20.40	21.25	20.87	21.69	22.16	20.03	20.88	20.49	21.32	21.78
	6H	21.12	21.82	21.61	22.31	22.79	20.74	21.44	21.23	21.93	22.40
	8H	21.38	22.01	21.89	22.52	23.00	20.99	21.62	21.50	22.12	22.61
	12H	21.58	22.14	22.08	22.63	23.19	21.16	21.72	21.67	22.21	22.77
12H	4H	20.43	21.19	20.91	21.67	22.14	20.07	20.83	20.55	21.30	21.77
	6H	21.16	21.80	21.67	22.30	22.79	20.80	21.43	21.30	21.93	22.42
	8H	21.48	22.04	21.99	22.53	23.09	21.10	21.66	21.61	22.15	22.71

END OF REPORT