

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929964

Luminaire Tested: DFN2DS-4P4F0-040DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-040DS940-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3032.8 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 39.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929964
CATALOG NUMBER: DFN2DS-4P4F0-040DS940-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P929964

CATALOG NUMBER: DFN2DS-4P4F0-040DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	957	957	957
5°	960	945	950
10°	953	929	921
15°	942	902	876
20°	927	862	819
25°	911	818	764
30°	890	772	694
35°	869	722	632
40°	848	670	561
45°	823	612	496
50°	797	554	432
55°	771	491	371
60°	741	424	308
65°	707	356	281
70°	666	294	258
75°	615	268	241
80°	543	239	220
85°	427	188	188

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 823 cd/sqm



TEST NUMBER: P929964
 CATALOG NUMBER: DFN2DS-4P4F0-040DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	4.6
10°-20°	379.4	12.5
20°-30°	532.7	17.6
30°-40°	580.6	19.1
40°-50°	533.7	17.6
50°-60°	419.1	13.8
60°-70°	272.8	9.0
70°-80°	140.4	4.6
80°-90°	35.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1050.3	34.6
0°-40°	1630.9	53.8
0°-60°	2583.7	85.2
0°-90°	3032.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3032.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1475	1468	1451	1463	1459	140
15°	1403	1388	1342	1317	1304	395
25°	1273	1230	1142	1088	1068	586
35°	1097	1029	912	827	798	687
45°	897	807	667	572	540	693
55°	682	578	434	354	328	609
65°	460	352	232	187	183	457
75°	246	152	107	97	96	260
85°	57	29	25	25	25	69
90°	0	0	0	0	0	



TEST NUMBER: P929964

CATALOG NUMBER: DFN2DS-4P4F0-040DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.7	1474.7	1474.7	1474.7	1474.7
2.5°	1481.3	1474.7	1459.9	1473.4	1470.6
5°	1474.7	1468.0	1450.6	1462.6	1458.7
7.5°	1462.6	1454.7	1436.0	1441.2	1434.6
10°	1446.6	1437.3	1410.6	1406.5	1398.7
12.5°	1426.7	1414.6	1378.5	1370.6	1355.8
15°	1402.6	1387.9	1342.5	1317.2	1303.9
17.5°	1374.6	1353.2	1297.1	1267.8	1246.4
20°	1342.5	1315.8	1249.1	1215.8	1186.4
22.5°	1307.9	1277.2	1199.7	1154.3	1134.4
25°	1273.2	1230.4	1142.3	1087.7	1067.5
27.5°	1231.9	1186.4	1089.0	1026.2	995.5
30°	1187.8	1136.9	1030.2	962.2	926.2
32.5°	1145.1	1083.6	974.2	894.1	860.7
35°	1097.1	1028.9	911.5	827.4	798.0
37.5°	1050.3	976.8	852.8	760.6	727.3
40°	1000.9	920.9	791.4	696.7	662.0
42.5°	950.2	864.8	730.0	631.2	597.9
45°	896.8	807.3	667.3	572.5	540.5
47.5°	846.2	751.4	607.3	512.5	483.1
50°	790.0	695.3	548.5	456.3	428.4
52.5°	735.3	635.2	492.5	404.3	379.0
55°	681.9	577.8	433.7	353.7	328.3
57.5°	627.3	520.5	381.7	306.9	285.6
60°	571.1	464.4	326.9	258.9	237.6
62.5°	516.6	409.8	280.2	216.2	205.6
65°	460.5	352.3	232.2	186.9	182.8
67.5°	407.1	298.9	186.9	164.1	160.1
70°	351.0	246.9	154.8	141.5	136.0
72.5°	297.7	198.8	129.4	118.8	116.1
75°	245.5	152.1	106.8	97.4	96.2
77.5°	193.6	108.0	84.1	78.8	76.0
80°	145.4	77.4	64.0	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.4	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P929964
 CATALOG NUMBER: DFN2DS-4P4F0-040DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.08	12.60	11.45	12.92	13.23	7.04	8.56	7.41	8.88	9.19
	3H	12.85	14.21	13.22	14.54	14.90	8.31	9.67	8.68	10.00	10.36
	4H	13.51	14.79	13.91	15.14	15.52	8.81	10.09	9.21	10.44	10.82
	6H	14.00	15.18	14.41	15.55	15.94	9.19	10.37	9.60	10.74	11.13
	8H	14.17	15.29	14.59	15.68	16.08	9.31	10.44	9.74	10.83	11.23
	12H	14.27	15.35	14.70	15.73	16.16	9.39	10.47	9.82	10.85	11.28
4H	2H	11.18	12.47	11.58	12.81	13.19	7.74	9.02	8.14	9.37	9.74
	3H	13.12	14.18	13.53	14.58	14.98	9.18	10.24	9.59	10.64	11.04
	4H	13.87	14.82	14.30	15.24	15.68	9.78	10.74	10.21	11.15	11.59
	6H	14.46	15.29	14.92	15.73	16.19	10.27	11.10	10.73	11.54	12.00
	8H	14.67	15.45	15.14	15.90	16.36	10.43	11.21	10.89	11.65	12.12
	12H	14.83	15.52	15.31	16.00	16.47	10.55	11.24	11.03	11.72	12.19
8H	4H	13.89	14.67	14.36	15.11	15.58	10.13	10.91	10.60	11.35	11.82
	6H	14.53	15.17	15.03	15.66	16.14	10.72	11.36	11.22	11.85	12.33
	8H	14.78	15.36	15.29	15.87	16.35	10.94	11.52	11.45	12.03	12.52
	12H	14.98	15.49	15.49	15.99	16.55	11.12	11.63	11.63	12.12	12.69
12H	4H	13.88	14.57	14.36	15.05	15.52	10.18	10.87	10.66	11.35	11.82
	6H	14.51	15.09	15.02	15.60	16.09	10.78	11.36	11.30	11.87	12.36
	8H	14.79	15.30	15.30	15.80	16.36	11.06	11.57	11.57	12.06	12.62