

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931316

Luminaire Tested: DFN2DS-TR2F0-060DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-060DS950-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4819.5 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931316

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931316

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5227	5227	5227
5°	5247	5161	5190
10°	5206	5077	5034
15°	5147	4926	4784
20°	5064	4712	4475
25°	4979	4467	4175
30°	4861	4216	3790
35°	4747	3944	3453
40°	4631	3661	3063
45°	4496	3345	2709
50°	4357	3025	2363
55°	4214	2680	2029
60°	4049	2318	1684
65°	3862	1947	1533
70°	3637	1604	1410
75°	3363	1462	1317
80°	2968	1306	1200
85°	2331	1031	1031

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4496 cd/sqm

TEST NUMBER: P931316

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.6	4.6
10°-20°	602.9	12.5
20°-30°	846.5	17.6
30°-40°	922.7	19.1
40°-50°	848.1	17.6
50°-60°	666.0	13.8
60°-70°	433.5	9.0
70°-80°	223.2	4.6
80°-90°	57.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1669.0	34.6
0°-40°	2591.7	53.8
0°-60°	4105.8	85.2
0°-90°	4819.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4819.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2343	2343	2343	2343	2343	
5°	2343	2333	2305	2324	2318	222
15°	2229	2205	2133	2093	2072	628
25°	2023	1955	1815	1728	1697	930
35°	1743	1635	1449	1315	1268	1091
45°	1425	1283	1060	910	859	1101
55°	1084	918	689	562	522	968
65°	732	560	369	297	290	725
75°	390	242	170	155	153	413
85°	91	47	40	40	40	109
90°	0	0	0	0	0	

TEST NUMBER: P931316

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2343.4	2343.4	2343.4	2343.4	2343.4
2.5°	2354.0	2343.4	2320.0	2341.3	2337.1
5°	2343.4	2332.8	2305.1	2324.3	2318.0
7.5°	2324.3	2311.7	2282.0	2290.3	2279.7
10°	2298.8	2284.0	2241.7	2235.2	2222.5
12.5°	2267.1	2248.0	2190.6	2178.0	2154.6
15°	2228.9	2205.4	2133.4	2093.2	2072.0
17.5°	2184.4	2150.3	2061.2	2014.6	1980.7
20°	2133.4	2090.9	1985.0	1932.1	1885.3
22.5°	2078.3	2029.5	1906.4	1834.4	1802.7
25°	2023.2	1955.3	1815.3	1728.5	1696.6
27.5°	1957.6	1885.3	1730.5	1630.8	1582.0
30°	1887.5	1806.7	1637.1	1529.1	1471.7
32.5°	1819.6	1722.0	1548.3	1420.9	1367.8
35°	1743.3	1635.1	1448.6	1314.9	1268.1
37.5°	1669.1	1552.3	1355.2	1208.7	1155.8
40°	1590.5	1463.4	1257.5	1107.0	1051.9
42.5°	1510.0	1374.3	1160.1	1003.0	950.2
45°	1425.2	1282.9	1060.5	909.7	858.8
47.5°	1344.6	1194.1	965.0	814.3	767.7
50°	1255.5	1105.0	871.7	725.2	680.9
52.5°	1168.4	1009.4	782.6	642.6	602.3
55°	1083.6	918.3	689.2	562.1	521.7
57.5°	996.8	827.1	606.6	487.8	453.8
60°	907.7	738.0	519.6	411.5	377.5
62.5°	820.8	651.2	445.3	343.6	326.7
65°	731.7	559.8	369.0	297.0	290.5
67.5°	646.9	475.0	297.0	260.8	254.5
70°	557.7	392.4	245.9	224.8	216.2
72.5°	473.0	315.9	205.6	188.8	184.5
75°	390.2	241.6	169.6	154.8	152.8
77.5°	307.6	171.7	133.6	125.1	120.9
80°	231.1	123.0	101.7	93.4	93.4
82.5°	161.1	82.8	69.9	65.7	65.7
85°	91.1	46.6	40.3	40.3	40.3
87.5°	34.0	16.9	16.9	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931316

CATALOG NUMBER: DFN2DS-TR2F0-060DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.98	18.50	17.35	18.82	19.13	12.94	14.46	13.31	14.78	15.09
	3H	18.75	20.11	19.12	20.44	20.80	14.21	15.57	14.58	15.90	16.26
	4H	19.41	20.69	19.81	21.04	21.42	14.71	15.99	15.11	16.34	16.72
	6H	19.90	21.08	20.31	21.45	21.84	15.09	16.27	15.50	16.64	17.03
	8H	20.07	21.19	20.49	21.58	21.98	15.21	16.34	15.64	16.73	17.13
	12H	20.17	21.25	20.60	21.63	22.06	15.30	16.37	15.73	16.76	17.18
4H	2H	17.08	18.37	17.48	18.71	19.09	13.64	14.92	14.04	15.27	15.64
	3H	19.02	20.08	19.43	20.48	20.88	15.08	16.14	15.49	16.54	16.94
	4H	19.77	20.72	20.20	21.14	21.58	15.68	16.64	16.11	17.05	17.49
	6H	20.36	21.19	20.82	21.63	22.09	16.17	17.00	16.63	17.44	17.90
	8H	20.57	21.35	21.04	21.79	22.26	16.33	17.11	16.79	17.55	18.02
	12H	20.73	21.42	21.21	21.90	22.37	16.45	17.14	16.93	17.62	18.09
8H	4H	19.79	20.57	20.25	21.01	21.48	16.03	16.81	16.50	17.25	17.72
	6H	20.43	21.07	20.93	21.56	22.04	16.62	17.26	17.12	17.75	18.23
	8H	20.68	21.26	21.19	21.77	22.25	16.84	17.42	17.35	17.93	18.42
	12H	20.88	21.39	21.39	21.89	22.45	17.02	17.53	17.53	18.02	18.59
12H	4H	19.78	20.47	20.26	20.95	21.42	16.08	16.77	16.56	17.25	17.72
	6H	20.41	20.99	20.92	21.50	21.99	16.68	17.26	17.20	17.77	18.26
	8H	20.69	21.20	21.20	21.70	22.26	16.96	17.47	17.47	17.96	18.52