

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930096

Luminaire Tested: DFN2DS-HX2F0-050DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-050DS835-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4250.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930096

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930096

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4869	4869	4869
5°	4888	4808	4835
10°	4850	4729	4689
15°	4794	4589	4457
20°	4717	4389	4168
25°	4638	4162	3889
30°	4528	3928	3531
35°	4422	3674	3217
40°	4314	3411	2853
45°	4188	3116	2523
50°	4058	2818	2201
55°	3925	2496	1890
60°	3772	2159	1569
65°	3597	1814	1428
70°	3389	1494	1314
75°	3132	1362	1226
80°	2765	1217	1117
85°	2174	960	960

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4188 cd/sqm

TEST NUMBER: P930096

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	4.6
10°-20°	531.7	12.5
20°-30°	746.5	17.6
30°-40°	813.7	19.1
40°-50°	747.9	17.6
50°-60°	587.3	13.8
60°-70°	382.3	9.0
70°-80°	196.8	4.6
80°-90°	50.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.8	34.6
0°-40°	2285.5	53.8
0°-60°	3620.7	85.2
0°-90°	4250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4250.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	96
90°	0	0	0	0	0	

TEST NUMBER: P930096

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930096

CATALOG NUMBER: DFN2DS-HX2F0-050DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.73	18.26	17.10	18.57	18.88	12.70	14.22	13.06	14.53	14.84
	3H	18.50	19.86	18.88	20.19	20.55	13.96	15.33	14.34	15.65	16.02
	4H	19.17	20.45	19.57	20.80	21.17	14.46	15.74	14.86	16.09	16.47
	6H	19.65	20.84	20.07	21.20	21.60	14.84	16.03	15.25	16.39	16.78
	8H	19.82	20.95	20.25	21.34	21.74	14.97	16.09	15.39	16.48	16.88
	12H	19.92	21.00	20.35	21.38	21.81	15.05	16.13	15.48	16.51	16.94
4H	2H	16.84	18.12	17.24	18.47	18.85	13.39	14.67	13.79	15.02	15.40
	3H	18.77	19.83	19.18	20.23	20.64	14.83	15.90	15.24	16.30	16.70
	4H	19.52	20.48	19.95	20.89	21.33	15.43	16.39	15.87	16.81	17.24
	6H	20.11	20.94	20.57	21.39	21.85	15.92	16.75	16.38	17.20	17.66
	8H	20.33	21.10	20.79	21.55	22.02	16.08	16.86	16.55	17.30	17.77
	12H	20.48	21.18	20.96	21.65	22.12	16.20	16.89	16.68	17.37	17.84
8H	4H	19.55	20.32	20.01	20.77	21.23	15.79	16.56	16.25	17.01	17.48
	6H	20.18	20.83	20.68	21.32	21.79	16.37	17.02	16.87	17.51	17.98
	8H	20.43	21.01	20.95	21.52	22.01	16.59	17.17	17.11	17.68	18.17
	12H	20.64	21.15	21.15	21.64	22.20	16.77	17.28	17.28	17.77	18.34
12H	4H	19.53	20.22	20.01	20.70	21.17	15.83	16.52	16.31	17.00	17.47
	6H	20.16	20.74	20.68	21.25	21.74	16.44	17.01	16.95	17.52	18.01
	8H	20.45	20.96	20.96	21.45	22.01	16.71	17.22	17.22	17.71	18.28