

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931443

Luminaire Tested: DFN2DS-TR4F0-040DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931443
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-040DS830-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3730.3 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 38.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931443

CATALOG NUMBER: DFN2DS-TR4F0-040DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931443

CATALOG NUMBER: DFN2DS-TR4F0-040DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1165	1165	1165
5°	1169	1152	1159
10°	1162	1141	1146
15°	1148	1126	1125
20°	1127	1104	1103
25°	1107	1076	1076
30°	1081	1051	1042
35°	1057	1021	1006
40°	1026	991	972
45°	996	961	938
50°	964	930	897
55°	930	894	861
60°	892	851	820
65°	851	808	771
70°	799	756	721
75°	727	696	680
80°	645	625	593
85°	526	501	450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 996 cd/sqm

TEST NUMBER: P931443

CATALOG NUMBER: DFN2DS-TR4F0-040DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	3.7
10°-20°	388.3	10.4
20°-30°	570.6	15.3
30°-40°	662.7	17.8
40°-50°	661.9	17.7
50°-60°	577.1	15.5
60°-70°	426.6	11.4
70°-80°	241.4	6.5
80°-90°	63.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1096.8	29.4
0°-40°	1759.5	47.2
0°-60°	2998.6	80.4
0°-90°	3730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3730.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1461	1445	1456	1454	139
15°	1396	1387	1369	1375	1368	393
25°	1263	1252	1228	1231	1228	581
35°	1090	1076	1053	1045	1038	681
45°	887	877	856	840	835	684
55°	671	663	646	629	622	600
65°	453	444	430	417	410	447
75°	237	234	227	218	221	253
85°	58	56	55	51	49	68
90°	0	0	0	0	0	

TEST NUMBER: P931443

CATALOG NUMBER: DFN2DS-TR4F0-040DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1466.1	1466.1	1466.1	1466.1	1466.1
2.5°	1474.7	1467.6	1452.1	1466.1	1463.5
5°	1466.1	1460.6	1445.0	1456.2	1453.6
7.5°	1456.2	1447.9	1432.3	1443.7	1440.9
10°	1440.9	1431.0	1414.1	1425.3	1421.1
12.5°	1419.6	1411.2	1394.3	1401.4	1398.5
15°	1395.7	1387.3	1368.9	1374.6	1367.6
17.5°	1366.1	1357.7	1339.3	1346.3	1339.3
20°	1333.6	1325.2	1305.5	1309.7	1304.2
22.5°	1301.3	1288.6	1270.2	1270.2	1267.4
25°	1263.1	1251.9	1228.0	1230.7	1228.0
27.5°	1220.8	1210.9	1192.8	1188.5	1181.6
30°	1178.6	1167.3	1146.2	1142.0	1136.3
32.5°	1133.5	1125.1	1102.5	1094.0	1088.3
35°	1089.8	1075.8	1053.2	1044.7	1037.6
37.5°	1040.4	1027.7	1005.1	995.3	988.3
40°	989.8	978.4	955.8	943.2	937.6
42.5°	940.4	929.0	906.6	892.4	884.0
45°	886.8	877.0	855.7	840.4	834.6
47.5°	834.6	824.7	802.2	786.7	778.3
50°	779.6	772.5	752.8	733.1	726.0
52.5°	726.0	716.2	697.9	682.4	672.5
55°	671.2	662.6	645.7	628.8	621.8
57.5°	616.1	609.1	590.6	573.8	568.1
60°	561.1	555.5	535.8	520.3	516.0
62.5°	507.5	497.7	483.6	469.5	463.8
65°	452.6	444.1	430.0	417.3	410.3
67.5°	396.2	389.0	376.5	366.6	361.0
70°	344.0	338.4	325.6	315.8	310.2
72.5°	290.5	284.8	277.8	267.9	263.7
75°	236.8	234.1	226.9	218.5	221.4
77.5°	188.9	183.2	180.4	176.2	172.0
80°	141.0	139.5	136.7	132.5	129.7
82.5°	95.9	95.9	94.6	88.8	88.8
85°	57.7	56.4	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.5	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931443

CATALOG NUMBER: DFN2DS-TR4F0-040DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.81	13.42	12.18	13.74	14.05	11.37	12.98	11.73	13.29	13.61
	3H	13.56	15.02	13.94	15.34	15.70	13.07	14.53	13.45	14.85	15.21
	4H	14.21	15.58	14.61	15.93	16.30	13.71	15.08	14.11	15.43	15.81
	6H	14.68	15.95	15.09	16.31	16.70	14.18	15.45	14.59	15.81	16.20
	8H	14.82	16.03	15.25	16.42	16.82	14.32	15.53	14.74	15.92	16.32
	12H	14.91	16.07	15.34	16.45	16.88	14.40	15.56	14.83	15.94	16.37
4H	2H	12.37	13.74	12.77	14.09	14.47	12.02	13.39	12.42	13.74	14.11
	3H	14.35	15.49	14.76	15.89	16.29	13.94	15.09	14.35	15.49	15.89
	4H	15.12	16.16	15.56	16.57	17.01	14.70	15.74	15.13	16.15	16.59
	6H	15.72	16.63	16.18	17.07	17.52	15.29	16.19	15.74	16.63	17.09
	8H	15.91	16.76	16.37	17.20	17.66	15.47	16.32	15.93	16.76	17.23
	12H	16.04	16.80	16.52	17.28	17.75	15.59	16.35	16.07	16.83	17.30
8H	4H	15.40	16.24	15.86	16.69	17.15	15.02	15.87	15.48	16.31	16.78
	6H	16.11	16.82	16.61	17.30	17.78	15.73	16.43	16.22	16.92	17.40
	8H	16.37	17.00	16.88	17.51	17.99	15.98	16.61	16.49	17.12	17.60
	12H	16.57	17.13	17.08	17.62	18.18	16.16	16.72	16.66	17.21	17.77
12H	4H	15.42	16.18	15.90	16.66	17.13	15.06	15.82	15.54	16.30	16.76
	6H	16.16	16.79	16.67	17.30	17.78	15.79	16.42	16.30	16.93	17.41
	8H	16.47	17.03	16.98	17.52	18.08	16.09	16.65	16.60	17.14	17.70