

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930043

Luminaire Tested: DFN2DS-HX2F0-020DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-020DS840-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1982.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 17.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930043

CATALOG NUMBER: DFN2DS-HX2F0-020DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930043

CATALOG NUMBER: DFN2DS-HX2F0-020DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1835	1835	1835
5°	1842	1816	1827
10°	1832	1798	1807
15°	1809	1774	1772
20°	1777	1739	1737
25°	1745	1696	1696
30°	1704	1657	1642
35°	1666	1610	1586
40°	1617	1562	1532
45°	1570	1515	1477
50°	1518	1466	1414
55°	1465	1409	1357
60°	1405	1342	1292
65°	1340	1274	1215
70°	1259	1192	1136
75°	1145	1097	1071
80°	1018	986	935
85°	827	789	708

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1570 cd/sqm

TEST NUMBER: P930043

CATALOG NUMBER: DFN2DS-HX2F0-020DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	3.7
10°-20°	206.3	10.4
20°-30°	303.2	15.3
30°-40°	352.1	17.8
40°-50°	351.7	17.7
50°-60°	306.6	15.5
60°-70°	226.7	11.4
70°-80°	128.3	6.5
80°-90°	33.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.8	29.4
0°-40°	934.9	47.2
0°-60°	1593.2	80.4
0°-90°	1982.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1982.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	768	774	772	74
15°	742	737	727	730	727	209
25°	671	665	652	654	652	309
35°	579	572	560	555	551	362
45°	471	466	455	446	443	364
55°	357	352	343	334	330	319
65°	240	236	228	222	218	238
75°	126	124	120	116	118	134
85°	31	30	29	27	26	36
90°	0	0	0	0	0	

TEST NUMBER: P930043

CATALOG NUMBER: DFN2DS-HX2F0-020DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	779.0	779.0	779.0	779.0	779.0
2.5°	783.5	779.8	771.5	779.0	777.6
5°	779.0	776.1	767.8	773.8	772.3
7.5°	773.8	769.3	761.1	767.1	765.6
10°	765.6	760.4	751.4	757.3	755.1
12.5°	754.3	749.8	740.8	744.5	743.0
15°	741.5	737.1	727.3	730.3	726.6
17.5°	725.8	721.4	711.6	715.3	711.6
20°	708.6	704.1	693.6	695.9	692.9
22.5°	691.4	684.7	674.9	674.9	673.4
25°	671.2	665.2	652.5	653.9	652.5
27.5°	648.6	643.4	633.7	631.5	627.7
30°	626.2	620.2	609.0	606.8	603.7
32.5°	602.2	597.8	585.8	581.3	578.3
35°	579.1	571.6	559.6	555.1	551.3
37.5°	552.9	546.0	534.0	528.8	525.0
40°	525.8	519.8	507.8	501.2	498.1
42.5°	499.6	493.6	481.7	474.2	469.7
45°	471.2	466.0	454.7	446.4	443.4
47.5°	443.4	438.2	426.2	417.9	413.5
50°	414.2	410.5	400.0	389.5	385.8
52.5°	385.8	380.5	370.8	362.6	357.4
55°	356.6	352.1	343.0	334.1	330.3
57.5°	327.3	323.6	313.8	304.9	301.8
60°	298.1	295.2	284.7	276.4	274.2
62.5°	269.7	264.4	257.0	249.4	246.4
65°	240.4	235.9	228.5	221.7	218.0
67.5°	210.5	206.7	200.0	194.8	191.8
70°	182.8	179.8	173.0	167.8	164.9
72.5°	154.4	151.4	147.5	142.3	140.1
75°	125.8	124.4	120.5	116.1	117.6
77.5°	100.4	97.4	95.8	93.6	91.4
80°	75.0	74.2	72.7	70.4	68.9
82.5°	51.0	51.0	50.3	47.2	47.2
85°	30.6	29.9	29.2	26.9	26.2
87.5°	13.5	12.0	10.5	8.3	7.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930043

CATALOG NUMBER: DFN2DS-HX2F0-020DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.39	15.00	13.76	15.32	15.63	12.95	14.56	13.31	14.87	15.19
	3H	15.14	16.60	15.52	16.92	17.28	14.65	16.11	15.03	16.43	16.79
	4H	15.79	17.16	16.19	17.51	17.88	15.29	16.66	15.69	17.01	17.39
	6H	16.26	17.53	16.67	17.89	18.28	15.76	17.03	16.17	17.39	17.78
	8H	16.40	17.61	16.83	18.00	18.40	15.90	17.11	16.32	17.50	17.90
	12H	16.49	17.65	16.92	18.03	18.46	15.98	17.14	16.41	17.52	17.95
4H	2H	13.95	15.32	14.35	15.67	16.05	13.60	14.97	14.00	15.32	15.69
	3H	15.93	17.07	16.34	17.47	17.87	15.52	16.67	15.93	17.07	17.47
	4H	16.70	17.74	17.14	18.15	18.59	16.28	17.32	16.71	17.73	18.17
	6H	17.30	18.21	17.76	18.65	19.10	16.87	17.77	17.32	18.21	18.67
	8H	17.49	18.34	17.95	18.78	19.25	17.05	17.90	17.51	18.34	18.81
	12H	17.62	18.38	18.10	18.86	19.33	17.17	17.93	17.65	18.41	18.88
8H	4H	16.98	17.82	17.44	18.27	18.73	16.60	17.45	17.06	17.89	18.36
	6H	17.69	18.40	18.19	18.88	19.36	17.31	18.01	17.80	18.50	18.98
	8H	17.95	18.58	18.46	19.09	19.58	17.56	18.19	18.07	18.70	19.18
	12H	18.15	18.71	18.66	19.20	19.76	17.74	18.30	18.24	18.79	19.35
12H	4H	17.00	17.76	17.48	18.24	18.71	16.64	17.40	17.12	17.88	18.34
	6H	17.74	18.37	18.25	18.88	19.36	17.37	18.00	17.88	18.51	18.99
	8H	18.05	18.61	18.56	19.10	19.66	17.67	18.23	18.18	18.72	19.28