

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930073

Luminaire Tested: DFN2DS-HX2F0-030DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-030DS950-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2806.7 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930073
CATALOG NUMBER: DFN2DS-HX2F0-030DS950-FLL

Luminous Intensity Polar Plot





TEST NUMBER: P930073

CATALOG NUMBER: DFN2DS-HX2F0-030DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	73	73	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	62	62	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	54	54	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	47	47	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	41	41	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	37	37	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	27	27	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2599	2599	2599
5°	2609	2571	2587
10°	2594	2546	2558
15°	2561	2512	2510
20°	2516	2463	2460
25°	2471	2402	2402
30°	2413	2346	2326
35°	2359	2279	2246
40°	2290	2212	2170
45°	2224	2145	2093
50°	2150	2076	2002
55°	2074	1996	1922
60°	1989	1900	1830
65°	1899	1804	1721
70°	1783	1688	1608
75°	1621	1555	1517
80°	1440	1395	1324
85°	1176	1119	1003

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2224 cd/sqm



TEST NUMBER: P930073

CATALOG NUMBER: DFN2DS-HX2F0-030DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.8	3.7
10°-20°	292.1	10.4
20°-30°	429.3	15.3
30°-40°	498.6	17.8
40°-50°	498.0	17.7
50°-60°	434.2	15.5
60°-70°	321.0	11.4
70°-80°	181.6	6.5
80°-90°	47.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	825.3	29.4
0°-40°	1323.9	47.2
0°-60°	2256.1	80.4
0°-90°	2806.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2806.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1103	1103	1103	1103	1103	
5°	1103	1099	1087	1096	1094	105
15°	1050	1044	1030	1034	1029	296
25°	950	942	924	926	924	437
35°	820	809	792	786	781	512
45°	667	660	644	632	628	515
55°	505	499	486	473	468	451
65°	341	334	324	314	309	337
75°	178	176	171	164	167	190
85°	44	42	41	38	37	51
90°	0	0	0	0	0	



TEST NUMBER: P930073

CATALOG NUMBER: DFN2DS-HX2F0-030DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1103.1	1103.1	1103.1	1103.1	1103.1
2.5°	1109.5	1104.2	1092.5	1103.1	1101.1
5°	1103.1	1098.9	1087.2	1095.7	1093.6
7.5°	1095.7	1089.4	1077.7	1086.3	1084.1
10°	1084.1	1076.6	1064.0	1072.4	1069.3
12.5°	1068.1	1061.8	1049.1	1054.3	1052.3
15°	1050.1	1043.8	1030.0	1034.2	1028.9
17.5°	1027.8	1021.5	1007.7	1012.9	1007.7
20°	1003.4	997.1	982.2	985.4	981.2
22.5°	979.1	969.6	955.7	955.7	953.5
25°	950.4	942.0	923.9	926.0	923.9
27.5°	918.5	911.1	897.4	894.3	889.0
30°	886.8	878.3	862.4	859.2	854.9
32.5°	852.9	846.5	829.5	823.1	818.8
35°	820.0	809.4	792.4	786.0	780.7
37.5°	782.8	773.3	756.3	748.8	743.5
40°	744.7	736.2	719.1	709.7	705.4
42.5°	707.5	699.0	682.1	671.4	665.1
45°	667.3	659.8	643.8	632.2	628.0
47.5°	628.0	620.6	603.6	591.9	585.5
50°	586.6	581.3	566.4	551.6	546.3
52.5°	546.3	538.8	525.1	513.4	506.0
55°	505.0	498.6	485.8	473.2	467.9
57.5°	463.5	458.2	444.4	431.7	427.4
60°	422.1	418.0	403.1	391.4	388.3
62.5°	381.9	374.4	363.8	353.2	349.0
65°	340.6	334.2	323.6	314.0	308.7
67.5°	298.1	292.8	283.2	275.8	271.6
70°	258.8	254.6	245.0	237.6	233.4
72.5°	218.6	214.2	208.9	201.6	198.4
75°	178.1	176.1	170.8	164.4	166.6
77.5°	142.1	137.9	135.7	132.6	129.5
80°	106.1	105.0	102.8	99.7	97.6
82.5°	72.1	72.1	71.2	66.8	66.8
85°	43.5	42.4	41.4	38.2	37.1
87.5°	19.1	17.0	14.8	11.7	10.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930073
 CATALOG NUMBER: DFN2DS-HX2F0-030DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.60	16.21	14.97	16.53	16.84	14.16	15.77	14.52	16.08	16.40
	3H	16.35	17.81	16.73	18.13	18.49	15.86	17.31	16.24	17.64	18.00
	4H	17.00	18.37	17.40	18.71	19.09	16.50	17.87	16.90	18.22	18.60
	6H	17.47	18.73	17.88	19.10	19.49	16.97	18.23	17.38	18.60	18.99
	8H	17.61	18.82	18.03	19.21	19.61	17.11	18.32	17.53	18.71	19.11
	12H	17.70	18.86	18.13	19.24	19.67	17.19	18.35	17.62	18.73	19.16
4H	2H	15.16	16.53	15.56	16.88	17.25	14.81	16.18	15.21	16.53	16.90
	3H	17.14	18.28	17.55	18.68	19.08	16.73	17.88	17.14	18.27	18.67
	4H	17.91	18.95	18.34	19.36	19.80	17.49	18.53	17.92	18.94	19.38
	6H	18.51	19.41	18.96	19.85	20.31	18.08	18.98	18.53	19.42	19.88
	8H	18.70	19.55	19.16	19.99	20.45	18.26	19.11	18.72	19.55	20.02
	12H	18.83	19.59	19.31	20.07	20.54	18.38	19.14	18.86	19.61	20.08
8H	4H	18.19	19.03	18.65	19.48	19.94	17.81	18.66	18.27	19.10	19.57
	6H	18.90	19.60	19.39	20.09	20.57	18.52	19.22	19.01	19.71	20.19
	8H	19.16	19.79	19.67	20.30	20.78	18.77	19.40	19.28	19.91	20.39
	12H	19.36	19.92	19.87	20.41	20.97	18.95	19.50	19.45	20.00	20.56
12H	4H	18.21	18.97	18.69	19.45	19.92	17.85	18.61	18.33	19.08	19.55
	6H	18.95	19.58	19.46	20.08	20.57	18.58	19.21	19.09	19.72	20.20
	8H	19.26	19.82	19.77	20.31	20.87	18.88	19.44	19.39	19.93	20.49