

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930203

Luminaire Tested: DFN2DS-HX3F0-070DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930203
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS835-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930203

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930203

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3155	3155	3155
5°	3167	3122	3140
10°	3149	3090	3105
15°	3109	3050	3047
20°	3054	2990	2987
25°	2999	2916	2916
30°	2929	2848	2824
35°	2863	2767	2726
40°	2780	2685	2634
45°	2699	2604	2540
50°	2610	2520	2431
55°	2518	2423	2333
60°	2415	2306	2221
65°	2305	2190	2089
70°	2164	2049	1952
75°	1969	1886	1841
80°	1748	1694	1607
85°	1426	1360	1219

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2699 cd/sqm

TEST NUMBER: P930203

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	3.7
10°-20°	721.3	10.4
20°-30°	1060.0	15.3
30°-40°	1231.1	17.8
40°-50°	1229.6	17.7
50°-60°	1072.2	15.5
60°-70°	792.6	11.4
70°-80°	448.4	6.5
80°-90°	118.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2037.7	29.4
0°-40°	3268.8	47.2
0°-60°	5570.6	80.4
0°-90°	6930.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	126
90°	0	0	0	0	0	

TEST NUMBER: P930203

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930203

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.27	16.89	15.64	17.20	17.51	14.83	16.44	15.20	16.75	17.07
	3H	17.02	18.48	17.40	18.81	19.17	16.53	17.99	16.91	18.31	18.68
	4H	17.67	19.04	18.07	19.39	19.76	17.18	18.55	17.57	18.89	19.27
	6H	18.14	19.41	18.55	19.77	20.16	17.64	18.91	18.05	19.27	19.66
	8H	18.28	19.49	18.71	19.88	20.28	17.78	18.99	18.21	19.38	19.78
	12H	18.37	19.53	18.80	19.92	20.34	17.86	19.02	18.29	19.40	19.83
4H	2H	15.84	17.20	16.23	17.55	17.93	15.48	16.85	15.88	17.20	17.58
	3H	17.81	18.96	18.22	19.35	19.75	17.40	18.55	17.81	18.95	19.35
	4H	18.59	19.62	19.02	20.04	20.47	18.16	19.20	18.59	19.61	20.05
	6H	19.18	20.09	19.64	20.53	20.99	18.75	19.66	19.21	20.10	20.55
	8H	19.37	20.22	19.83	20.66	21.13	18.93	19.78	19.40	20.22	20.69
	12H	19.50	20.26	19.98	20.74	21.21	19.05	19.81	19.53	20.29	20.76
8H	4H	18.86	19.71	19.32	20.15	20.61	18.49	19.33	18.95	19.77	20.24
	6H	19.57	20.28	20.07	20.77	21.24	19.19	19.90	19.69	20.38	20.86
	8H	19.83	20.46	20.34	20.97	21.46	19.44	20.07	19.95	20.58	21.07
	12H	20.03	20.59	20.54	21.08	21.64	19.62	20.18	20.13	20.67	21.23
12H	4H	18.89	19.65	19.37	20.12	20.59	18.52	19.28	19.00	19.76	20.23
	6H	19.62	20.25	20.13	20.76	21.24	19.25	19.88	19.76	20.39	20.88
	8H	19.93	20.49	20.44	20.98	21.54	19.56	20.11	20.06	20.60	21.17