

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930192

Luminaire Tested: DFN2DS-HX3F0-060DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-060DS927-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4039.2 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 61.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930192
CATALOG NUMBER: DFN2DS-HX3F0-060DS927-RL

Luminous Intensity Polar Plot





TEST NUMBER: P930192

CATALOG NUMBER: DFN2DS-HX3F0-060DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2275	2275	2275
5°	2284	2246	2259
10°	2266	2210	2191
15°	2240	2144	2082
20°	2204	2051	1948
25°	2167	1944	1817
30°	2116	1835	1650
35°	2066	1717	1503
40°	2016	1594	1333
45°	1957	1456	1179
50°	1896	1316	1028
55°	1834	1166	883
60°	1762	1009	733
65°	1681	848	667
70°	1583	698	614
75°	1463	636	573
80°	1291	568	522
85°	1014	448	448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1957 cd/sqm



TEST NUMBER: P930192
 CATALOG NUMBER: DFN2DS-HX3F0-060DS927-RL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	4.6
10°-20°	505.3	12.5
20°-30°	709.4	17.6
30°-40°	773.3	19.1
40°-50°	710.8	17.6
50°-60°	558.2	13.8
60°-70°	363.3	9.0
70°-80°	187.0	4.6
80°-90°	47.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1398.8	34.6
0°-40°	2172.1	53.8
0°-60°	3441.1	85.2
0°-90°	4039.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4039.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1955	1932	1948	1943	186
15°	1868	1848	1788	1754	1736	526
25°	1696	1639	1521	1449	1422	780
35°	1461	1370	1214	1102	1063	914
45°	1194	1075	889	762	720	922
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	202	142	130	128	346
85°	76	39	34	34	34	92
90°	0	0	0	0	0	



TEST NUMBER: P930192

CATALOG NUMBER: DFN2DS-HX3F0-060DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.0	1964.0	1964.0	1964.0	1964.0
2.5°	1972.9	1964.0	1944.4	1962.3	1958.7
5°	1964.0	1955.1	1931.9	1948.0	1942.7
7.5°	1948.0	1937.4	1912.5	1919.5	1910.6
10°	1926.6	1914.2	1878.8	1873.3	1862.7
12.5°	1900.1	1884.0	1835.9	1825.4	1805.8
15°	1868.0	1848.4	1788.0	1754.3	1736.5
17.5°	1830.7	1802.2	1727.5	1688.5	1660.0
20°	1788.0	1752.4	1663.6	1619.2	1580.0
22.5°	1741.8	1700.9	1597.8	1537.4	1510.8
25°	1695.7	1638.7	1521.4	1448.6	1421.9
27.5°	1640.6	1580.0	1450.3	1366.8	1325.9
30°	1581.9	1514.2	1372.1	1281.5	1233.5
32.5°	1525.0	1443.2	1297.6	1190.9	1146.3
35°	1461.1	1370.4	1214.1	1102.0	1062.8
37.5°	1398.8	1300.9	1135.8	1013.0	968.7
40°	1333.0	1226.5	1053.9	927.7	881.6
42.5°	1265.5	1151.8	972.3	840.6	796.4
45°	1194.4	1075.2	888.8	762.4	719.8
47.5°	1126.9	1000.8	808.8	682.5	643.4
50°	1052.3	926.1	730.5	607.8	570.6
52.5°	979.2	845.9	655.9	538.6	504.8
55°	908.2	769.6	577.6	471.1	437.3
57.5°	835.4	693.2	508.4	408.8	380.3
60°	760.7	618.6	435.4	344.9	316.4
62.5°	687.9	545.8	373.2	288.0	273.8
65°	613.2	469.2	309.3	248.9	243.5
67.5°	542.1	398.1	248.9	218.6	213.3
70°	467.4	328.8	206.1	188.4	181.2
72.5°	396.4	264.8	172.3	158.2	154.6
75°	327.0	202.5	142.2	129.7	128.1
77.5°	257.8	143.9	112.0	104.9	101.3
80°	193.6	103.1	85.2	78.2	78.2
82.5°	135.0	69.4	58.6	55.0	55.0
85°	76.3	39.0	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930192
 CATALOG NUMBER: DFN2DS-HX3F0-060DS927-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.09	15.61	14.46	15.93	16.24	10.05	11.57	10.42	11.89	12.20
	3H	15.86	17.22	16.23	17.55	17.91	11.32	12.68	11.69	13.01	13.37
	4H	16.52	17.80	16.92	18.15	18.53	11.82	13.10	12.22	13.45	13.83
	6H	17.01	18.19	17.42	18.56	18.95	12.20	13.38	12.61	13.75	14.14
	8H	17.18	18.30	17.60	18.69	19.09	12.32	13.45	12.75	13.84	14.24
	12H	17.28	18.36	17.71	18.74	19.17	12.40	13.48	12.83	13.86	14.29
4H	2H	14.19	15.48	14.59	15.82	16.20	10.75	12.03	11.15	12.38	12.75
	3H	16.13	17.19	16.54	17.59	17.99	12.19	13.25	12.60	13.65	14.05
	4H	16.88	17.83	17.31	18.25	18.69	12.79	13.75	13.22	14.16	14.60
	6H	17.47	18.30	17.93	18.74	19.20	13.28	14.11	13.73	14.55	15.01
	8H	17.68	18.46	18.15	18.90	19.37	13.44	14.22	13.90	14.66	15.13
	12H	17.84	18.53	18.32	19.01	19.48	13.56	14.25	14.04	14.73	15.20
8H	4H	16.90	17.68	17.36	18.12	18.59	13.14	13.92	13.61	14.36	14.83
	6H	17.54	18.18	18.04	18.67	19.15	13.73	14.37	14.23	14.86	15.34
	8H	17.79	18.37	18.30	18.88	19.36	13.95	14.53	14.46	15.04	15.52
	12H	17.99	18.50	18.50	18.99	19.56	14.13	14.64	14.64	15.13	15.70
12H	4H	16.89	17.58	17.37	18.06	18.53	13.19	13.88	13.67	14.36	14.83
	6H	17.52	18.10	18.03	18.61	19.09	13.79	14.37	14.31	14.88	15.37
	8H	17.80	18.31	18.31	18.81	19.37	14.07	14.58	14.57	15.07	15.63