

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931481

Luminaire Tested: DFN2DS-TR4F0-060DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-060DS835-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5940.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 59.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931481

CATALOG NUMBER: DFN2DS-TR4F0-060DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931481

CATALOG NUMBER: DFN2DS-TR4F0-060DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1855	1855	1855
5°	1862	1835	1846
10°	1851	1816	1825
15°	1828	1793	1791
20°	1795	1757	1756
25°	1763	1714	1714
30°	1722	1674	1660
35°	1683	1626	1602
40°	1634	1578	1548
45°	1587	1531	1493
50°	1534	1482	1429
55°	1480	1424	1371
60°	1419	1356	1306
65°	1355	1287	1228
70°	1272	1204	1147
75°	1157	1109	1082
80°	1028	996	945
85°	838	798	716

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1587 cd/sqm

TEST NUMBER: P931481

CATALOG NUMBER: DFN2DS-TR4F0-060DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	3.7
10°-20°	618.3	10.4
20°-30°	908.6	15.3
30°-40°	1055.3	17.8
40°-50°	1054.0	17.7
50°-60°	919.0	15.5
60°-70°	679.4	11.4
70°-80°	384.4	6.5
80°-90°	101.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.6	29.4
0°-40°	2801.8	47.2
0°-60°	4774.8	80.4
0°-90°	5940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5940.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P931481

CATALOG NUMBER: DFN2DS-TR4F0-060DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931481

CATALOG NUMBER: DFN2DS-TR4F0-060DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.43	15.04	13.79	15.35	15.67	12.98	14.60	13.35	14.91	15.22
	3H	15.18	16.63	15.56	16.96	17.32	14.69	16.14	15.06	16.47	16.83
	4H	15.83	17.19	16.22	17.54	17.92	15.33	16.70	15.73	17.05	17.42
	6H	16.29	17.56	16.71	17.93	18.32	15.79	17.06	16.20	17.43	17.82
	8H	16.44	17.65	16.86	18.04	18.44	15.93	17.15	16.36	17.53	17.93
	12H	16.53	17.69	16.96	18.07	18.50	16.02	17.18	16.45	17.56	17.99
4H	2H	13.99	15.36	14.39	15.71	16.08	13.64	15.01	14.03	15.35	15.73
	3H	15.96	17.11	16.37	17.51	17.91	15.56	16.70	15.97	17.10	17.50
	4H	16.74	17.78	17.17	18.19	18.63	16.32	17.35	16.75	17.77	18.20
	6H	17.34	18.24	17.79	18.68	19.14	16.91	17.81	17.36	18.25	18.71
	8H	17.53	18.37	17.99	18.82	19.28	17.09	17.94	17.55	18.38	18.84
	12H	17.66	18.42	18.14	18.89	19.36	17.21	17.97	17.69	18.44	18.91
8H	4H	17.01	17.86	17.47	18.30	18.77	16.64	17.49	17.10	17.93	18.39
	6H	17.73	18.43	18.22	18.92	19.40	17.35	18.05	17.84	18.54	19.01
	8H	17.99	18.62	18.50	19.13	19.61	17.60	18.23	18.11	18.73	19.22
	12H	18.19	18.75	18.69	19.24	19.80	17.77	18.33	18.28	18.82	19.38
12H	4H	17.04	17.80	17.52	18.28	18.75	16.68	17.44	17.16	17.91	18.38
	6H	17.77	18.41	18.28	18.91	19.40	17.41	18.04	17.91	18.54	19.03
	8H	18.09	18.65	18.59	19.14	19.70	17.71	18.27	18.22	18.76	19.32