

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930176

Luminaire Tested: DFN2DS-HX3F0-050DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-050DS930-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3463.8 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930176
CATALOG NUMBER: DFN2DS-HX3F0-050DS930-RL

Luminous Intensity Polar Plot





TEST NUMBER: P930176

CATALOG NUMBER: DFN2DS-HX3F0-050DS930-RL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1951	1951	1951
5°	1958	1926	1937
10°	1943	1895	1879
15°	1921	1839	1786
20°	1890	1759	1670
25°	1858	1668	1558
30°	1815	1574	1415
35°	1772	1472	1289
40°	1729	1367	1143
45°	1678	1248	1011
50°	1626	1129	882
55°	1573	1000	757
60°	1511	865	629
65°	1441	727	572
70°	1358	599	526
75°	1255	546	491
80°	1108	488	448
85°	871	384	384

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1678 cd/sqm



TEST NUMBER: P930176
 CATALOG NUMBER: DFN2DS-HX3F0-050DS930-RL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.8	4.6
10°-20°	433.3	12.5
20°-30°	608.4	17.6
30°-40°	663.2	19.1
40°-50°	609.5	17.6
50°-60°	478.7	13.8
60°-70°	311.6	9.0
70°-80°	160.4	4.6
80°-90°	40.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1199.5	34.6
0°-40°	1862.7	53.8
0°-60°	2950.9	85.2
0°-90°	3463.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3463.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1684	1684	1684	1684	1684	
5°	1684	1677	1657	1670	1666	160
15°	1602	1585	1533	1504	1489	451
25°	1454	1405	1305	1242	1219	669
35°	1253	1175	1041	945	911	784
45°	1024	922	762	654	617	791
55°	779	660	495	404	375	696
65°	526	402	265	213	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	79
90°	0	0	0	0	0	



TEST NUMBER: P930176

CATALOG NUMBER: DFN2DS-HX3F0-050DS930-RL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.2	1684.2	1684.2	1684.2	1684.2
2.5°	1691.8	1684.2	1667.4	1682.7	1679.6
5°	1684.2	1676.6	1656.7	1670.4	1665.9
7.5°	1670.4	1661.4	1640.0	1646.1	1638.4
10°	1652.2	1641.5	1611.1	1606.4	1597.3
12.5°	1629.3	1615.7	1574.4	1565.4	1548.5
15°	1601.9	1585.1	1533.3	1504.4	1489.2
17.5°	1569.9	1545.5	1481.4	1447.9	1423.5
20°	1533.3	1502.8	1426.6	1388.6	1354.9
22.5°	1493.7	1458.6	1370.2	1318.4	1295.6
25°	1454.0	1405.2	1304.7	1242.2	1219.2
27.5°	1406.9	1354.9	1243.7	1172.1	1137.0
30°	1356.6	1298.5	1176.6	1098.9	1057.7
32.5°	1307.7	1237.6	1112.7	1021.2	983.1
35°	1252.9	1175.1	1041.1	945.0	911.4
37.5°	1199.5	1115.7	974.0	868.7	830.7
40°	1143.1	1051.8	903.8	795.6	756.0
42.5°	1085.3	987.7	833.7	720.9	682.9
45°	1024.3	922.1	762.1	653.8	617.2
47.5°	966.3	858.2	693.6	585.3	551.8
50°	902.4	794.1	626.5	521.2	489.3
52.5°	839.8	725.4	562.4	461.9	432.9
55°	778.8	659.9	495.3	403.9	375.0
57.5°	716.4	594.5	435.9	350.6	326.2
60°	652.3	530.4	373.4	295.8	271.3
62.5°	589.9	468.0	320.1	246.9	234.8
65°	525.8	402.4	265.2	213.4	208.8
67.5°	464.9	341.4	213.4	187.4	182.9
70°	400.9	282.0	176.8	161.5	155.4
72.5°	339.9	227.1	147.8	135.7	132.6
75°	280.4	173.7	121.9	111.2	109.8
77.5°	221.0	123.4	96.1	89.9	86.8
80°	166.1	88.4	73.1	67.1	67.1
82.5°	115.8	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.4	12.1	12.1	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930176
 CATALOG NUMBER: DFN2DS-HX3F0-050DS930-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.56	15.08	13.92	15.39	15.71	9.52	11.04	9.88	11.35	11.67
	3H	15.32	16.69	15.70	17.02	17.38	10.78	12.15	11.16	12.48	12.84
	4H	15.99	17.27	16.39	17.62	18.00	11.28	12.56	11.68	12.91	13.29
	6H	16.48	17.66	16.89	18.03	18.42	11.66	12.85	12.08	13.21	13.61
	8H	16.64	17.77	17.07	18.16	18.56	11.79	12.92	12.22	13.31	13.71
	12H	16.75	17.82	17.18	18.21	18.64	11.87	12.95	12.30	13.33	13.76
4H	2H	13.66	14.94	14.06	15.29	15.67	10.21	11.49	10.61	11.84	12.22
	3H	15.59	16.66	16.00	17.06	17.46	11.66	12.72	12.07	13.12	13.52
	4H	16.34	17.30	16.78	17.72	18.15	12.25	13.21	12.69	13.63	14.07
	6H	16.94	17.77	17.39	18.21	18.67	12.74	13.57	13.20	14.02	14.48
	8H	17.15	17.93	17.61	18.37	18.84	12.90	13.68	13.37	14.13	14.59
	12H	17.30	18.00	17.79	18.48	18.95	13.02	13.72	13.50	14.19	14.67
8H	4H	16.37	17.15	16.83	17.59	18.06	12.61	13.39	13.07	13.83	14.30
	6H	17.01	17.65	17.50	18.14	18.62	13.20	13.84	13.69	14.33	14.81
	8H	17.26	17.83	17.77	18.34	18.83	13.42	13.99	13.93	14.50	14.99
	12H	17.46	17.97	17.97	18.46	19.03	13.60	14.10	14.10	14.60	15.16
12H	4H	16.35	17.05	16.83	17.53	18.00	12.65	13.35	13.13	13.83	14.30
	6H	16.99	17.56	17.50	18.07	18.56	13.26	13.84	13.77	14.35	14.83
	8H	17.27	17.78	17.78	18.27	18.84	13.53	14.04	14.04	14.53	15.10