

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930214

Luminaire Tested: DFN2DS-HX3F0-070DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS935-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5117.0 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930214
CATALOG NUMBER: DFN2DS-HX3F0-070DS935-RL

Luminous Intensity Polar Plot





TEST NUMBER: P930214

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2882	2882	2882
5°	2893	2846	2862
10°	2871	2799	2776
15°	2838	2716	2638
20°	2792	2598	2467
25°	2745	2463	2302
30°	2681	2325	2090
35°	2617	2175	1904
40°	2554	2019	1689
45°	2479	1844	1494
50°	2402	1668	1303
55°	2323	1478	1119
60°	2233	1278	929
65°	2129	1074	845
70°	2006	884	777
75°	1854	806	726
80°	1637	720	662
85°	1287	568	568

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2479 cd/sqm



TEST NUMBER: P930214

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-RL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.2	4.6
10°-20°	640.1	12.5
20°-30°	898.7	17.6
30°-40°	979.7	19.1
40°-50°	900.4	17.6
50°-60°	707.1	13.8
60°-70°	460.3	9.0
70°-80°	236.9	4.6
80°-90°	60.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1772.1	34.6
0°-40°	2751.7	53.8
0°-60°	4359.3	85.2
0°-90°	5117.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5117.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2488	2488	2488	2488	2488	
5°	2488	2477	2448	2468	2461	236
15°	2366	2342	2265	2222	2200	667
25°	2148	2076	1927	1835	1801	988
35°	1851	1736	1538	1396	1346	1158
45°	1513	1362	1126	966	912	1169
55°	1150	975	732	597	554	1028
65°	777	594	392	315	308	770
75°	414	256	180	164	162	438
85°	97	49	43	43	43	116
90°	0	0	0	0	0	



TEST NUMBER: P930214

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2488.1	2488.1	2488.1	2488.1	2488.1
2.5°	2499.2	2488.1	2463.2	2485.9	2481.4
5°	2488.1	2476.8	2447.5	2467.8	2461.1
7.5°	2467.8	2454.4	2422.9	2431.6	2420.5
10°	2440.8	2425.0	2380.0	2373.2	2359.8
12.5°	2407.1	2386.8	2325.9	2312.5	2287.6
15°	2366.5	2341.6	2265.2	2222.4	2200.0
17.5°	2319.2	2283.1	2188.5	2139.0	2103.0
20°	2265.2	2220.0	2107.5	2051.4	2001.6
22.5°	2206.7	2154.8	2024.1	1947.6	1914.0
25°	2148.1	2076.0	1927.3	1835.2	1801.3
27.5°	2078.4	2001.6	1837.3	1731.5	1679.7
30°	2004.1	1918.3	1738.1	1623.5	1562.6
32.5°	1931.9	1828.3	1643.8	1508.6	1452.2
35°	1850.9	1736.0	1538.0	1396.1	1346.4
37.5°	1772.1	1648.1	1438.9	1283.3	1227.2
40°	1688.7	1553.8	1335.2	1175.4	1116.8
42.5°	1603.2	1459.2	1231.7	1064.9	1008.9
45°	1513.2	1362.2	1125.9	965.9	911.9
47.5°	1427.6	1267.8	1024.6	864.6	815.1
50°	1333.0	1173.2	925.4	770.0	722.9
52.5°	1240.6	1071.6	830.8	682.2	639.5
55°	1150.5	974.9	731.7	596.8	554.0
57.5°	1058.3	878.1	644.1	517.9	481.9
60°	963.7	783.5	551.6	437.0	400.8
62.5°	871.4	691.4	472.7	364.8	346.8
65°	776.8	594.3	391.8	315.4	308.4
67.5°	686.8	504.3	315.4	276.8	270.2
70°	592.2	416.6	261.1	238.6	229.5
72.5°	502.2	335.4	218.4	200.5	195.9
75°	414.3	256.5	180.1	164.3	162.2
77.5°	326.5	182.2	141.9	132.8	128.3
80°	245.4	130.6	108.0	99.2	99.2
82.5°	171.1	87.9	74.3	69.7	69.7
85°	96.8	49.4	42.7	42.7	42.7
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930214
 CATALOG NUMBER: DFN2DS-HX3F0-070DS935-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.91	16.43	15.28	16.75	17.06	10.87	12.39	11.24	12.71	13.02
	3H	16.68	18.04	17.06	18.37	18.73	12.14	13.50	12.52	13.83	14.19
	4H	17.34	18.62	17.74	18.97	19.35	12.64	13.92	13.04	14.27	14.65
	6H	17.83	19.02	18.24	19.38	19.77	13.02	14.20	13.43	14.57	14.96
	8H	18.00	19.12	18.42	19.51	19.92	13.15	14.27	13.57	14.66	15.06
	12H	18.10	19.18	18.53	19.56	19.99	13.23	14.30	13.66	14.69	15.12
4H	2H	15.02	16.30	15.42	16.65	17.02	11.57	12.85	11.97	13.20	13.58
	3H	16.95	18.01	17.36	18.41	18.81	13.01	14.07	13.42	14.47	14.87
	4H	17.70	18.66	18.13	19.07	19.51	13.61	14.57	14.04	14.98	15.42
	6H	18.29	19.12	18.75	19.57	20.02	14.10	14.93	14.56	15.37	15.83
	8H	18.50	19.28	18.97	19.73	20.19	14.26	15.04	14.72	15.48	15.95
	12H	18.66	19.35	19.14	19.83	20.30	14.38	15.07	14.86	15.55	16.02
8H	4H	17.72	18.50	18.19	18.94	19.41	13.96	14.74	14.43	15.19	15.65
	6H	18.36	19.00	18.86	19.49	19.97	14.55	15.19	15.05	15.68	16.16
	8H	18.61	19.19	19.12	19.70	20.19	14.77	15.35	15.29	15.86	16.35
	12H	18.81	19.32	19.32	19.82	20.38	14.95	15.46	15.46	15.95	16.52
12H	4H	17.71	18.40	18.19	18.88	19.35	14.01	14.70	14.49	15.18	15.65
	6H	18.34	18.92	18.85	19.43	19.92	14.61	15.19	15.13	15.70	16.19
	8H	18.63	19.14	19.14	19.63	20.19	14.89	15.40	15.40	15.89	16.45