

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931500

Luminaire Tested: DFN2DS-TR4F0-070DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-070DS835-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5950.0 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931500

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931500

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2298	2298	2298
5°	2307	2270	2282
10°	2289	2233	2213
15°	2263	2166	2104
20°	2227	2072	1968
25°	2189	1964	1836
30°	2138	1854	1667
35°	2087	1734	1518
40°	2036	1610	1347
45°	1977	1471	1191
50°	1916	1330	1039
55°	1853	1178	892
60°	1780	1019	741
65°	1698	856	674
70°	1599	705	620
75°	1479	643	579
80°	1305	575	527
85°	1025	453	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1977 cd/sqm

TEST NUMBER: P931500

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	4.6
10°-20°	744.3	12.5
20°-30°	1045.0	17.6
30°-40°	1139.2	19.1
40°-50°	1047.0	17.6
50°-60°	822.3	13.8
60°-70°	535.2	9.0
70°-80°	275.5	4.6
80°-90°	70.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2060.5	34.6
0°-40°	3199.7	53.8
0°-60°	5068.9	85.2
0°-90°	5950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	135
90°	0	0	0	0	0	

TEST NUMBER: P931500

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931500

CATALOG NUMBER: DFN2DS-TR4F0-070DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.13	15.65	14.49	15.96	16.28	10.09	11.61	10.45	11.92	12.24
	3H	15.89	17.26	16.27	17.58	17.95	11.35	12.72	11.73	13.04	13.41
	4H	16.56	17.84	16.96	18.19	18.57	11.85	13.13	12.25	13.48	13.86
	6H	17.05	18.23	17.46	18.60	18.99	12.23	13.42	12.65	13.78	14.18
	8H	17.21	18.34	17.64	18.73	19.13	12.36	13.49	12.79	13.88	14.28
	12H	17.32	18.39	17.75	18.78	19.20	12.44	13.52	12.87	13.90	14.33
4H	2H	14.23	15.51	14.63	15.86	16.24	10.78	12.06	11.18	12.41	12.79
	3H	16.16	17.23	16.57	17.63	18.03	12.23	13.29	12.64	13.69	14.09
	4H	16.91	17.87	17.35	18.28	18.72	12.82	13.78	13.26	14.20	14.64
	6H	17.50	18.34	17.96	18.78	19.24	13.31	14.14	13.77	14.59	15.05
	8H	17.72	18.50	18.18	18.94	19.41	13.47	14.25	13.94	14.70	15.16
	12H	17.87	18.57	18.35	19.05	19.52	13.59	14.29	14.07	14.76	15.24
8H	4H	16.94	17.71	17.40	18.16	18.63	13.18	13.96	13.64	14.40	14.87
	6H	17.57	18.22	18.07	18.71	19.19	13.77	14.41	14.26	14.90	15.38
	8H	17.82	18.40	18.34	18.91	19.40	13.99	14.56	14.50	15.07	15.56
	12H	18.03	18.54	18.54	19.03	19.60	14.17	14.68	14.67	15.17	15.73
12H	4H	16.92	17.62	17.40	18.09	18.57	13.22	13.92	13.70	14.39	14.87
	6H	17.56	18.13	18.07	18.64	19.13	13.83	14.41	14.34	14.92	15.40
	8H	17.84	18.35	18.35	18.84	19.41	14.10	14.61	14.61	15.10	15.67