

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930198

Luminaire Tested: DFN2DS-HX3F0-060DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-060DS940-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4549.2 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 61.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930198

CATALOG NUMBER: DFN2DS-HX3F0-060DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930198

CATALOG NUMBER: DFN2DS-HX3F0-060DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2562	2562	2562
5°	2572	2530	2544
10°	2552	2489	2468
15°	2523	2415	2345
20°	2482	2310	2194
25°	2441	2190	2047
30°	2383	2067	1858
35°	2327	1933	1693
40°	2270	1795	1501
45°	2204	1640	1328
50°	2136	1483	1158
55°	2066	1314	995
60°	1985	1136	826
65°	1893	955	752
70°	1783	786	691
75°	1648	717	645
80°	1455	640	588
85°	1143	505	505

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2204 cd/sqm

TEST NUMBER: P930198

CATALOG NUMBER: DFN2DS-HX3F0-060DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.3	4.6
10°-20°	569.1	12.5
20°-30°	799.0	17.6
30°-40°	871.0	19.1
40°-50°	800.5	17.6
50°-60°	628.7	13.8
60°-70°	409.2	9.0
70°-80°	210.6	4.6
80°-90°	53.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1575.4	34.6
0°-40°	2446.4	53.8
0°-60°	3875.6	85.2
0°-90°	4549.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4549.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2212	2212	2212	2212	2212	
5°	2212	2202	2176	2194	2188	210
15°	2104	2082	2014	1976	1956	593
25°	1910	1846	1714	1632	1601	878
35°	1646	1543	1367	1241	1197	1030
45°	1345	1211	1001	859	811	1039
55°	1023	867	650	531	492	914
65°	691	528	348	280	274	685
75°	368	228	160	146	144	390
85°	86	44	38	38	38	103
90°	0	0	0	0	0	

TEST NUMBER: P930198

CATALOG NUMBER: DFN2DS-HX3F0-060DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2212.0	2212.0	2212.0	2212.0	2212.0
2.5°	2222.0	2212.0	2189.9	2210.0	2206.0
5°	2212.0	2202.0	2175.9	2194.0	2188.0
7.5°	2194.0	2182.0	2154.0	2161.9	2151.9
10°	2169.9	2155.9	2116.0	2109.8	2097.9
12.5°	2140.0	2121.9	2067.7	2055.9	2033.8
15°	2103.9	2081.7	2013.8	1975.8	1955.8
17.5°	2061.9	2029.7	1945.6	1901.7	1869.6
20°	2013.8	1973.6	1873.6	1823.7	1779.5
22.5°	1961.8	1915.7	1799.5	1731.6	1701.6
25°	1909.8	1845.6	1713.5	1631.6	1601.4
27.5°	1847.8	1779.5	1633.4	1539.3	1493.3
30°	1781.7	1705.4	1545.3	1443.3	1389.2
32.5°	1717.5	1625.4	1461.5	1341.2	1291.1
35°	1645.6	1543.4	1367.3	1241.1	1197.0
37.5°	1575.5	1465.2	1279.2	1141.0	1091.0
40°	1501.3	1381.4	1187.0	1044.9	992.9
42.5°	1425.3	1297.2	1095.0	946.8	896.9
45°	1345.2	1211.0	1001.0	858.6	810.6
47.5°	1269.2	1127.1	910.9	768.6	724.7
50°	1185.1	1043.0	822.8	684.5	642.7
52.5°	1102.9	952.7	738.7	606.6	568.6
55°	1022.9	866.8	650.5	530.6	492.5
57.5°	940.9	780.7	572.6	460.5	428.3
60°	856.8	696.7	490.4	388.5	356.4
62.5°	774.8	614.7	420.3	324.3	308.4
65°	690.7	528.4	348.3	280.4	274.2
67.5°	610.6	448.3	280.4	246.2	240.2
70°	526.5	370.4	232.1	212.2	204.1
72.5°	446.4	298.2	194.1	178.2	174.1
75°	368.3	228.1	160.1	146.1	144.2
77.5°	290.3	162.1	126.1	118.1	114.1
80°	218.1	116.1	96.0	88.1	88.1
82.5°	152.1	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930198

CATALOG NUMBER: DFN2DS-HX3F0-060DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.50	16.03	14.87	16.34	16.65	10.46	11.99	10.83	12.30	12.61
	3H	16.27	17.63	16.65	17.96	18.32	11.73	13.10	12.11	13.42	13.78
	4H	16.94	18.22	17.33	18.56	18.94	12.23	13.51	12.63	13.86	14.24
	6H	17.42	18.61	17.84	18.97	19.37	12.61	13.80	13.02	14.16	14.55
	8H	17.59	18.72	18.02	19.11	19.51	12.74	13.86	13.16	14.25	14.65
	12H	17.69	18.77	18.12	19.15	19.58	12.82	13.90	13.25	14.28	14.71
4H	2H	14.61	15.89	15.01	16.24	16.62	11.16	12.44	11.56	12.79	13.17
	3H	16.54	17.60	16.95	18.00	18.40	12.60	13.67	13.01	14.07	14.47
	4H	17.29	18.25	17.72	18.66	19.10	13.20	14.16	13.63	14.57	15.01
	6H	17.88	18.71	18.34	19.16	19.62	13.69	14.52	14.15	14.97	15.42
	8H	18.10	18.87	18.56	19.32	19.79	13.85	14.63	14.32	15.07	15.54
	12H	18.25	18.94	18.73	19.42	19.89	13.97	14.66	14.45	15.14	15.61
8H	4H	17.31	18.09	17.78	18.54	19.00	13.56	14.33	14.02	14.78	15.24
	6H	17.95	18.59	18.45	19.09	19.56	14.14	14.79	14.64	15.28	15.75
	8H	18.20	18.78	18.72	19.29	19.78	14.36	14.94	14.88	15.45	15.94
	12H	18.41	18.92	18.92	19.41	19.97	14.54	15.05	15.05	15.54	16.11
12H	4H	17.30	17.99	17.78	18.47	18.94	13.60	14.29	14.08	14.77	15.24
	6H	17.93	18.51	18.45	19.02	19.51	14.21	14.78	14.72	15.29	15.78
	8H	18.22	18.73	18.73	19.22	19.78	14.48	14.99	14.99	15.48	16.05

END OF REPORT