

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930302

Luminaire Tested: DFN2DS-HX4F0-060DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-060DS930-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4156.5 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930302

CATALOG NUMBER: DFN2DS-HX4F0-060DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930302

CATALOG NUMBER: DFN2DS-HX4F0-060DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1503	1503	1503
5°	1508	1484	1492
10°	1497	1460	1447
15°	1480	1416	1376
20°	1456	1355	1287
25°	1432	1284	1200
30°	1398	1212	1090
35°	1365	1134	993
40°	1331	1053	881
45°	1292	962	779
50°	1253	870	679
55°	1212	771	583
60°	1164	666	484
65°	1110	560	441
70°	1046	461	405
75°	967	420	379
80°	853	376	345
85°	671	296	296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1292 cd/sqm

TEST NUMBER: P930302

CATALOG NUMBER: DFN2DS-HX4F0-060DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.4	4.6
10°-20°	520.0	12.5
20°-30°	730.0	17.6
30°-40°	795.8	19.1
40°-50°	731.4	17.6
50°-60°	574.4	13.8
60°-70°	373.9	9.0
70°-80°	192.5	4.6
80°-90°	49.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1439.4	34.6
0°-40°	2235.2	53.8
0°-60°	3541.0	85.2
0°-90°	4156.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4156.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2021	2021	2021	2021	2021	
5°	2021	2012	1988	2005	1999	192
15°	1922	1902	1840	1805	1787	542
25°	1745	1686	1566	1491	1463	802
35°	1504	1410	1249	1134	1094	941
45°	1229	1106	915	784	741	949
55°	935	792	594	485	450	835
65°	631	483	318	256	250	626
75°	336	208	146	134	132	356
85°	79	40	35	35	35	94
90°	0	0	0	0	0	

TEST NUMBER: P930302

CATALOG NUMBER: DFN2DS-HX4F0-060DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.0	2021.0	2021.0	2021.0	2021.0
2.5°	2030.2	2021.0	2000.8	2019.2	2015.6
5°	2021.0	2011.9	1988.0	2004.6	1999.1
7.5°	2004.6	1993.7	1968.1	1975.2	1966.1
10°	1982.6	1969.8	1933.3	1927.7	1916.8
12.5°	1955.3	1938.7	1889.3	1878.4	1858.2
15°	1922.3	1902.0	1839.9	1805.2	1787.0
17.5°	1883.9	1854.5	1777.7	1737.5	1708.2
20°	1839.9	1803.3	1711.9	1666.3	1625.9
22.5°	1792.4	1750.3	1644.2	1582.1	1554.7
25°	1744.9	1686.3	1565.6	1490.7	1463.2
27.5°	1688.3	1625.9	1492.4	1406.4	1364.4
30°	1627.9	1558.2	1411.9	1318.8	1269.3
32.5°	1569.3	1485.1	1335.3	1225.4	1179.6
35°	1503.5	1410.2	1249.3	1134.0	1093.6
37.5°	1439.5	1338.7	1168.8	1042.5	996.8
40°	1371.7	1262.1	1084.5	954.7	907.2
42.5°	1302.3	1185.3	1000.5	865.0	819.5
45°	1229.1	1106.4	914.6	784.5	740.7
47.5°	1159.7	1029.8	832.3	702.3	662.1
50°	1082.8	953.0	751.8	625.4	587.2
52.5°	1007.7	870.5	674.9	554.2	519.5
55°	934.6	791.9	594.4	484.8	450.0
57.5°	859.7	713.3	523.1	420.7	391.4
60°	782.8	636.5	448.1	354.9	325.6
62.5°	707.9	561.6	384.0	296.3	281.7
65°	631.1	482.8	318.3	256.2	250.5
67.5°	557.9	409.6	256.2	224.9	219.5
70°	481.0	338.4	212.1	193.9	186.5
72.5°	407.9	272.5	177.3	162.8	159.1
75°	336.5	208.4	146.3	133.5	131.8
77.5°	265.3	148.1	115.2	107.9	104.2
80°	199.3	106.1	87.7	80.5	80.5
82.5°	139.0	71.4	60.3	56.6	56.6
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.3	14.6	14.6	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930302

CATALOG NUMBER: DFN2DS-HX4F0-060DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.65	14.17	13.01	14.48	14.80	8.61	10.13	8.98	10.45	10.76
	3H	14.41	15.78	14.79	16.11	16.47	9.88	11.24	10.25	11.57	11.93
	4H	15.08	16.36	15.48	16.71	17.09	10.38	11.66	10.78	12.01	12.39
	6H	15.57	16.75	15.98	17.12	17.51	10.76	11.94	11.17	12.31	12.70
	8H	15.74	16.86	16.16	17.25	17.65	10.88	12.01	11.31	12.40	12.80
	12H	15.84	16.92	16.27	17.30	17.73	10.96	12.04	11.39	12.42	12.85
4H	2H	12.75	14.03	13.15	14.38	14.76	9.31	10.59	9.71	10.94	11.31
	3H	14.69	15.75	15.10	16.15	16.55	10.75	11.81	11.16	12.21	12.61
	4H	15.44	16.39	15.87	16.81	17.25	11.35	12.31	11.78	12.72	13.16
	6H	16.03	16.86	16.49	17.30	17.76	11.84	12.67	12.29	13.11	13.57
	8H	16.24	17.02	16.71	17.46	17.93	12.00	12.78	12.46	13.22	13.69
	12H	16.40	17.09	16.88	17.57	18.04	12.12	12.81	12.60	13.29	13.76
8H	4H	15.46	16.24	15.92	16.68	17.15	11.70	12.48	12.17	12.92	13.39
	6H	16.10	16.74	16.59	17.23	17.71	12.29	12.93	12.79	13.42	13.90
	8H	16.35	16.93	16.86	17.43	17.92	12.51	13.09	13.02	13.60	14.08
	12H	16.55	17.06	17.06	17.55	18.12	12.69	13.20	13.20	13.69	14.25
12H	4H	15.45	16.14	15.93	16.62	17.09	11.75	12.44	12.23	12.92	13.39
	6H	16.08	16.66	16.59	17.17	17.65	12.35	12.93	12.87	13.44	13.93
	8H	16.36	16.87	16.87	17.37	17.93	12.62	13.13	13.13	13.63	14.19