

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931447

Luminaire Tested: DFN2DS-TR4F0-040DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-040DS840-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3963.9 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 38.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931447

CATALOG NUMBER: DFN2DS-TR4F0-040DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931447

CATALOG NUMBER: DFN2DS-TR4F0-040DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1238	1238	1238
5°	1242	1225	1232
10°	1235	1212	1218
15°	1220	1196	1195
20°	1198	1173	1172
25°	1177	1144	1144
30°	1149	1117	1108
35°	1123	1085	1069
40°	1091	1053	1033
45°	1059	1022	996
50°	1024	989	954
55°	988	950	915
60°	947	905	871
65°	904	859	820
70°	849	804	766
75°	773	740	722
80°	685	664	630
85°	560	533	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1059 cd/sqm

TEST NUMBER: P931447

CATALOG NUMBER: DFN2DS-TR4F0-040DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.6	3.7
10°-20°	412.6	10.4
20°-30°	606.3	15.3
30°-40°	704.2	17.8
40°-50°	703.3	17.7
50°-60°	613.3	15.5
60°-70°	453.4	11.4
70°-80°	256.5	6.5
80°-90°	67.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.5	29.4
0°-40°	1869.8	47.2
0°-60°	3186.4	80.4
0°-90°	3963.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3963.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1552	1536	1547	1545	148
15°	1483	1474	1455	1461	1453	418
25°	1342	1330	1305	1308	1305	618
35°	1158	1143	1119	1110	1103	723
45°	942	932	909	893	887	727
55°	713	704	686	668	661	638
65°	481	472	457	443	436	476
75°	252	249	241	232	235	269
85°	61	60	58	54	52	72
90°	0	0	0	0	0	

TEST NUMBER: P931447

CATALOG NUMBER: DFN2DS-TR4F0-040DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.0	1558.0	1558.0	1558.0	1558.0
2.5°	1567.1	1559.6	1543.0	1558.0	1555.2
5°	1558.0	1552.1	1535.5	1547.4	1544.6
7.5°	1547.4	1538.5	1522.0	1534.1	1531.1
10°	1531.1	1520.6	1502.7	1514.6	1510.1
12.5°	1508.5	1499.6	1481.7	1489.2	1486.1
15°	1483.1	1474.2	1454.7	1460.7	1453.3
17.5°	1451.7	1442.7	1423.2	1430.6	1423.2
20°	1417.1	1408.2	1387.3	1391.7	1385.9
22.5°	1382.8	1369.3	1349.7	1349.7	1346.7
25°	1342.2	1330.3	1304.9	1307.8	1304.9
27.5°	1297.3	1286.8	1267.5	1263.0	1255.6
30°	1252.5	1240.4	1218.0	1213.5	1207.5
32.5°	1204.5	1195.6	1171.6	1162.6	1156.5
35°	1158.1	1143.1	1119.1	1110.1	1102.6
37.5°	1105.6	1092.1	1068.1	1057.7	1050.1
40°	1051.8	1039.6	1015.6	1002.3	996.3
42.5°	999.3	987.2	963.4	948.2	939.3
45°	942.3	931.9	909.3	893.0	886.9
47.5°	886.9	876.4	852.5	835.9	827.0
50°	828.4	820.9	800.0	779.0	771.5
52.5°	771.5	761.1	741.6	725.1	714.6
55°	713.2	704.1	686.2	668.2	660.8
57.5°	654.7	647.2	627.6	609.7	603.7
60°	596.2	590.3	569.4	552.9	548.3
62.5°	539.3	528.8	513.9	498.9	492.9
65°	481.0	471.9	457.0	443.4	436.0
67.5°	421.0	413.4	400.1	389.6	383.6
70°	365.6	359.6	346.0	335.5	329.6
72.5°	308.7	302.6	295.2	284.7	280.2
75°	251.7	248.7	241.1	232.2	235.2
77.5°	200.7	194.7	191.7	187.2	182.8
80°	149.8	148.2	145.2	140.8	137.8
82.5°	101.9	101.9	100.5	94.4	94.4
85°	61.4	60.0	58.5	53.9	52.5
87.5°	27.0	24.0	21.0	16.5	14.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931447

CATALOG NUMBER: DFN2DS-TR4F0-040DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.02	13.63	12.39	13.95	14.26	11.58	13.19	11.94	13.50	13.82
	3H	13.77	15.23	14.15	15.55	15.92	13.28	14.74	13.66	15.06	15.42
	4H	14.42	15.79	14.82	16.14	16.51	13.92	15.29	14.32	15.64	16.02
	6H	14.89	16.16	15.30	16.52	16.91	14.39	15.66	14.80	16.02	16.41
	8H	15.03	16.24	15.46	16.63	17.03	14.53	15.74	14.95	16.13	16.53
	12H	15.12	16.28	15.55	16.66	17.09	14.61	15.77	15.04	16.15	16.58
4H	2H	12.58	13.95	12.98	14.30	14.68	12.23	13.60	12.63	13.95	14.32
	3H	14.56	15.71	14.97	16.10	16.50	14.15	15.30	14.56	15.70	16.10
	4H	15.34	16.37	15.77	16.79	17.22	14.91	15.95	15.34	16.36	16.80
	6H	15.93	16.84	16.39	17.28	17.73	15.50	16.40	15.95	16.85	17.30
	8H	16.12	16.97	16.58	17.41	17.88	15.68	16.53	16.14	16.97	17.44
	12H	16.25	17.01	16.73	17.49	17.96	15.80	16.56	16.28	17.04	17.51
8H	4H	15.61	16.46	16.07	16.90	17.36	15.23	16.08	15.70	16.52	16.99
	6H	16.32	17.03	16.82	17.51	17.99	15.94	16.64	16.44	17.13	17.61
	8H	16.58	17.21	17.09	17.72	18.21	16.19	16.82	16.70	17.33	17.81
	12H	16.78	17.34	17.29	17.83	18.39	16.37	16.93	16.88	17.42	17.98
12H	4H	15.63	16.39	16.12	16.87	17.34	15.27	16.03	15.75	16.51	16.98
	6H	16.37	17.00	16.88	17.51	17.99	16.00	16.63	16.51	17.14	17.62
	8H	16.68	17.24	17.19	17.73	18.29	16.30	16.86	16.81	17.35	17.91