

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930268

Luminaire Tested: DFN2DS-HX4F0-040DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-040DS935-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2924.0 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930268

CATALOG NUMBER: DFN2DS-HX4F0-040DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930268

CATALOG NUMBER: DFN2DS-HX4F0-040DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1057	1057	1057
5°	1061	1044	1050
10°	1053	1027	1018
15°	1041	996	968
20°	1024	953	905
25°	1007	904	844
30°	983	853	767
35°	960	798	698
40°	937	741	619
45°	909	677	548
50°	881	612	478
55°	852	542	410
60°	819	469	341
65°	781	394	310
70°	736	324	285
75°	680	296	266
80°	600	264	243
85°	472	208	208

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 909 cd/sqm

TEST NUMBER: P930268

CATALOG NUMBER: DFN2DS-HX4F0-040DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.2	4.6
10°-20°	365.8	12.5
20°-30°	513.6	17.6
30°-40°	559.8	19.1
40°-50°	514.5	17.6
50°-60°	404.1	13.8
60°-70°	263.0	9.0
70°-80°	135.4	4.6
80°-90°	34.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1012.6	34.6
0°-40°	1572.4	53.8
0°-60°	2491.0	85.2
0°-90°	2924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2924.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1422	1422	1422	1422	1422	
5°	1422	1415	1398	1410	1406	135
15°	1352	1338	1294	1270	1257	381
25°	1228	1186	1101	1049	1029	565
35°	1058	992	879	798	769	662
45°	865	778	643	552	521	668
55°	658	557	418	341	317	588
65°	444	340	224	180	176	440
75°	237	147	103	94	93	250
85°	55	28	24	24	24	66
90°	0	0	0	0	0	

TEST NUMBER: P930268

CATALOG NUMBER: DFN2DS-HX4F0-040DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.8	1421.8	1421.8	1421.8	1421.8
2.5°	1428.2	1421.8	1407.6	1420.5	1417.9
5°	1421.8	1415.3	1398.5	1410.1	1406.4
7.5°	1410.1	1402.5	1384.5	1389.5	1383.1
10°	1394.7	1385.7	1360.0	1356.0	1348.5
12.5°	1375.5	1363.9	1329.0	1321.4	1307.2
15°	1352.3	1338.1	1294.4	1270.0	1257.1
17.5°	1325.3	1304.6	1250.5	1222.3	1201.7
20°	1294.4	1268.6	1204.3	1172.2	1143.8
22.5°	1260.9	1231.3	1156.6	1112.9	1093.7
25°	1227.5	1186.3	1101.3	1048.7	1029.2
27.5°	1187.7	1143.8	1049.9	989.4	959.8
30°	1145.2	1096.2	993.2	927.7	892.9
32.5°	1104.0	1044.7	939.3	862.1	829.8
35°	1057.7	992.0	878.8	797.7	769.4
37.5°	1012.6	941.8	822.2	733.3	701.2
40°	965.0	887.9	763.0	671.7	638.2
42.5°	916.1	833.8	703.8	608.5	576.5
45°	864.6	778.4	643.4	551.9	521.1
47.5°	815.8	724.5	585.5	494.1	465.8
50°	761.7	670.4	528.8	440.0	413.1
52.5°	708.9	612.4	474.8	389.8	365.4
55°	657.5	557.1	418.1	341.0	316.6
57.5°	604.8	501.8	368.0	295.9	275.4
60°	550.7	447.7	315.2	249.7	229.1
62.5°	498.0	395.1	270.1	208.5	198.2
65°	443.9	339.6	223.9	180.2	176.2
67.5°	392.5	288.2	180.2	158.2	154.4
70°	338.4	238.0	149.2	136.4	131.2
72.5°	287.0	191.7	124.8	114.6	112.0
75°	236.7	146.6	102.9	93.9	92.7
77.5°	186.6	104.1	81.1	75.9	73.3
80°	140.2	74.6	61.7	56.7	56.7
82.5°	97.8	50.2	42.5	39.8	39.8
85°	55.3	28.3	24.4	24.4	24.4
87.5°	20.6	10.2	10.2	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930268

CATALOG NUMBER: DFN2DS-HX4F0-040DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.43	12.95	11.79	13.26	13.58	7.39	8.91	7.75	9.22	9.54
	3H	13.19	14.56	13.57	14.89	15.25	8.65	10.02	9.03	10.35	10.71
	4H	13.86	15.14	14.26	15.49	15.87	9.16	10.44	9.55	10.78	11.16
	6H	14.35	15.53	14.76	15.90	16.29	9.54	10.72	9.95	11.09	11.48
	8H	14.51	15.64	14.94	16.03	16.43	9.66	10.79	10.09	11.18	11.58
	12H	14.62	15.70	15.05	16.08	16.51	9.74	10.82	10.17	11.20	11.63
4H	2H	11.53	12.81	11.93	13.16	13.54	8.08	9.36	8.48	9.71	10.09
	3H	13.47	14.53	13.88	14.93	15.33	9.53	10.59	9.94	10.99	11.39
	4H	14.21	15.17	14.65	15.59	16.03	10.13	11.08	10.56	11.50	11.94
	6H	14.81	15.64	15.26	16.08	16.54	10.62	11.45	11.07	11.89	12.35
	8H	15.02	15.80	15.48	16.24	16.71	10.78	11.55	11.24	12.00	12.47
	12H	15.17	15.87	15.66	16.35	16.82	10.89	11.59	11.38	12.07	12.54
8H	4H	14.24	15.02	14.70	15.46	15.93	10.48	11.26	10.94	11.70	12.17
	6H	14.88	15.52	15.37	16.01	16.49	11.07	11.71	11.56	12.20	12.68
	8H	15.13	15.70	15.64	16.21	16.70	11.29	11.86	11.80	12.37	12.86
	12H	15.33	15.84	15.84	16.33	16.90	11.47	11.98	11.98	12.47	13.03
12H	4H	14.22	14.92	14.71	15.40	15.87	10.52	11.22	11.01	11.70	12.17
	6H	14.86	15.43	15.37	15.94	16.43	11.13	11.71	11.64	12.22	12.71
	8H	15.14	15.65	15.65	16.14	16.71	11.40	11.91	11.91	12.41	12.97