

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930544

Luminaire Tested: DFN2DS-PN3F0-050DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930544
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-050DS830-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4003.5 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930544

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930544

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2276	2276	2276
5°	2284	2247	2259
10°	2267	2210	2191
15°	2241	2145	2083
20°	2205	2051	1948
25°	2168	1945	1818
30°	2117	1836	1650
35°	2067	1717	1503
40°	2016	1594	1333
45°	1957	1456	1179
50°	1897	1317	1029
55°	1835	1167	883
60°	1763	1009	733
65°	1681	848	667
70°	1584	698	614
75°	1464	636	573
80°	1293	569	522
85°	1015	448	448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1957 cd/sqm

TEST NUMBER: P930544

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.4	4.6
10°-20°	500.8	12.5
20°-30°	703.2	17.6
30°-40°	766.5	19.1
40°-50°	704.5	17.6
50°-60°	553.3	13.8
60°-70°	360.1	9.0
70°-80°	185.4	4.6
80°-90°	47.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1386.4	34.6
0°-40°	2152.9	53.8
0°-60°	3410.7	85.2
0°-90°	4003.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4003.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1938	1915	1931	1926	185
15°	1852	1832	1772	1739	1721	522
25°	1681	1624	1508	1436	1409	773
35°	1448	1358	1203	1092	1053	906
45°	1184	1066	881	756	713	914
55°	900	763	572	467	433	804
65°	608	465	306	247	241	603
75°	324	201	141	129	127	343
85°	76	39	33	33	33	91
90°	0	0	0	0	0	

TEST NUMBER: P930544

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1946.6	1946.6	1946.6	1946.6	1946.6
2.5°	1955.4	1946.6	1927.2	1944.9	1941.4
5°	1946.6	1937.9	1914.9	1930.7	1925.5
7.5°	1930.7	1920.3	1895.6	1902.6	1893.7
10°	1909.6	1897.3	1862.1	1856.8	1846.2
12.5°	1883.2	1867.4	1819.8	1809.3	1789.8
15°	1851.5	1832.1	1772.3	1738.8	1721.2
17.5°	1814.5	1786.3	1712.3	1673.6	1645.3
20°	1772.3	1737.0	1648.9	1605.0	1566.1
22.5°	1726.5	1685.9	1583.7	1523.9	1497.5
25°	1680.6	1624.2	1508.0	1435.8	1409.2
27.5°	1626.1	1566.1	1437.5	1354.7	1314.2
30°	1568.0	1500.9	1360.0	1270.2	1222.5
32.5°	1511.5	1430.4	1286.1	1180.3	1136.2
35°	1448.1	1358.3	1203.3	1092.2	1053.4
37.5°	1386.4	1289.5	1125.8	1004.1	960.2
40°	1321.2	1215.7	1044.6	919.6	873.8
42.5°	1254.4	1141.6	963.7	833.2	789.3
45°	1183.9	1065.8	880.9	755.7	713.4
47.5°	1116.9	991.9	801.6	676.5	637.7
50°	1043.0	917.9	724.1	602.4	565.6
52.5°	970.6	838.5	650.1	533.8	500.4
55°	900.2	762.7	572.5	466.9	433.4
57.5°	828.0	687.1	503.9	405.2	377.0
60°	754.0	613.1	431.5	341.9	313.6
62.5°	681.8	540.9	369.9	285.4	271.4
65°	607.8	465.1	306.5	246.7	241.3
67.5°	537.3	394.6	246.7	216.7	211.4
70°	463.4	325.9	204.3	186.7	179.6
72.5°	392.9	262.4	170.9	156.8	153.3
75°	324.1	200.7	140.9	128.6	126.9
77.5°	255.5	142.6	111.1	103.9	100.3
80°	192.0	102.2	84.5	77.5	77.5
82.5°	133.9	68.8	58.1	54.5	54.5
85°	75.7	38.7	33.4	33.4	33.4
87.5°	28.3	14.0	14.0	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930544

CATALOG NUMBER: DFN2DS-PN3F0-050DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.09	15.61	14.46	15.93	16.24	10.05	11.57	10.42	11.89	12.20
	3H	15.86	17.22	16.23	17.55	17.91	11.32	12.68	11.70	13.01	13.37
	4H	16.52	17.80	16.92	18.15	18.53	11.82	13.10	12.22	13.45	13.83
	6H	17.01	18.20	17.42	18.56	18.95	12.20	13.38	12.61	13.75	14.14
	8H	17.18	18.30	17.60	18.69	19.09	12.32	13.45	12.75	13.84	14.24
	12H	17.28	18.36	17.71	18.74	19.17	12.40	13.48	12.83	13.86	14.29
4H	2H	14.20	15.48	14.60	15.82	16.20	10.75	12.03	11.15	12.38	12.76
	3H	16.13	17.19	16.54	17.59	17.99	12.19	13.25	12.60	13.65	14.05
	4H	16.88	17.83	17.31	18.25	18.69	12.79	13.75	13.22	14.16	14.60
	6H	17.47	18.30	17.93	18.74	19.20	13.28	14.11	13.73	14.55	15.01
	8H	17.68	18.46	18.15	18.91	19.37	13.44	14.22	13.90	14.66	15.13
	12H	17.84	18.53	18.32	19.01	19.48	13.56	14.25	14.04	14.73	15.20
8H	4H	16.90	17.68	17.37	18.12	18.59	13.14	13.92	13.61	14.37	14.83
	6H	17.54	18.18	18.04	18.67	19.15	13.73	14.37	14.23	14.86	15.34
	8H	17.79	18.37	18.30	18.88	19.36	13.95	14.53	14.46	15.04	15.52
	12H	17.99	18.50	18.50	19.00	19.56	14.13	14.64	14.64	15.13	15.70
12H	4H	16.89	17.58	17.37	18.06	18.53	13.19	13.88	13.67	14.36	14.83
	6H	17.52	18.10	18.03	18.61	19.10	13.79	14.37	14.31	14.88	15.37
	8H	17.81	18.32	18.31	18.81	19.37	14.07	14.58	14.58	15.07	15.63