

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930513

Luminaire Tested: DFN2DS-PN3F0-030DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-030DS850-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3293.8 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 28.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930513

CATALOG NUMBER: DFN2DS-PN3F0-030DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930513

CATALOG NUMBER: DFN2DS-PN3F0-030DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1513	1513	1513
5°	1519	1497	1506
10°	1510	1482	1489
15°	1491	1463	1461
20°	1465	1434	1432
25°	1439	1399	1399
30°	1405	1366	1354
35°	1373	1327	1307
40°	1334	1288	1263
45°	1295	1249	1218
50°	1252	1209	1166
55°	1208	1162	1119
60°	1158	1106	1065
65°	1106	1050	1002
70°	1038	983	936
75°	944	905	883
80°	838	813	771
85°	684	652	585

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1295 cd/sqm

TEST NUMBER: P930513

CATALOG NUMBER: DFN2DS-PN3F0-030DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	3.7
10°-20°	342.8	10.4
20°-30°	503.8	15.3
30°-40°	585.2	17.8
40°-50°	584.4	17.7
50°-60°	509.6	15.5
60°-70°	376.7	11.4
70°-80°	213.1	6.5
80°-90°	56.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.5	29.4
0°-40°	1553.6	47.2
0°-60°	2647.7	80.4
0°-90°	3293.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3293.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	60
90°	0	0	0	0	0	

TEST NUMBER: P930513

CATALOG NUMBER: DFN2DS-PN3F0-030DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930513

CATALOG NUMBER: DFN2DS-PN3F0-030DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.72	14.33	13.09	14.65	14.96	12.28	13.89	12.64	14.20	14.52
	3H	14.47	15.93	14.85	16.25	16.61	13.98	15.44	14.36	15.76	16.12
	4H	15.12	16.49	15.52	16.84	17.21	14.62	15.99	15.02	16.34	16.72
	6H	15.59	16.86	16.00	17.22	17.61	15.09	16.35	15.50	16.72	17.11
	8H	15.73	16.94	16.16	17.33	17.73	15.23	16.44	15.65	16.83	17.23
	12H	15.82	16.98	16.25	17.36	17.79	15.31	16.47	15.74	16.85	17.28
4H	2H	13.28	14.65	13.68	15.00	15.38	12.93	14.30	13.33	14.65	15.02
	3H	15.26	16.40	15.67	16.80	17.20	14.85	16.00	15.26	16.39	16.79
	4H	16.03	17.07	16.47	17.48	17.92	15.61	16.65	16.04	17.06	17.50
	6H	16.63	17.54	17.09	17.98	18.43	16.20	17.10	16.65	17.54	18.00
	8H	16.82	17.67	17.28	18.11	18.57	16.38	17.23	16.84	17.67	18.14
	12H	16.95	17.71	17.43	18.19	18.66	16.50	17.26	16.98	17.74	18.21
8H	4H	16.31	17.15	16.77	17.60	18.06	15.93	16.78	16.39	17.22	17.69
	6H	17.02	17.72	17.52	18.21	18.69	16.64	17.34	17.13	17.83	18.31
	8H	17.28	17.91	17.79	18.42	18.90	16.89	17.52	17.40	18.03	18.51
	12H	17.48	18.04	17.99	18.53	19.09	17.07	17.63	17.57	18.12	18.68
12H	4H	16.33	17.09	16.81	17.57	18.04	15.97	16.73	16.45	17.20	17.67
	6H	17.07	17.70	17.58	18.21	18.69	16.70	17.33	17.21	17.84	18.32
	8H	17.38	17.94	17.89	18.43	18.99	17.00	17.56	17.51	18.05	18.61