

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930549

Luminaire Tested: DFN2DS-PN3F0-050DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-050DS850-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5489.6 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930549

CATALOG NUMBER: DFN2DS-PN3F0-050DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930549

CATALOG NUMBER: DFN2DS-PN3F0-050DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2522	2522	2522
5°	2532	2495	2510
10°	2517	2470	2483
15°	2486	2438	2436
20°	2441	2390	2387
25°	2398	2331	2331
30°	2341	2277	2257
35°	2289	2212	2179
40°	2223	2146	2105
45°	2158	2082	2030
50°	2086	2015	1943
55°	2013	1937	1865
60°	1930	1843	1775
65°	1842	1750	1670
70°	1730	1638	1561
75°	1574	1508	1472
80°	1398	1354	1285
85°	1139	1086	974

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2158 cd/sqm

TEST NUMBER: P930549

CATALOG NUMBER: DFN2DS-PN3F0-050DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.1	3.7
10°-20°	571.4	10.4
20°-30°	839.7	15.3
30°-40°	975.2	17.8
40°-50°	974.0	17.7
50°-60°	849.3	15.5
60°-70°	627.9	11.4
70°-80°	355.2	6.5
80°-90°	93.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1614.1	29.4
0°-40°	2589.4	47.2
0°-60°	4412.7	80.4
0°-90°	5489.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5489.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2126	2143	2139	205
15°	2054	2042	2014	2023	2012	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1001
45°	1305	1290	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	100
90°	0	0	0	0	0	

TEST NUMBER: P930549

CATALOG NUMBER: DFN2DS-PN3F0-050DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.6	2157.6	2157.6	2157.6	2157.6
2.5°	2170.1	2159.8	2136.9	2157.6	2153.7
5°	2157.6	2149.5	2126.5	2143.0	2139.2
7.5°	2143.0	2130.7	2107.9	2124.6	2120.4
10°	2120.4	2105.9	2081.0	2097.5	2091.4
12.5°	2089.1	2076.8	2052.0	2062.3	2058.1
15°	2053.9	2041.6	2014.5	2022.9	2012.5
17.5°	2010.3	1998.0	1970.9	1981.2	1970.9
20°	1962.6	1950.3	1921.2	1927.3	1919.2
22.5°	1915.0	1896.3	1869.2	1869.2	1865.0
25°	1858.9	1842.4	1807.1	1811.1	1807.1
27.5°	1796.6	1782.1	1755.2	1749.0	1738.7
30°	1734.5	1717.8	1686.8	1680.6	1672.3
32.5°	1668.0	1655.7	1622.5	1609.9	1601.6
35°	1603.7	1583.1	1549.8	1537.3	1527.0
37.5°	1531.1	1512.5	1479.2	1464.7	1454.3
40°	1456.6	1439.8	1406.5	1388.0	1379.7
42.5°	1383.9	1367.2	1334.1	1313.2	1300.9
45°	1305.1	1290.5	1259.3	1236.6	1228.2
47.5°	1228.2	1213.7	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.8	1068.4
52.5°	1068.4	1053.9	1027.0	1004.2	989.7
55°	987.7	975.1	950.2	925.3	915.0
57.5°	906.6	896.3	869.2	844.4	836.0
60°	825.7	817.6	788.5	765.5	759.4
62.5°	746.9	732.4	711.6	690.9	682.6
65°	666.1	653.5	632.8	614.2	603.7
67.5°	583.1	572.6	554.1	539.5	531.1
70°	506.3	497.9	479.2	464.7	456.6
72.5°	427.5	419.1	408.8	394.2	388.0
75°	348.4	344.5	333.9	321.6	325.8
77.5°	278.0	269.6	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.1	190.9
82.5°	141.1	141.1	139.1	130.8	130.8
85°	84.9	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.8	20.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930549

CATALOG NUMBER: DFN2DS-PN3F0-050DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.50	16.11	14.86	16.42	16.74	14.05	15.66	14.42	15.98	16.29
	3H	16.25	17.70	16.62	18.03	18.39	15.76	17.21	16.13	17.54	17.90
	4H	16.89	18.26	17.29	18.61	18.99	16.40	17.77	16.80	18.12	18.49
	6H	17.36	18.63	17.77	19.00	19.39	16.86	18.13	17.27	18.49	18.89
	8H	17.51	18.72	17.93	19.11	19.50	17.00	18.21	17.43	18.60	19.00
	12H	17.60	18.76	18.03	19.14	19.57	17.08	18.24	17.51	18.63	19.05
4H	2H	15.06	16.43	15.46	16.77	17.15	14.70	16.07	15.10	16.42	16.80
	3H	17.03	18.18	17.44	18.58	18.98	16.63	17.77	17.04	18.17	18.57
	4H	17.81	18.84	18.24	19.26	19.69	17.39	18.42	17.82	18.83	19.27
	6H	18.41	19.31	18.86	19.75	20.21	17.97	18.88	18.43	19.32	19.77
	8H	18.59	19.44	19.06	19.88	20.35	18.16	19.00	18.62	19.45	19.91
	12H	18.73	19.49	19.21	19.96	20.43	18.27	19.03	18.76	19.51	19.98
8H	4H	18.08	18.93	18.54	19.37	19.84	17.71	18.55	18.17	19.00	19.46
	6H	18.80	19.50	19.29	19.99	20.46	18.42	19.12	18.91	19.61	20.08
	8H	19.06	19.69	19.57	20.19	20.68	18.66	19.30	19.17	19.80	20.29
	12H	19.26	19.81	19.76	20.30	20.87	18.84	19.40	19.35	19.89	20.45
12H	4H	18.11	18.87	18.59	19.34	19.81	17.74	18.50	18.22	18.98	19.45
	6H	18.84	19.47	19.35	19.98	20.47	18.47	19.11	18.98	19.61	20.10
	8H	19.16	19.71	19.66	20.20	20.77	18.78	19.34	19.29	19.83	20.39