

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931528

Luminaire Tested: DFN2DS-TR4F0-080DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-080DS935-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5848.0 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 81.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931528

CATALOG NUMBER: DFN2DS-TR4F0-080DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931528

CATALOG NUMBER: DFN2DS-TR4F0-080DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2259	2259	2259
5°	2268	2231	2243
10°	2250	2194	2176
15°	2224	2129	2068
20°	2189	2036	1934
25°	2152	1931	1804
30°	2101	1822	1638
35°	2051	1705	1492
40°	2002	1582	1324
45°	1943	1446	1171
50°	1883	1307	1021
55°	1821	1158	877
60°	1750	1002	728
65°	1669	842	662
70°	1572	693	609
75°	1453	632	569
80°	1283	565	518
85°	1008	445	445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1943 cd/sqm

TEST NUMBER: P931528

CATALOG NUMBER: DFN2DS-TR4F0-080DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.5	4.6
10°-20°	731.6	12.5
20°-30°	1027.1	17.6
30°-40°	1119.6	19.1
40°-50°	1029.1	17.6
50°-60°	808.2	13.8
60°-70°	526.0	9.0
70°-80°	270.8	4.6
80°-90°	69.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2025.2	34.6
0°-40°	3144.8	53.8
0°-60°	4982.0	85.2
0°-90°	5848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5848.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2844	2844	2844	2844	2844	
5°	2844	2831	2797	2820	2813	270
15°	2704	2676	2589	2540	2514	762
25°	2455	2373	2203	2097	2059	1129
35°	2115	1984	1758	1596	1539	1324
45°	1729	1557	1287	1104	1042	1335
55°	1315	1114	836	682	633	1175
65°	888	679	448	360	352	880
75°	473	293	206	188	185	501
85°	111	56	49	49	49	133
90°	0	0	0	0	0	

TEST NUMBER: P931528

CATALOG NUMBER: DFN2DS-TR4F0-080DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2843.5	2843.5	2843.5	2843.5	2843.5
2.5°	2856.3	2843.5	2815.1	2841.0	2835.8
5°	2843.5	2830.7	2797.1	2820.3	2812.6
7.5°	2820.3	2805.0	2768.9	2779.1	2766.2
10°	2789.4	2771.4	2720.1	2712.2	2696.9
12.5°	2751.0	2727.7	2658.1	2642.8	2614.4
15°	2704.5	2676.1	2588.8	2539.9	2514.2
17.5°	2650.4	2609.2	2501.1	2444.6	2403.4
20°	2588.8	2537.2	2408.6	2344.4	2287.6
22.5°	2521.9	2462.6	2313.3	2225.9	2187.4
25°	2455.0	2372.6	2202.7	2097.4	2058.6
27.5°	2375.2	2287.6	2099.8	1978.9	1919.6
30°	2290.4	2192.3	1986.5	1855.4	1785.8
32.5°	2207.9	2089.5	1878.7	1724.1	1659.7
35°	2115.3	1984.0	1757.7	1595.6	1538.7
37.5°	2025.2	1883.6	1644.4	1466.6	1402.5
40°	1930.0	1775.7	1525.9	1343.2	1276.3
42.5°	1832.2	1667.6	1407.6	1217.2	1152.9
45°	1729.3	1556.8	1286.7	1103.8	1042.1
47.5°	1631.6	1448.9	1171.0	988.1	931.6
50°	1523.4	1340.8	1057.7	880.0	826.1
52.5°	1417.8	1224.7	949.5	779.8	730.9
55°	1314.9	1114.2	836.3	682.0	633.1
57.5°	1209.5	1003.6	736.1	591.9	550.7
60°	1101.3	895.5	630.4	499.3	458.1
62.5°	996.0	790.1	540.3	416.9	396.5
65°	887.9	679.2	447.7	360.4	352.4
67.5°	784.9	576.4	360.4	316.4	308.8
70°	676.8	476.2	298.4	272.7	262.4
72.5°	573.9	383.3	249.6	229.1	223.9
75°	473.4	293.3	205.9	187.8	185.4
77.5°	373.2	208.3	162.2	151.8	146.6
80°	280.4	149.4	123.4	113.3	113.3
82.5°	195.5	100.4	84.9	79.7	79.7
85°	110.6	56.5	48.8	48.8	48.8
87.5°	41.2	20.5	20.5	18.1	18.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931528

CATALOG NUMBER: DFN2DS-TR4F0-080DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.07	15.59	14.43	15.90	16.22	10.03	11.55	10.39	11.86	12.18
	3H	15.83	17.20	16.21	17.52	17.89	11.29	12.66	11.67	12.98	13.35
	4H	16.50	17.78	16.90	18.13	18.51	11.79	13.07	12.19	13.42	13.80
	6H	16.99	18.17	17.40	18.54	18.93	12.17	13.36	12.59	13.72	14.12
	8H	17.15	18.28	17.58	18.67	19.07	12.30	13.43	12.73	13.82	14.22
	12H	17.26	18.33	17.69	18.72	19.14	12.38	13.46	12.81	13.84	14.27
4H	2H	14.17	15.45	14.57	15.80	16.18	10.72	12.00	11.12	12.35	12.73
	3H	16.10	17.17	16.51	17.57	17.97	12.16	13.23	12.58	13.63	14.03
	4H	16.85	17.81	17.29	18.23	18.66	12.76	13.72	13.20	14.14	14.58
	6H	17.44	18.28	17.90	18.72	19.18	13.25	14.08	13.71	14.53	14.99
	8H	17.66	18.44	18.12	18.88	19.35	13.41	14.19	13.88	14.64	15.10
	12H	17.81	18.51	18.29	18.99	19.46	13.53	14.23	14.01	14.70	15.18
8H	4H	16.88	17.65	17.34	18.10	18.57	13.12	13.90	13.58	14.34	14.81
	6H	17.51	18.16	18.01	18.65	19.13	13.71	14.35	14.20	14.84	15.32
	8H	17.76	18.34	18.28	18.85	19.34	13.93	14.50	14.44	15.01	15.50
	12H	17.97	18.48	18.48	18.97	19.54	14.10	14.61	14.61	15.11	15.67
12H	4H	16.86	17.56	17.34	18.03	18.51	13.16	13.86	13.64	14.33	14.81
	6H	17.50	18.07	18.01	18.58	19.07	13.77	14.35	14.28	14.86	15.34
	8H	17.78	18.29	18.29	18.78	19.35	14.04	14.55	14.55	15.04	15.61

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7