

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930813

Luminaire Tested: DFN2DS-SQ2F0-040DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-040DS830-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3730.3 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 37.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930813

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930813

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3224	3224	3224
5°	3236	3190	3209
10°	3217	3157	3173
15°	3177	3116	3113
20°	3121	3055	3052
25°	3065	2979	2979
30°	2993	2910	2885
35°	2925	2827	2785
40°	2841	2744	2691
45°	2758	2661	2595
50°	2667	2575	2484
55°	2573	2475	2384
60°	2468	2356	2269
65°	2355	2237	2135
70°	2212	2093	1994
75°	2012	1928	1881
80°	1785	1731	1642
85°	1456	1388	1246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2758 cd/sqm

TEST NUMBER: P930813

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	3.7
10°-20°	388.3	10.4
20°-30°	570.6	15.3
30°-40°	662.7	17.8
40°-50°	661.9	17.7
50°-60°	577.1	15.5
60°-70°	426.6	11.4
70°-80°	241.4	6.5
80°-90°	63.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1096.8	29.4
0°-40°	1759.5	47.2
0°-60°	2998.6	80.4
0°-90°	3730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3730.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1461	1445	1456	1454	139
15°	1396	1387	1369	1375	1368	393
25°	1263	1252	1228	1231	1228	581
35°	1090	1076	1053	1045	1038	681
45°	887	877	856	840	835	684
55°	671	663	646	629	622	600
65°	453	444	430	417	410	447
75°	237	234	227	218	221	253
85°	58	56	55	51	49	68
90°	0	0	0	0	0	

TEST NUMBER: P930813

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1466.1	1466.1	1466.1	1466.1	1466.1
2.5°	1474.7	1467.6	1452.1	1466.1	1463.5
5°	1466.1	1460.6	1445.0	1456.2	1453.6
7.5°	1456.2	1447.9	1432.3	1443.7	1440.9
10°	1440.9	1431.0	1414.1	1425.3	1421.1
12.5°	1419.6	1411.2	1394.3	1401.4	1398.5
15°	1395.7	1387.3	1368.9	1374.6	1367.6
17.5°	1366.1	1357.7	1339.3	1346.3	1339.3
20°	1333.6	1325.2	1305.5	1309.7	1304.2
22.5°	1301.3	1288.6	1270.2	1270.2	1267.4
25°	1263.1	1251.9	1228.0	1230.7	1228.0
27.5°	1220.8	1210.9	1192.8	1188.5	1181.6
30°	1178.6	1167.3	1146.2	1142.0	1136.3
32.5°	1133.5	1125.1	1102.5	1094.0	1088.3
35°	1089.8	1075.8	1053.2	1044.7	1037.6
37.5°	1040.4	1027.7	1005.1	995.3	988.3
40°	989.8	978.4	955.8	943.2	937.6
42.5°	940.4	929.0	906.6	892.4	884.0
45°	886.8	877.0	855.7	840.4	834.6
47.5°	834.6	824.7	802.2	786.7	778.3
50°	779.6	772.5	752.8	733.1	726.0
52.5°	726.0	716.2	697.9	682.4	672.5
55°	671.2	662.6	645.7	628.8	621.8
57.5°	616.1	609.1	590.6	573.8	568.1
60°	561.1	555.5	535.8	520.3	516.0
62.5°	507.5	497.7	483.6	469.5	463.8
65°	452.6	444.1	430.0	417.3	410.3
67.5°	396.2	389.0	376.5	366.6	361.0
70°	344.0	338.4	325.6	315.8	310.2
72.5°	290.5	284.8	277.8	267.9	263.7
75°	236.8	234.1	226.9	218.5	221.4
77.5°	188.9	183.2	180.4	176.2	172.0
80°	141.0	139.5	136.7	132.5	129.7
82.5°	95.9	95.9	94.6	88.8	88.8
85°	57.7	56.4	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.5	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930813

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.35	16.96	15.71	17.27	17.59	14.91	16.52	15.27	16.83	17.14
	3H	17.10	18.55	17.48	18.88	19.24	16.61	18.06	16.99	18.39	18.75
	4H	17.75	19.12	18.14	19.46	19.84	17.25	18.62	17.65	18.97	19.34
	6H	18.22	19.48	18.63	19.85	20.24	17.71	18.98	18.13	19.35	19.74
	8H	18.36	19.57	18.78	19.96	20.36	17.86	19.07	18.28	19.46	19.85
	12H	18.45	19.61	18.88	19.99	20.42	17.94	19.10	18.37	19.48	19.91
4H	2H	15.91	17.28	16.31	17.63	18.00	15.56	16.93	15.96	17.27	17.65
	3H	17.89	19.03	18.29	19.43	19.83	17.48	18.62	17.89	19.02	19.42
	4H	18.66	19.70	19.09	20.11	20.55	18.24	19.27	18.67	19.69	20.12
	6H	19.26	20.16	19.71	20.60	21.06	18.83	19.73	19.28	20.17	20.63
	8H	19.45	20.29	19.91	20.74	21.20	19.01	19.86	19.47	20.30	20.76
	12H	19.58	20.34	20.06	20.82	21.28	19.13	19.89	19.61	20.36	20.83
8H	4H	18.94	19.78	19.40	20.22	20.69	18.56	19.41	19.02	19.85	20.32
	6H	19.65	20.35	20.14	20.84	21.32	19.27	19.97	19.76	20.46	20.93
	8H	19.91	20.54	20.42	21.05	21.53	19.52	20.15	20.03	20.65	21.14
	12H	20.11	20.67	20.62	21.16	21.72	19.70	20.25	20.20	20.74	21.30
12H	4H	18.96	19.72	19.44	20.20	20.67	18.60	19.36	19.08	19.83	20.30
	6H	19.69	20.33	20.20	20.83	21.32	19.33	19.96	19.84	20.46	20.95
	8H	20.01	20.57	20.52	21.06	21.62	19.63	20.19	20.14	20.68	21.24