

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930814

Luminaire Tested: DFN2DS-SQ2F0-040DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-040DS830-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3202.8 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 37.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930814
CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P930814

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3424	3424	3424
5°	3437	3381	3400
10°	3411	3326	3298
15°	3372	3228	3135
20°	3318	3087	2932
25°	3262	2927	2735
30°	3185	2762	2483
35°	3110	2584	2262
40°	3034	2399	2007
45°	2945	2191	1775
50°	2854	1981	1548
55°	2761	1756	1330
60°	2653	1518	1103
65°	2530	1276	1004
70°	2383	1051	924
75°	2202	958	862
80°	1944	855	786
85°	1529	676	676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2945 cd/sqm



TEST NUMBER: P930814

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-RL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	4.6
10°-20°	400.7	12.5
20°-30°	562.5	17.6
30°-40°	613.2	19.1
40°-50°	563.6	17.6
50°-60°	442.6	13.8
60°-70°	288.1	9.0
70°-80°	148.3	4.6
80°-90°	37.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.1	34.6
0°-40°	1722.3	53.8
0°-60°	2728.5	85.2
0°-90°	3202.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3202.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1557	1557	1557	1557	1557	
5°	1557	1550	1532	1545	1540	148
15°	1481	1466	1418	1391	1377	417
25°	1344	1299	1206	1149	1127	618
35°	1159	1087	963	874	843	725
45°	947	853	705	605	571	731
55°	720	610	458	374	347	644
65°	486	372	245	197	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	73
90°	0	0	0	0	0	



TEST NUMBER: P930814

CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1557.3	1557.3	1557.3	1557.3	1557.3
2.5°	1564.4	1557.3	1541.8	1556.0	1553.1
5°	1557.3	1550.2	1531.9	1544.6	1540.5
7.5°	1544.6	1536.2	1516.5	1522.0	1515.0
10°	1527.7	1517.8	1489.7	1485.3	1477.1
12.5°	1506.6	1493.9	1455.8	1447.4	1431.8
15°	1481.2	1465.7	1417.8	1391.1	1377.0
17.5°	1451.6	1429.0	1369.8	1338.9	1316.3
20°	1417.8	1389.5	1319.1	1283.9	1252.9
22.5°	1381.2	1348.8	1266.9	1219.0	1198.0
25°	1344.5	1299.4	1206.3	1148.7	1127.4
27.5°	1300.9	1252.9	1150.0	1083.8	1051.3
30°	1254.4	1200.7	1087.9	1016.1	978.1
32.5°	1209.2	1144.3	1028.9	944.3	908.9
35°	1158.6	1086.6	962.6	873.8	842.7
37.5°	1109.2	1031.6	900.6	803.2	768.1
40°	1057.0	972.5	835.7	735.7	699.1
42.5°	1003.4	913.3	770.9	666.6	631.4
45°	947.1	852.6	704.7	604.6	570.8
47.5°	893.6	793.5	641.3	541.2	510.2
50°	834.3	734.3	579.2	481.9	452.4
52.5°	776.5	670.8	520.1	427.0	400.3
55°	720.2	610.2	458.0	373.5	346.8
57.5°	662.4	549.7	403.1	324.1	301.6
60°	603.2	490.4	345.2	273.5	250.9
62.5°	545.5	432.8	295.9	228.3	217.1
65°	486.3	372.0	245.2	197.3	193.0
67.5°	429.9	315.7	197.3	173.3	169.1
70°	370.7	260.7	163.4	149.4	143.7
72.5°	314.3	210.0	136.7	125.5	122.6
75°	259.2	160.6	112.8	102.9	101.5
77.5°	204.4	114.1	88.8	83.2	80.3
80°	153.5	81.8	67.5	62.1	62.1
82.5°	107.1	55.0	46.5	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930814
 CATALOG NUMBER: DFN2DS-SQ2F0-040DS830-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.51	17.03	15.88	17.35	17.66	11.47	12.99	11.84	13.31	13.62
	3H	17.28	18.64	17.65	18.97	19.33	12.74	14.10	13.11	14.43	14.79
	4H	17.94	19.22	18.34	19.57	19.95	13.24	14.52	13.64	14.87	15.25
	6H	18.43	19.61	18.84	19.98	20.37	13.62	14.80	14.03	15.17	15.56
	8H	18.60	19.72	19.02	20.11	20.51	13.74	14.87	14.17	15.26	15.66
	12H	18.70	19.78	19.13	20.16	20.59	13.83	14.90	14.26	15.29	15.71
4H	2H	15.62	16.90	16.02	17.24	17.62	12.17	13.45	12.57	13.80	14.17
	3H	17.55	18.61	17.96	19.01	19.41	13.61	14.67	14.02	15.07	15.47
	4H	18.30	19.25	18.73	19.67	20.11	14.21	15.17	14.64	15.58	16.02
	6H	18.89	19.72	19.35	20.16	20.62	14.70	15.53	15.16	15.97	16.43
	8H	19.10	19.88	19.57	20.33	20.79	14.86	15.64	15.32	16.08	16.55
	12H	19.26	19.95	19.74	20.43	20.90	14.98	15.67	15.46	16.15	16.62
8H	4H	18.32	19.10	18.79	19.54	20.01	14.56	15.34	15.03	15.79	16.25
	6H	18.96	19.60	19.46	20.09	20.57	15.15	15.79	15.65	16.28	16.76
	8H	19.21	19.79	19.72	20.30	20.78	15.37	15.95	15.89	16.46	16.95
	12H	19.41	19.92	19.92	20.42	20.98	15.55	16.06	16.06	16.55	17.12
12H	4H	18.31	19.00	18.79	19.48	19.95	14.61	15.30	15.09	15.78	16.25
	6H	18.94	19.52	19.45	20.03	20.52	15.21	15.79	15.73	16.30	16.79
	8H	19.22	19.73	19.73	20.23	20.79	15.49	16.00	16.00	16.49	17.05