

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931478

Luminaire Tested: DFN2DS-TR4F0-050DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931478
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-050DS950-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4016.3 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 48.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931478

CATALOG NUMBER: DFN2DS-TR4F0-050DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931478

CATALOG NUMBER: DFN2DS-TR4F0-050DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1551	1551	1551
5°	1557	1532	1540
10°	1545	1507	1494
15°	1528	1462	1420
20°	1503	1398	1328
25°	1478	1326	1239
30°	1443	1252	1125
35°	1409	1171	1025
40°	1375	1087	909
45°	1334	993	804
50°	1293	898	701
55°	1251	795	602
60°	1202	688	500
65°	1146	578	455
70°	1080	476	419
75°	998	434	391
80°	881	388	356
85°	693	305	305

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1334 cd/sqm

TEST NUMBER: P931478

CATALOG NUMBER: DFN2DS-TR4F0-050DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	4.6
10°-20°	502.4	12.5
20°-30°	705.4	17.6
30°-40°	768.9	19.1
40°-50°	706.7	17.6
50°-60°	555.0	13.8
60°-70°	361.3	9.0
70°-80°	186.0	4.6
80°-90°	47.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1390.9	34.6
0°-40°	2159.8	53.8
0°-60°	3421.5	85.2
0°-90°	4016.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4016.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1953	1953	1953	1953	1953	
5°	1953	1944	1921	1937	1932	185
15°	1857	1838	1778	1744	1727	523
25°	1686	1629	1513	1440	1414	775
35°	1453	1363	1207	1096	1057	909
45°	1188	1069	884	758	716	917
55°	903	765	574	468	435	807
65°	610	466	308	248	242	604
75°	325	201	141	129	127	344
85°	76	39	34	34	34	91
90°	0	0	0	0	0	

TEST NUMBER: P931478

CATALOG NUMBER: DFN2DS-TR4F0-050DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1952.8	1952.8	1952.8	1952.8	1952.8
2.5°	1961.6	1952.8	1933.4	1951.1	1947.6
5°	1952.8	1944.1	1921.0	1936.9	1931.7
7.5°	1936.9	1926.4	1901.6	1908.6	1899.7
10°	1915.7	1903.3	1868.1	1862.7	1852.1
12.5°	1889.2	1873.4	1825.6	1815.1	1795.5
15°	1857.4	1837.9	1777.9	1744.4	1726.7
17.5°	1820.3	1792.0	1717.7	1678.9	1650.5
20°	1777.9	1742.5	1654.1	1610.1	1571.1
22.5°	1732.0	1691.3	1588.7	1528.7	1502.3
25°	1686.0	1629.4	1512.8	1440.4	1413.7
27.5°	1631.3	1571.1	1442.1	1359.0	1318.4
30°	1573.0	1505.7	1364.3	1274.2	1226.4
32.5°	1516.3	1435.0	1290.2	1184.1	1139.9
35°	1452.7	1362.6	1207.1	1095.7	1056.8
37.5°	1390.9	1293.6	1129.4	1007.3	963.2
40°	1325.5	1219.5	1047.9	922.5	876.6
42.5°	1258.4	1145.2	966.7	835.9	791.8
45°	1187.7	1069.2	883.7	758.1	715.6
47.5°	1120.5	995.1	804.2	678.6	639.8
50°	1046.3	920.8	726.4	604.3	567.4
52.5°	973.7	841.1	652.1	535.5	502.0
55°	903.0	765.2	574.3	468.3	434.8
57.5°	830.7	689.3	505.5	406.5	378.2
60°	756.4	615.0	432.9	342.9	314.6
62.5°	684.0	542.6	371.1	286.3	272.3
65°	609.7	466.5	307.5	247.5	242.1
67.5°	539.0	395.9	247.5	217.4	212.1
70°	464.8	327.0	205.0	187.3	180.2
72.5°	394.2	263.3	171.4	157.3	153.8
75°	325.2	201.4	141.4	129.0	127.3
77.5°	256.3	143.1	111.4	104.2	100.6
80°	192.6	102.5	84.8	77.8	77.8
82.5°	134.3	69.0	58.3	54.7	54.7
85°	76.0	38.8	33.5	33.5	33.5
87.5°	28.4	14.1	14.1	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931478

CATALOG NUMBER: DFN2DS-TR4F0-050DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.76	14.28	13.13	14.60	14.91	8.72	10.24	9.09	10.56	10.87
	3H	14.53	15.89	14.90	16.22	16.58	9.99	11.35	10.36	11.68	12.04
	4H	15.19	16.47	15.59	16.82	17.20	10.49	11.77	10.89	12.12	12.50
	6H	15.68	16.86	16.09	17.23	17.62	10.87	12.05	11.28	12.42	12.81
	8H	15.85	16.97	16.27	17.36	17.76	10.99	12.12	11.42	12.51	12.91
	12H	15.95	17.03	16.38	17.41	17.84	11.07	12.15	11.50	12.53	12.96
4H	2H	12.86	14.15	13.26	14.49	14.87	9.42	10.70	9.82	11.05	11.42
	3H	14.80	15.86	15.21	16.26	16.66	10.86	11.92	11.27	12.32	12.72
	4H	15.55	16.50	15.98	16.92	17.36	11.46	12.42	11.89	12.83	13.27
	6H	16.14	16.97	16.60	17.41	17.87	11.95	12.78	12.40	13.22	13.68
	8H	16.35	17.13	16.82	17.58	18.04	12.11	12.89	12.57	13.33	13.80
	12H	16.51	17.20	16.99	17.68	18.15	12.23	12.92	12.71	13.40	13.87
8H	4H	15.57	16.35	16.04	16.79	17.26	11.81	12.59	12.28	13.03	13.50
	6H	16.21	16.85	16.71	17.34	17.82	12.40	13.04	12.90	13.53	14.01
	8H	16.46	17.04	16.97	17.55	18.03	12.62	13.20	13.13	13.71	14.19
	12H	16.66	17.17	17.17	17.67	18.23	12.80	13.31	13.31	13.80	14.37
12H	4H	15.56	16.25	16.04	16.73	17.20	11.86	12.55	12.34	13.03	13.50
	6H	16.19	16.77	16.70	17.28	17.77	12.46	13.04	12.98	13.55	14.04
	8H	16.47	16.98	16.98	17.48	18.04	12.74	13.25	13.25	13.74	14.30