

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930903

Luminaire Tested: DFN2DS-SQ3F0-040DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-040DS830-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3730.3 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930903

CATALOG NUMBER: DFN2DS-SQ3F0-040DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930903

CATALOG NUMBER: DFN2DS-SQ3F0-040DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1680	1680	1680
5°	1686	1662	1672
10°	1676	1645	1653
15°	1656	1624	1622
20°	1626	1592	1590
25°	1597	1553	1553
30°	1559	1516	1503
35°	1524	1473	1451
40°	1480	1430	1402
45°	1437	1387	1352
50°	1390	1342	1294
55°	1341	1290	1242
60°	1286	1228	1182
65°	1227	1166	1112
70°	1152	1091	1039
75°	1048	1004	980
80°	930	902	856
85°	759	723	649

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1437 cd/sqm

TEST NUMBER: P930903

CATALOG NUMBER: DFN2DS-SQ3F0-040DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	3.7
10°-20°	388.3	10.4
20°-30°	570.6	15.3
30°-40°	662.7	17.8
40°-50°	661.9	17.7
50°-60°	577.1	15.5
60°-70°	426.6	11.4
70°-80°	241.4	6.5
80°-90°	63.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1096.8	29.4
0°-40°	1759.5	47.2
0°-60°	2998.6	80.4
0°-90°	3730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3730.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1461	1445	1456	1454	139
15°	1396	1387	1369	1375	1368	393
25°	1263	1252	1228	1231	1228	581
35°	1090	1076	1053	1045	1038	681
45°	887	877	856	840	835	684
55°	671	663	646	629	622	600
65°	453	444	430	417	410	447
75°	237	234	227	218	221	253
85°	58	56	55	51	49	68
90°	0	0	0	0	0	

TEST NUMBER: P930903

CATALOG NUMBER: DFN2DS-SQ3F0-040DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1466.1	1466.1	1466.1	1466.1	1466.1
2.5°	1474.7	1467.6	1452.1	1466.1	1463.5
5°	1466.1	1460.6	1445.0	1456.2	1453.6
7.5°	1456.2	1447.9	1432.3	1443.7	1440.9
10°	1440.9	1431.0	1414.1	1425.3	1421.1
12.5°	1419.6	1411.2	1394.3	1401.4	1398.5
15°	1395.7	1387.3	1368.9	1374.6	1367.6
17.5°	1366.1	1357.7	1339.3	1346.3	1339.3
20°	1333.6	1325.2	1305.5	1309.7	1304.2
22.5°	1301.3	1288.6	1270.2	1270.2	1267.4
25°	1263.1	1251.9	1228.0	1230.7	1228.0
27.5°	1220.8	1210.9	1192.8	1188.5	1181.6
30°	1178.6	1167.3	1146.2	1142.0	1136.3
32.5°	1133.5	1125.1	1102.5	1094.0	1088.3
35°	1089.8	1075.8	1053.2	1044.7	1037.6
37.5°	1040.4	1027.7	1005.1	995.3	988.3
40°	989.8	978.4	955.8	943.2	937.6
42.5°	940.4	929.0	906.6	892.4	884.0
45°	886.8	877.0	855.7	840.4	834.6
47.5°	834.6	824.7	802.2	786.7	778.3
50°	779.6	772.5	752.8	733.1	726.0
52.5°	726.0	716.2	697.9	682.4	672.5
55°	671.2	662.6	645.7	628.8	621.8
57.5°	616.1	609.1	590.6	573.8	568.1
60°	561.1	555.5	535.8	520.3	516.0
62.5°	507.5	497.7	483.6	469.5	463.8
65°	452.6	444.1	430.0	417.3	410.3
67.5°	396.2	389.0	376.5	366.6	361.0
70°	344.0	338.4	325.6	315.8	310.2
72.5°	290.5	284.8	277.8	267.9	263.7
75°	236.8	234.1	226.9	218.5	221.4
77.5°	188.9	183.2	180.4	176.2	172.0
80°	141.0	139.5	136.7	132.5	129.7
82.5°	95.9	95.9	94.6	88.8	88.8
85°	57.7	56.4	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.5	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930903

CATALOG NUMBER: DFN2DS-SQ3F0-040DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.09	14.70	13.45	15.01	15.32	12.64	14.25	13.01	14.57	14.88
	3H	14.83	16.29	15.21	16.62	16.98	14.34	15.80	14.72	16.13	16.49
	4H	15.48	16.85	15.88	17.20	17.57	14.99	16.36	15.39	16.70	17.08
	6H	15.95	17.22	16.36	17.58	17.97	15.45	16.72	15.86	17.08	17.47
	8H	16.09	17.30	16.52	17.69	18.09	15.59	16.80	16.02	17.19	17.59
	12H	16.18	17.34	16.61	17.73	18.15	15.67	16.83	16.10	17.21	17.64
4H	2H	13.65	15.01	14.04	15.36	15.74	13.29	14.66	13.69	15.01	15.39
	3H	15.62	16.77	16.03	17.16	17.56	15.21	16.36	15.62	16.76	17.16
	4H	16.40	17.43	16.83	17.85	18.28	15.97	17.01	16.40	17.42	17.86
	6H	16.99	17.90	17.45	18.34	18.79	16.56	17.47	17.02	17.91	18.36
	8H	17.18	18.03	17.64	18.47	18.94	16.74	17.59	17.21	18.03	18.50
	12H	17.31	18.07	17.79	18.55	19.02	16.86	17.62	17.34	18.10	18.57
8H	4H	16.67	17.52	17.13	17.96	18.42	16.30	17.14	16.76	17.59	18.05
	6H	17.38	18.09	17.88	18.58	19.05	17.00	17.71	17.50	18.19	18.67
	8H	17.64	18.27	18.15	18.78	19.27	17.25	17.88	17.76	18.39	18.88
	12H	17.84	18.40	18.35	18.89	19.45	17.43	17.99	17.94	18.48	19.04
12H	4H	16.70	17.46	17.18	17.93	18.40	16.33	17.09	16.81	17.57	18.04
	6H	17.43	18.06	17.94	18.57	19.05	17.06	17.69	17.57	18.20	18.69
	8H	17.74	18.30	18.25	18.79	19.35	17.37	17.92	17.87	18.41	18.98