

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931495

Luminaire Tested: DFN2DS-TR4F0-060DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-060DS950-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.3 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 59.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931495

CATALOG NUMBER: DFN2DS-TR4F0-060DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931495

CATALOG NUMBER: DFN2DS-TR4F0-060DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1753	1753	1753
5°	1759	1734	1744
10°	1749	1717	1725
15°	1727	1694	1693
20°	1697	1661	1659
25°	1666	1620	1620
30°	1627	1582	1569
35°	1591	1537	1514
40°	1544	1492	1463
45°	1499	1447	1411
50°	1450	1400	1350
55°	1399	1346	1296
60°	1341	1281	1234
65°	1280	1216	1161
70°	1202	1138	1084
75°	1094	1048	1022
80°	971	941	893
85°	791	755	677

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1499 cd/sqm

TEST NUMBER: P931495

CATALOG NUMBER: DFN2DS-TR4F0-060DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	3.7
10°-20°	584.3	10.4
20°-30°	858.6	15.3
30°-40°	997.2	17.8
40°-50°	996.0	17.7
50°-60°	868.5	15.5
60°-70°	642.0	11.4
70°-80°	363.2	6.5
80°-90°	95.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1650.5	29.4
0°-40°	2647.7	47.2
0°-60°	4512.2	80.4
0°-90°	5613.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5613.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2206	2206	2206	2206	2206	
5°	2206	2198	2174	2191	2187	209
15°	2100	2088	2060	2068	2058	592
25°	1901	1884	1848	1852	1848	875
35°	1640	1619	1585	1572	1561	1024
45°	1334	1320	1288	1264	1256	1030
55°	1010	997	972	946	936	903
65°	681	668	647	628	617	673
75°	356	352	341	329	333	380
85°	87	85	83	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P931495

CATALOG NUMBER: DFN2DS-TR4F0-060DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2206.2	2206.2	2206.2	2206.2	2206.2
2.5°	2219.0	2208.5	2185.0	2206.2	2202.1
5°	2206.2	2197.9	2174.4	2191.4	2187.3
7.5°	2191.4	2178.8	2155.4	2172.5	2168.2
10°	2168.2	2153.4	2127.9	2144.8	2138.4
12.5°	2136.3	2123.6	2098.2	2108.8	2104.5
15°	2100.2	2087.6	2059.9	2068.5	2057.9
17.5°	2055.7	2043.1	2015.4	2025.9	2015.4
20°	2006.8	1994.2	1964.5	1970.8	1962.5
22.5°	1958.2	1939.0	1911.4	1911.4	1907.1
25°	1900.8	1884.0	1847.9	1851.9	1847.9
27.5°	1837.1	1822.2	1794.7	1788.5	1777.9
30°	1773.7	1756.5	1724.8	1718.5	1709.9
32.5°	1705.6	1693.1	1659.0	1646.2	1637.7
35°	1640.0	1618.8	1584.8	1571.9	1561.3
37.5°	1565.7	1546.5	1512.6	1497.6	1487.1
40°	1489.3	1472.2	1438.3	1419.4	1410.8
42.5°	1415.0	1397.9	1364.2	1342.8	1330.2
45°	1334.5	1319.6	1287.7	1264.5	1255.9
47.5°	1255.9	1241.1	1207.1	1183.7	1171.0
50°	1173.1	1162.5	1132.9	1103.1	1092.5
52.5°	1092.5	1077.7	1050.2	1026.8	1012.0
55°	1009.9	997.1	971.6	946.2	935.6
57.5°	927.1	916.6	888.9	863.4	854.8
60°	844.3	835.9	806.3	782.8	776.5
62.5°	763.7	748.8	727.6	706.5	698.0
65°	681.1	668.3	647.1	628.0	617.4
67.5°	596.2	585.4	566.5	551.7	543.1
70°	517.7	509.2	490.0	475.1	466.8
72.5°	437.1	428.6	418.0	403.1	396.8
75°	356.3	352.3	341.4	328.9	333.1
77.5°	284.3	275.8	271.4	265.2	258.8
80°	212.2	210.0	205.7	199.4	195.1
82.5°	144.3	144.3	142.2	133.7	133.7
85°	86.8	84.9	82.8	76.3	74.3
87.5°	38.3	34.0	29.7	23.4	21.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931495

CATALOG NUMBER: DFN2DS-TR4F0-060DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.23	14.84	13.60	15.16	15.47	12.79	14.40	13.15	14.71	15.03
	3H	14.98	16.44	15.36	16.76	17.12	14.49	15.95	14.87	16.27	16.63
	4H	15.63	17.00	16.03	17.35	17.72	15.13	16.50	15.53	16.85	17.23
	6H	16.10	17.37	16.51	17.73	18.12	15.60	16.86	16.01	17.23	17.62
	8H	16.24	17.45	16.67	17.84	18.24	15.74	16.95	16.16	17.34	17.74
	12H	16.33	17.49	16.76	17.87	18.30	15.82	16.98	16.25	17.36	17.79
4H	2H	13.79	15.16	14.19	15.51	15.89	13.44	14.81	13.84	15.16	15.53
	3H	15.77	16.91	16.18	17.31	17.71	15.36	16.51	15.77	16.90	17.30
	4H	16.54	17.58	16.98	17.99	18.43	16.12	17.16	16.55	17.57	18.01
	6H	17.14	18.05	17.60	18.49	18.94	16.71	17.61	17.16	18.05	18.51
	8H	17.33	18.18	17.79	18.62	19.08	16.89	17.74	17.35	18.18	18.65
	12H	17.46	18.22	17.94	18.70	19.17	17.01	17.77	17.49	18.25	18.72
8H	4H	16.82	17.66	17.28	18.11	18.57	16.44	17.29	16.90	17.73	18.20
	6H	17.53	18.24	18.03	18.72	19.20	17.15	17.85	17.64	18.34	18.82
	8H	17.79	18.42	18.30	18.93	19.42	17.40	18.03	17.91	18.54	19.02
	12H	17.99	18.55	18.50	19.04	19.60	17.58	18.14	18.08	18.63	19.19
12H	4H	16.84	17.60	17.32	18.08	18.55	16.48	17.24	16.96	17.71	18.18
	6H	17.58	18.21	18.09	18.72	19.20	17.21	17.84	17.72	18.35	18.83
	8H	17.89	18.45	18.40	18.94	19.50	17.51	18.07	18.02	18.56	19.12

END OF REPORT