

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930994

Luminaire Tested: DFN2DS-SQ3F0-090DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930994
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-090DS830-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7206.4 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 93.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930994

CATALOG NUMBER: DFN2DS-SQ3F0-090DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930994

CATALOG NUMBER: DFN2DS-SQ3F0-090DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4015	4015	4015
5°	4030	3964	3986
10°	3999	3900	3867
15°	3953	3784	3675
20°	3890	3619	3437
25°	3825	3432	3207
30°	3734	3239	2912
35°	3646	3030	2652
40°	3557	2812	2353
45°	3453	2569	2081
50°	3346	2323	1815
55°	3237	2059	1559
60°	3110	1780	1294
65°	2966	1496	1178
70°	2794	1232	1083
75°	2583	1123	1011
80°	2280	1003	921
85°	1791	791	791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3453 cd/sqm

TEST NUMBER: P930994

CATALOG NUMBER: DFN2DS-SQ3F0-090DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.4	4.6
10°-20°	901.5	12.5
20°-30°	1265.7	17.6
30°-40°	1379.7	19.1
40°-50°	1268.1	17.6
50°-60°	995.9	13.8
60°-70°	648.2	9.0
70°-80°	333.7	4.6
80°-90°	85.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2495.6	34.6
0°-40°	3875.3	53.8
0°-60°	6139.3	85.2
0°-90°	7206.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7206.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3504	3504	3504	3504	3504	
5°	3504	3488	3447	3475	3466	332
15°	3333	3298	3190	3130	3098	939
25°	3025	2924	2714	2584	2537	1391
35°	2607	2445	2166	1966	1896	1632
45°	2131	1918	1586	1360	1284	1646
55°	1620	1373	1030	840	780	1448
65°	1094	837	552	444	434	1085
75°	583	361	254	231	228	617
85°	136	70	60	60	60	163
90°	0	0	0	0	0	

TEST NUMBER: P930994

CATALOG NUMBER: DFN2DS-SQ3F0-090DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3504.0	3504.0	3504.0	3504.0	3504.0
2.5°	3519.8	3504.0	3468.9	3500.9	3494.5
5°	3504.0	3488.1	3446.8	3475.3	3465.9
7.5°	3475.3	3456.5	3412.1	3424.5	3408.7
10°	3437.4	3415.1	3351.9	3342.1	3323.3
12.5°	3389.9	3361.3	3275.5	3256.7	3221.6
15°	3332.7	3297.8	3190.1	3129.8	3098.2
17.5°	3266.1	3215.3	3082.0	3012.4	2961.6
20°	3190.1	3126.5	2968.0	2888.9	2818.9
22.5°	3107.7	3034.7	2850.6	2742.9	2695.5
25°	3025.2	2923.6	2714.4	2584.5	2536.7
27.5°	2927.0	2818.9	2587.5	2438.5	2365.5
30°	2822.3	2701.6	2447.9	2286.4	2200.6
32.5°	2720.7	2574.7	2315.0	2124.6	2045.2
35°	2606.7	2444.9	2165.9	1966.1	1896.2
37.5°	2495.6	2321.1	2026.3	1807.3	1728.3
40°	2378.3	2188.2	1880.3	1655.3	1572.9
42.5°	2257.8	2055.0	1734.6	1499.9	1420.7
45°	2131.0	1918.4	1585.6	1360.2	1284.1
47.5°	2010.5	1785.5	1443.0	1217.5	1147.9
50°	1877.3	1652.2	1303.4	1084.3	1018.0
52.5°	1747.1	1509.3	1170.2	960.8	900.6
55°	1620.2	1373.0	1030.5	840.5	780.2
57.5°	1490.4	1236.8	907.1	729.4	678.6
60°	1357.1	1103.5	776.9	615.3	564.5
62.5°	1227.3	973.7	665.8	513.8	488.5
65°	1094.0	837.1	551.7	444.1	434.4
67.5°	967.2	710.2	444.1	389.9	380.5
70°	834.0	586.8	367.8	336.1	323.3
72.5°	707.2	472.3	307.5	282.2	275.9
75°	583.4	361.4	253.7	231.4	228.4
77.5°	459.9	256.7	199.8	187.1	180.7
80°	345.5	184.1	152.0	139.6	139.6
82.5°	240.9	123.8	104.7	98.3	98.3
85°	136.2	69.6	60.2	60.2	60.2
87.5°	50.8	25.2	25.2	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930994

CATALOG NUMBER: DFN2DS-SQ3F0-090DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.06	17.59	16.43	17.90	18.21	12.02	13.55	12.39	13.86	14.17
	3H	17.83	19.19	18.21	19.52	19.88	13.29	14.66	13.67	14.98	15.34
	4H	18.50	19.78	18.90	20.13	20.50	13.79	15.07	14.19	15.42	15.80
	6H	18.98	20.17	19.40	20.53	20.93	14.17	15.36	14.58	15.72	16.11
	8H	19.15	20.28	19.58	20.67	21.07	14.30	15.42	14.72	15.81	16.21
	12H	19.25	20.33	19.68	20.71	21.14	14.38	15.46	14.81	15.84	16.27
4H	2H	16.17	17.45	16.57	17.80	18.18	12.72	14.00	13.12	14.35	14.73
	3H	18.10	19.16	18.51	19.56	19.97	14.16	15.23	14.57	15.63	16.03
	4H	18.85	19.81	19.28	20.22	20.66	14.76	15.72	15.19	16.13	16.57
	6H	19.44	20.27	19.90	20.72	21.18	15.25	16.08	15.71	16.53	16.98
	8H	19.66	20.43	20.12	20.88	21.35	15.41	16.19	15.88	16.63	17.10
	12H	19.81	20.51	20.29	20.98	21.45	15.53	16.22	16.01	16.70	17.17
8H	4H	18.87	19.65	19.34	20.10	20.56	15.12	15.89	15.58	16.34	16.80
	6H	19.51	20.16	20.01	20.65	21.12	15.70	16.35	16.20	16.84	17.31
	8H	19.76	20.34	20.28	20.85	21.34	15.92	16.50	16.44	17.01	17.50
	12H	19.97	20.48	20.48	20.97	21.53	16.10	16.61	16.61	17.11	17.67
12H	4H	18.86	19.55	19.34	20.03	20.50	15.16	15.85	15.64	16.33	16.80
	6H	19.49	20.07	20.01	20.58	21.07	15.77	16.34	16.28	16.85	17.34
	8H	19.78	20.29	20.29	20.78	21.34	16.04	16.55	16.55	17.04	17.61