

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931531

Luminaire Tested: DFN2DS-TR4F0-080DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-080DS950-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7484.4 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 81.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931531

CATALOG NUMBER: DFN2DS-TR4F0-080DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931531

CATALOG NUMBER: DFN2DS-TR4F0-080DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2337	2337	2337
5°	2346	2312	2326
10°	2332	2289	2300
15°	2303	2259	2257
20°	2262	2214	2212
25°	2222	2160	2160
30°	2169	2110	2091
35°	2121	2049	2019
40°	2059	1989	1951
45°	1999	1929	1881
50°	1933	1867	1800
55°	1865	1794	1728
60°	1789	1708	1645
65°	1707	1622	1547
70°	1603	1518	1446
75°	1458	1398	1363
80°	1295	1255	1190
85°	1056	1007	902

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1999 cd/sqm

TEST NUMBER: P931531

CATALOG NUMBER: DFN2DS-TR4F0-080DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.9	3.7
10°-20°	779.0	10.4
20°-30°	1144.8	15.3
30°-40°	1329.6	17.8
40°-50°	1328.0	17.7
50°-60°	1158.0	15.5
60°-70°	856.0	11.4
70°-80°	484.3	6.5
80°-90°	127.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2200.7	29.4
0°-40°	3530.3	47.2
0°-60°	6016.3	80.4
0°-90°	7484.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7484.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2942	2942	2942	2942	2942	
5°	2942	2930	2899	2922	2916	279
15°	2800	2784	2746	2758	2744	789
25°	2534	2512	2464	2469	2464	1166
35°	2186	2158	2113	2096	2082	1365
45°	1779	1760	1717	1686	1675	1373
55°	1346	1329	1296	1262	1248	1204
65°	908	891	863	837	823	898
75°	475	470	455	438	444	507
85°	116	113	110	102	99	136
90°	0	0	0	0	0	

TEST NUMBER: P931531

CATALOG NUMBER: DFN2DS-TR4F0-080DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2941.6	2941.6	2941.6	2941.6	2941.6
2.5°	2958.7	2944.6	2913.4	2941.6	2936.2
5°	2941.6	2930.5	2899.4	2921.8	2916.5
7.5°	2921.8	2905.0	2873.8	2896.6	2890.9
10°	2890.9	2871.1	2837.2	2859.7	2851.3
12.5°	2848.3	2831.5	2797.6	2811.7	2806.0
15°	2800.3	2783.5	2746.5	2758.0	2743.9
17.5°	2740.9	2724.1	2687.1	2701.3	2687.1
20°	2675.8	2658.9	2619.4	2627.8	2616.6
22.5°	2610.9	2585.4	2548.5	2548.5	2542.8
25°	2534.4	2511.9	2463.9	2469.3	2463.9
27.5°	2449.4	2429.7	2393.0	2384.6	2370.5
30°	2364.9	2342.0	2299.8	2291.3	2279.9
32.5°	2274.2	2257.4	2212.1	2195.0	2183.6
35°	2186.5	2158.4	2113.0	2095.9	2081.8
37.5°	2087.5	2062.0	2016.7	1996.9	1982.8
40°	1985.8	1963.0	1917.7	1892.5	1881.0
42.5°	1886.8	1863.9	1818.9	1790.4	1773.7
45°	1779.3	1759.5	1716.9	1686.0	1674.6
47.5°	1674.6	1654.8	1609.4	1578.2	1561.4
50°	1564.2	1550.1	1510.4	1470.8	1456.7
52.5°	1456.7	1436.9	1400.3	1369.1	1349.3
55°	1346.5	1329.4	1295.6	1261.7	1247.5
57.5°	1236.2	1222.1	1185.1	1151.2	1139.8
60°	1125.7	1114.6	1074.9	1043.8	1035.3
62.5°	1018.2	998.5	970.2	942.1	930.6
65°	908.1	891.0	862.8	837.3	823.2
67.5°	794.9	780.6	755.3	735.6	724.2
70°	690.2	678.8	653.4	633.5	622.4
72.5°	582.8	571.4	557.3	537.5	529.1
75°	475.1	469.7	455.3	438.5	444.2
77.5°	379.0	367.6	361.9	353.5	345.1
80°	283.0	280.0	274.3	265.9	260.2
82.5°	192.4	192.4	189.7	178.2	178.2
85°	115.9	113.1	110.5	101.8	99.0
87.5°	51.0	45.4	39.6	31.2	28.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931531

CATALOG NUMBER: DFN2DS-TR4F0-080DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.23	15.84	14.60	16.16	16.47	13.79	15.40	14.15	15.71	16.03
	3H	15.98	17.44	16.36	17.76	18.12	15.49	16.95	15.87	17.27	17.63
	4H	16.63	18.00	17.03	18.35	18.72	16.13	17.50	16.53	17.85	18.23
	6H	17.10	18.37	17.51	18.73	19.12	16.60	17.86	17.01	18.23	18.62
	8H	17.24	18.45	17.67	18.84	19.24	16.74	17.95	17.16	18.34	18.74
	12H	17.33	18.49	17.76	18.87	19.30	16.82	17.98	17.25	18.36	18.79
4H	2H	14.79	16.16	15.19	16.51	16.89	14.44	15.81	14.84	16.16	16.53
	3H	16.77	17.91	17.18	18.31	18.71	16.36	17.51	16.77	17.90	18.30
	4H	17.54	18.58	17.98	18.99	19.43	17.12	18.16	17.55	18.57	19.01
	6H	18.14	19.05	18.59	19.49	19.94	17.71	18.61	18.16	19.05	19.51
	8H	18.33	19.18	18.79	19.62	20.08	17.89	18.74	18.35	19.18	19.65
	12H	18.46	19.22	18.94	19.70	20.17	18.01	18.77	18.49	19.25	19.71
8H	4H	17.82	18.66	18.28	19.11	19.57	17.44	18.29	17.90	18.73	19.20
	6H	18.53	19.23	19.03	19.72	20.20	18.15	18.85	18.64	19.34	19.82
	8H	18.79	19.42	19.30	19.93	20.41	18.40	19.03	18.91	19.54	20.02
	12H	18.99	19.55	19.50	20.04	20.60	18.58	19.14	19.08	19.63	20.19
12H	4H	17.84	18.60	18.32	19.08	19.55	17.48	18.24	17.96	18.71	19.18
	6H	18.58	19.21	19.09	19.72	20.20	18.21	18.84	18.72	19.35	19.83
	8H	18.89	19.45	19.40	19.94	20.50	18.51	19.07	19.02	19.56	20.12

END OF REPORT