

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931549

Luminaire Tested: DFN2DS-TR4F0-090DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-090DS950-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8420.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 93.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931549

CATALOG NUMBER: DFN2DS-TR4F0-090DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931549

CATALOG NUMBER: DFN2DS-TR4F0-090DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2629	2629	2629
5°	2639	2601	2616
10°	2624	2575	2588
15°	2591	2541	2539
20°	2545	2491	2489
25°	2499	2430	2430
30°	2441	2373	2353
35°	2386	2305	2271
40°	2317	2237	2195
45°	2249	2170	2117
50°	2175	2100	2025
55°	2098	2019	1944
60°	2012	1921	1851
65°	1920	1825	1741
70°	1804	1707	1626
75°	1641	1572	1534
80°	1457	1411	1340
85°	1188	1133	1015

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2249 cd/sqm

TEST NUMBER: P931549

CATALOG NUMBER: DFN2DS-TR4F0-090DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.5	3.7
10°-20°	876.4	10.4
20°-30°	1287.9	15.3
30°-40°	1495.9	17.8
40°-50°	1494.0	17.7
50°-60°	1302.7	15.5
60°-70°	963.0	11.4
70°-80°	544.8	6.5
80°-90°	143.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2475.8	29.4
0°-40°	3971.6	47.2
0°-60°	6768.3	80.4
0°-90°	8420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3309	3309	3309	3309	3309	
5°	3309	3297	3262	3287	3281	314
15°	3150	3131	3090	3103	3087	887
25°	2851	2826	2772	2778	2772	1312
35°	2460	2428	2377	2358	2342	1536
45°	2002	1980	1932	1897	1884	1545
55°	1515	1496	1458	1419	1404	1354
65°	1022	1002	971	942	926	1010
75°	534	528	512	493	500	571
85°	130	127	124	114	111	153
90°	0	0	0	0	0	

TEST NUMBER: P931549

CATALOG NUMBER: DFN2DS-TR4F0-090DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3309.3	3309.3	3309.3	3309.3	3309.3
2.5°	3328.6	3312.7	3277.6	3309.3	3303.2
5°	3309.3	3296.8	3261.8	3287.1	3280.9
7.5°	3287.1	3268.2	3233.0	3258.7	3252.3
10°	3252.3	3230.0	3191.8	3217.2	3207.7
12.5°	3204.3	3185.4	3147.3	3163.1	3156.8
15°	3150.3	3131.4	3089.9	3102.7	3086.8
17.5°	3083.4	3064.5	3023.1	3038.9	3023.1
20°	3010.2	2991.3	2946.7	2956.1	2943.7
22.5°	2937.2	2908.6	2867.0	2867.0	2860.6
25°	2851.2	2825.8	2771.9	2777.9	2771.9
27.5°	2755.6	2733.3	2692.2	2682.8	2666.9
30°	2660.5	2634.8	2587.1	2577.7	2564.9
32.5°	2558.5	2539.6	2488.6	2469.4	2456.5
35°	2459.9	2428.2	2377.1	2358.0	2342.1
37.5°	2348.5	2319.8	2268.8	2246.5	2230.7
40°	2234.0	2208.4	2157.3	2129.0	2116.2
42.5°	2122.6	2097.0	2046.3	2014.3	1995.4
45°	2001.7	1979.5	1931.5	1896.7	1884.0
47.5°	1884.0	1861.6	1810.6	1775.6	1756.7
50°	1759.7	1743.8	1699.2	1654.7	1638.8
52.5°	1638.8	1616.5	1575.3	1540.3	1518.0
55°	1514.9	1495.7	1457.5	1419.4	1403.5
57.5°	1390.7	1374.8	1333.3	1295.1	1282.3
60°	1266.4	1253.9	1209.3	1174.3	1164.8
62.5°	1145.5	1123.2	1091.5	1059.8	1047.0
65°	1021.6	1002.4	970.6	942.0	926.1
67.5°	894.3	878.2	849.7	827.5	814.7
70°	776.5	763.7	735.0	712.7	700.2
72.5°	655.6	642.8	626.9	604.7	595.3
75°	534.5	528.3	512.2	493.3	499.7
77.5°	426.4	413.6	407.2	397.8	388.3
80°	318.4	315.0	308.5	299.1	292.8
82.5°	216.4	216.4	213.4	200.5	200.5
85°	130.3	127.3	124.3	114.4	111.4
87.5°	57.4	50.9	44.6	35.2	31.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931549

CATALOG NUMBER: DFN2DS-TR4F0-090DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.64	16.25	15.01	16.57	16.88	14.20	15.81	14.56	16.12	16.44
	3H	16.39	17.85	16.77	18.17	18.53	15.90	17.35	16.28	17.68	18.04
	4H	17.04	18.41	17.44	18.75	19.13	16.54	17.91	16.94	18.26	18.64
	6H	17.51	18.78	17.92	19.14	19.53	17.01	18.27	17.42	18.64	19.03
	8H	17.65	18.86	18.07	19.25	19.65	17.15	18.36	17.57	18.75	19.15
	12H	17.74	18.90	18.17	19.28	19.71	17.23	18.39	17.66	18.77	19.20
4H	2H	15.20	16.57	15.60	16.92	17.29	14.85	16.22	15.25	16.57	16.94
	3H	17.18	18.32	17.59	18.72	19.12	16.77	17.92	17.18	18.31	18.71
	4H	17.95	18.99	18.38	19.40	19.84	17.53	18.57	17.96	18.98	19.42
	6H	18.55	19.45	19.00	19.90	20.35	18.12	19.02	18.57	19.46	19.92
	8H	18.74	19.59	19.20	20.03	20.49	18.30	19.15	18.76	19.59	20.06
	12H	18.87	19.63	19.35	20.11	20.58	18.42	19.18	18.90	19.65	20.12
8H	4H	18.23	19.07	18.69	19.52	19.98	17.85	18.70	18.31	19.14	19.61
	6H	18.94	19.64	19.43	20.13	20.61	18.56	19.26	19.05	19.75	20.23
	8H	19.20	19.83	19.71	20.34	20.82	18.81	19.44	19.32	19.95	20.43
	12H	19.40	19.96	19.91	20.45	21.01	18.99	19.54	19.49	20.03	20.60
12H	4H	18.25	19.01	18.73	19.49	19.96	17.89	18.65	18.37	19.12	19.59
	6H	18.99	19.62	19.50	20.12	20.61	18.62	19.25	19.13	19.76	20.24
	8H	19.30	19.86	19.81	20.35	20.91	18.92	19.48	19.43	19.97	20.53