

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644346

Luminaire Tested: CRQ4DIP-SR4F0-50D150U930-FLLOOB-1DUDD-WW

Issue Date: 2/20/2023



Test Information

Test Method: LM-79-2019
Report Number: P644346
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-14)
Test Lab: INNOVATION CENTER
Issue Date: 2/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: CRQ4DIP-SR4F0-50D150U930-FLLOOB-1DUDD-WW
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE
DOWNLIGHT - CURVED FROSTED LENS - 500 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6785.5 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.33')
CIE Type: Semi-Indirect

Input Watts (W): 62.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644346

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U930-FLLOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644346

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U930-FLLOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	84	81	82	78	75	72	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24	18
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	17	15	11
6	59	47	40	34	52	42	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9	7
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10908	10908	10908
5°	10702	9631	9332
10°	10561	8569	8061
15°	10407	7674	7051
20°	10168	6884	6167
25°	9850	6147	5374
30°	9540	5431	4665
35°	9116	4777	4004
40°	8723	4182	3394
45°	8266	3594	2832
50°	7785	3045	2324
55°	7272	2561	1874
60°	6787	2099	1498
65°	6184	1675	1185
70°	5608	1312	936
75°	4906	1008	739
80°	4098	749	575
85°	2989	545	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8266 cd/sqm



TEST NUMBER: P644346

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U930-FLLOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.8	0.9
10°-20°	180.9	2.7
20°-30°	267.1	3.9
30°-40°	307.1	4.5
40°-50°	297.9	4.4
50°-60°	249.4	3.7
60°-70°	179.7	2.6
70°-80°	109.8	1.6
80°-90°	55.5	0.8
90°-100°	136.5	2.0
100°-110°	829.9	12.2
110°-120°	1119.0	16.5
120°-130°	909.7	13.4
130°-140°	730.9	10.8
140°-150°	576.1	8.5
150°-160°	421.3	6.2
160°-170°	261.7	3.9
170°-180°	89.2	1.3
0°-30°	511.8	7.5
0°-40°	818.9	12.1
0°-60°	1366.2	20.1
0°-90°	1711.2	25.2
90°-120°	2085.5	30.7
90°-150°	4302.2	63.4
90°-180°	5074.0	74.8
0°-180°	6785.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	676	676	676	676	676	
5°	665	677	671	672	676	63
15°	636	646	640	643	648	179
25°	574	584	582	579	583	265
35°	490	497	492	488	488	307
45°	392	396	389	378	372	302
55°	289	293	282	265	257	259
65°	191	192	182	169	164	190
75°	103	103	105	102	100	110
85°	32	38	52	56	56	33
90°	3	24	46	58	59	6
95°	57	96	67	80	93	61
105°	192	285	1073	1374	914	203
115°	331	397	923	1916	2239	329
125°	470	532	869	1517	1794	418
135°	578	642	874	1250	1434	445
145°	685	742	880	1089	1204	430
155°	803	832	897	987	1033	369
165°	891	903	921	945	962	250
175°	939	944	939	932	927	89
180°	939	939	939	939	939	



TEST NUMBER: P644346

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U930-FLLOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	675.6	675.6	675.6	675.6	675.6
2.5°	669.5	679.2	673.3	674.8	675.6
5°	665.1	677.2	670.8	671.9	676.5
7.5°	659.0	670.2	664.5	665.8	671.2
10°	653.6	664.8	658.4	660.4	665.1
12.5°	646.8	657.2	652.3	654.3	659.0
15°	636.5	645.8	640.3	643.2	647.9
17.5°	621.2	631.3	625.4	627.0	631.7
20°	609.7	619.1	615.5	615.6	620.2
22.5°	596.0	606.1	603.2	601.1	606.5
25°	574.4	583.8	582.1	579.3	583.0
27.5°	553.1	560.0	556.7	553.9	556.7
30°	536.3	544.7	539.1	536.3	539.1
32.5°	517.9	526.3	520.8	517.2	518.5
35°	489.5	497.0	492.4	487.6	487.6
37.5°	462.6	467.5	464.3	456.3	454.2
40°	442.8	448.3	443.7	434.1	431.3
42.5°	422.1	427.7	422.3	411.9	407.6
45°	392.2	395.9	389.3	377.7	372.1
47.5°	361.3	365.2	356.1	343.4	336.6
50°	340.7	345.3	334.0	320.4	313.0
52.5°	320.8	324.0	313.4	297.6	290.8
55°	289.1	292.9	282.4	265.1	256.7
57.5°	259.5	263.1	250.8	234.2	227.7
60°	240.5	243.3	230.9	213.6	207.1
62.5°	219.1	221.9	210.3	195.3	188.7
65°	190.8	191.8	182.3	168.8	164.1
67.5°	164.3	164.3	156.3	146.3	142.6
70°	146.0	146.0	140.3	132.5	128.8
72.5°	129.2	128.5	125.0	119.6	116.6
75°	103.1	103.1	105.0	102.1	100.2
77.5°	80.2	78.7	86.8	86.4	85.5
80°	64.9	64.9	75.4	77.3	76.3
82.5°	51.1	52.6	66.2	68.9	67.9
85°	31.5	38.0	52.5	56.3	56.3
87.5°	14.3	26.9	43.6	49.7	49.9
90°	2.9	24.5	46.2	57.8	58.7
92.5°	20.1	34.3	54.2	70.7	77.0
95°	56.8	96.2	67.3	80.1	92.6
97.5°	95.3	173.8	361.6	122.5	109.7
100°	123.6	215.2	708.0	221.3	153.9
102.5°	151.2	247.4	950.5	554.2	310.6
105°	192.5	285.1	1073.2	1373.5	913.6
107.5°	233.9	302.4	1022.7	1991.8	1866.9
110°	261.5	326.1	993.6	2091.1	2247.9



TEST NUMBER: P644346

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U930-FLLOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	289.8	354.4	965.3	2030.6	2293.6
115°	331.3	396.9	922.8	1915.9	2239.1
117.5°	373.9	439.4	911.9	1791.0	2123.4
120°	406.2	467.8	892.3	1696.1	2042.4
122.5°	429.8	495.3	868.7	1615.2	1933.8
125°	470.1	531.8	868.7	1517.4	1794.5
127.5°	503.2	567.1	869.9	1404.0	1677.6
130°	521.4	590.6	874.6	1328.1	1587.9
132.5°	543.4	612.7	873.8	1294.0	1507.6
135°	578.5	642.0	873.6	1249.7	1434.4
137.5°	608.0	676.1	873.6	1200.7	1358.8
140°	631.6	695.1	873.6	1172.0	1316.3
142.5°	655.2	714.1	878.3	1138.8	1273.8
145°	684.7	742.4	879.5	1088.8	1204.2
147.5°	720.1	770.9	886.6	1052.7	1141.6
150°	743.8	789.9	891.3	1028.8	1103.8
152.5°	767.4	808.9	891.3	1009.6	1070.8
155°	802.8	831.6	897.2	986.8	1033.0
157.5°	831.1	858.8	904.3	972.4	1005.8
160°	850.0	873.1	909.0	962.8	991.7
162.5°	864.2	887.3	913.8	957.9	977.5
165°	891.3	902.9	920.8	944.9	962.2
167.5°	906.7	917.1	926.7	938.8	949.2
170°	920.8	926.6	926.7	938.7	944.5
172.5°	925.6	936.0	931.5	934.0	939.7
175°	938.6	944.3	938.6	932.5	926.7
177.5°	938.6	943.2	938.6	938.5	933.8
180°	938.6	938.6	938.6	938.6	938.6

(END OF REPORT)