

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644460

Luminaire Tested: CRQ4DP-SR4F0-100D835-FLL-1DUDD-WW

Issue Date: 2/20/2023



Test Information

Test Method: LM-79-2019
Report Number: P644460
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-14)
Test Lab: INNOVATION CENTER
Issue Date: 2/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: CRQ4DP-SR4F0-100D835-FLL-1DUDD-WW
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE
DOWNLIGHT - CURVED FROSTED LENS - 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4049.5 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.02')
CIE Type: Direct

Input Watts (W): 29.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644460
CATALOG NUMBER: CRQ4DP-SR4F0-100D835-FLL-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644460

CATALOG NUMBER: CRQ4DP-SR4F0-100D835-FLL-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	100	100	100	98
1	108	103	99	95	105	101	97	93	96	93	90	92	89	87	88	86	84	82
2	99	91	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71	69
3	90	80	72	65	88	78	71	65	75	69	63	72	67	62	69	65	61	58
4	83	71	62	56	80	70	62	55	67	60	54	64	58	53	62	57	53	50
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	56	50	46	44
6	71	58	49	43	69	57	48	42	55	47	42	53	46	41	51	45	41	39
7	66	52	44	38	64	51	43	38	50	42	37	48	42	37	47	41	36	34
8	61	48	40	34	60	47	39	34	46	38	33	44	38	33	43	37	33	31
9	57	44	36	31	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25362	25362	25362
5°	25050	25037	25164
10°	24888	24618	24700
15°	24694	24169	24207
20°	24304	23637	23495
25°	23725	22928	22571
30°	23163	21968	21507
35°	22335	20944	20222
40°	21583	19898	18773
45°	20690	18613	17181
50°	19747	17235	15507
55°	18755	15966	13836
60°	17861	14553	12339
65°	16727	13090	11031
70°	15752	11809	10012
75°	14606	10777	9319
80°	13550	10021	8918
85°	12656	9988	8933

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20690 cd/sqm



TEST NUMBER: P644460

CATALOG NUMBER: CRQ4DP-SR4F0-100D835-FLL-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	3.7
10°-20°	420.7	10.4
20°-30°	621.1	15.3
30°-40°	714.0	17.6
40°-50°	692.7	17.1
50°-60°	579.8	14.3
60°-70°	417.7	10.3
70°-80°	255.3	6.3
80°-90°	124.0	3.1
90°-100°	49.1	1.2
100°-110°	17.8	0.4
110°-120°	6.2	0.2
120°-130°	2.6	0.1
130°-140°	0.3	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1190.0	29.4
0°-40°	1904.1	47.0
0°-60°	3176.6	78.4
0°-90°	3973.6	98.1
90°-120°	73.1	1.8
90°-150°	75.9	1.9
90°-180°	76.0	1.9
0°-180°	4049.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1571	1571	1571	1571	1571	
5°	1546	1575	1560	1562	1573	147
15°	1480	1502	1489	1496	1506	416
25°	1336	1357	1353	1347	1356	615
35°	1138	1156	1145	1134	1134	713
45°	912	920	905	878	865	703
55°	672	681	657	616	597	603
65°	444	446	424	392	382	441
75°	240	240	244	237	233	256
85°	73	88	122	131	131	77
90°	7	44	80	93	95	8
95°	22	20	47	62	64	19
105°	22	9	11	20	24	23
115°	16	7	4	4	4	15
125°	9	4	2	0	0	8
135°	0	0	0	0	0	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P644460

CATALOG NUMBER: CRQ4DP-SR4F0-100D835-FLL-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1570.8	1570.8	1570.8	1570.8	1570.8
2.5°	1556.6	1579.1	1565.4	1569.0	1570.8
5°	1546.4	1574.6	1559.7	1562.1	1573.0
7.5°	1532.2	1558.2	1545.0	1548.0	1560.6
10°	1519.7	1545.8	1530.8	1535.5	1546.4
12.5°	1503.8	1528.1	1516.6	1521.3	1532.2
15°	1479.8	1501.5	1488.7	1495.6	1506.4
17.5°	1444.3	1467.7	1454.1	1457.9	1468.7
20°	1417.7	1439.4	1431.0	1431.2	1442.1
22.5°	1385.7	1409.2	1402.6	1397.6	1410.1
25°	1335.6	1357.3	1353.3	1346.9	1355.6
27.5°	1285.9	1302.0	1294.3	1287.8	1294.3
30°	1246.9	1266.4	1253.5	1247.0	1253.5
32.5°	1204.3	1223.8	1210.9	1202.5	1205.6
35°	1138.1	1155.5	1144.8	1133.7	1133.7
37.5°	1075.6	1086.9	1079.6	1060.8	1056.1
40°	1029.4	1042.4	1031.6	1009.3	1002.8
42.5°	981.5	994.5	982.0	957.8	947.8
45°	911.8	920.5	905.2	878.3	865.3
47.5°	840.0	849.1	828.0	798.3	782.7
50°	792.0	802.9	776.5	745.1	727.7
52.5°	745.9	753.3	728.6	691.8	676.2
55°	672.2	680.9	656.7	616.3	596.8
57.5°	603.5	611.7	583.0	544.5	529.4
60°	559.1	565.6	536.9	496.6	481.4
62.5°	509.4	515.9	489.0	454.0	438.8
65°	443.7	445.9	423.8	392.4	381.6
67.5°	382.0	382.0	363.4	340.1	331.5
70°	339.4	339.4	326.1	308.2	299.5
72.5°	300.4	298.7	290.6	278.1	271.1
75°	239.6	239.6	244.0	237.3	233.0
77.5°	186.4	182.9	201.9	201.0	198.8
80°	150.9	150.9	175.3	179.7	177.5
82.5°	118.9	122.4	154.0	160.1	158.0
85°	73.2	88.4	122.0	130.9	130.9
87.5°	33.3	59.7	95.8	107.4	107.8
90°	6.7	43.5	79.9	93.2	95.4
92.5°	13.8	33.3	65.7	79.1	83.0
95°	22.2	20.0	46.6	62.2	64.3
97.5°	26.6	13.2	33.7	46.6	49.3
100°	26.6	11.4	26.6	37.8	42.2
102.5°	24.8	9.7	19.5	30.7	33.3
105°	22.2	9.2	11.1	20.1	24.4
107.5°	19.5	6.9	6.2	12.5	14.6
110°	17.7	6.9	4.4	8.9	11.1



TEST NUMBER: P644460

CATALOG NUMBER: CRQ4DP-SR4F0-100D835-FLL-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	17.7	6.9	4.4	5.4	7.5
115°	15.5	6.9	4.4	4.4	4.4
117.5°	12.9	6.8	4.0	1.8	1.8
120°	11.1	6.8	2.2	0.0	0.0
122.5°	11.1	5.0	2.2	0.0	0.0
125°	8.9	4.5	2.2	0.0	0.0
127.5°	6.2	4.5	2.2	0.0	0.0
130°	4.4	4.4	2.2	0.0	0.0
132.5°	0.9	0.9	0.4	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)