

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930923

Luminaire Tested: DFN2DS-SQ3F0-050DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-050DS835-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4950.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930923

CATALOG NUMBER: DFN2DS-SQ3F0-050DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930923

CATALOG NUMBER: DFN2DS-SQ3F0-050DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2229	2229	2229
5°	2238	2205	2219
10°	2225	2183	2194
15°	2197	2155	2153
20°	2158	2112	2110
25°	2119	2060	2060
30°	2069	2012	1995
35°	2023	1955	1926
40°	1965	1897	1861
45°	1907	1840	1795
50°	1844	1781	1717
55°	1779	1712	1648
60°	1706	1629	1569
65°	1628	1547	1476
70°	1529	1448	1379
75°	1391	1333	1301
80°	1235	1197	1136
85°	1007	960	861

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1907 cd/sqm

TEST NUMBER: P930923

CATALOG NUMBER: DFN2DS-SQ3F0-050DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	3.7
10°-20°	515.2	10.4
20°-30°	757.2	15.3
30°-40°	879.4	17.8
40°-50°	878.3	17.7
50°-60°	765.8	15.5
60°-70°	566.1	11.4
70°-80°	320.3	6.5
80°-90°	84.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1455.5	29.4
0°-40°	2334.9	47.2
0°-60°	3979.0	80.4
0°-90°	4950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P930923

CATALOG NUMBER: DFN2DS-SQ3F0-050DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930923

CATALOG NUMBER: DFN2DS-SQ3F0-050DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.07	15.68	14.43	15.99	16.31	13.62	15.23	13.99	15.55	15.86
	3H	15.82	17.27	16.19	17.60	17.96	15.33	16.78	15.70	17.11	17.47
	4H	16.46	17.83	16.86	18.18	18.56	15.97	17.34	16.37	17.69	18.06
	6H	16.93	18.20	17.34	18.57	18.96	16.43	17.70	16.84	18.07	18.46
	8H	17.08	18.29	17.50	18.68	19.08	16.57	17.78	17.00	18.17	18.57
	12H	17.17	18.33	17.60	18.71	19.14	16.65	17.81	17.08	18.20	18.63
4H	2H	14.63	16.00	15.03	16.34	16.72	14.28	15.64	14.67	15.99	16.37
	3H	16.60	17.75	17.01	18.15	18.55	16.20	17.34	16.61	17.74	18.14
	4H	17.38	18.42	17.81	18.83	19.27	16.96	17.99	17.39	18.41	18.84
	6H	17.98	18.88	18.43	19.32	19.78	17.54	18.45	18.00	18.89	19.35
	8H	18.17	19.01	18.63	19.45	19.92	17.73	18.57	18.19	19.02	19.48
	12H	18.30	19.06	18.78	19.53	20.00	17.85	18.61	18.33	19.08	19.55
8H	4H	17.65	18.50	18.11	18.94	19.41	17.28	18.13	17.74	18.57	19.03
	6H	18.37	19.07	18.86	19.56	20.03	17.99	18.69	18.48	19.18	19.65
	8H	18.63	19.26	19.14	19.76	20.25	18.24	18.87	18.75	19.37	19.86
	12H	18.83	19.38	19.33	19.87	20.44	18.41	18.97	18.92	19.46	20.02
12H	4H	17.68	18.44	18.16	18.91	19.38	17.31	18.07	17.79	18.55	19.02
	6H	18.41	19.04	18.92	19.55	20.04	18.04	18.68	18.55	19.18	19.67
	8H	18.73	19.28	19.23	19.77	20.34	18.35	18.91	18.86	19.40	19.96