

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644478

Luminaire Tested: CRQ4DP-SR4F0-75D835-FLL-1DUDD-WW

Issue Date: 2/20/2023



**Test Information**

Test Method: LM-79-2019  
Report Number: P644478  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/20/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: CRQ4DP-SR4F0-75D835-FLL-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - CURVED FROSTED LENS - 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3060.7 lumens  
Efficiency: N/A  
Efficacy: 140.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.02')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644478  
CATALOG NUMBER: CRQ4DP-SR4F0-75D835-FLL-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644478

CATALOG NUMBER: CRQ4DP-SR4F0-75D835-FLL-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	100	100	100	98
1	108	103	99	95	105	101	97	93	96	93	90	92	89	87	88	86	84	82
2	99	91	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71	69
3	90	80	72	65	88	78	71	65	75	69	63	72	67	62	69	65	61	58
4	83	71	62	56	80	70	62	55	67	60	54	64	58	53	62	57	53	50
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	56	50	46	44
6	71	58	49	43	69	57	48	42	55	47	42	53	46	41	51	45	41	39
7	66	52	44	38	64	51	43	38	50	42	37	48	42	37	47	41	36	34
8	61	48	40	34	60	47	39	34	46	38	33	44	38	33	43	37	33	31
9	57	44	36	31	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19168	19168	19168
5°	18933	18923	19020
10°	18810	18606	18669
15°	18665	18267	18297
20°	18369	17866	17757
25°	17932	17330	17058
30°	17507	16604	16255
35°	16881	15829	15285
40°	16314	15039	14188
45°	15639	14068	12985
50°	14925	13027	11720
55°	14176	12067	10458
60°	13500	10999	9328
65°	12644	9893	8336
70°	11909	8927	7569
75°	11040	8149	7043
80°	10237	7574	6737
85°	9561	7548	6749

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15639 cd/sqm



TEST NUMBER: P644478

CATALOG NUMBER: CRQ4DP-SR4F0-75D835-FLL-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.1	3.7
10°-20°	318.0	10.4
20°-30°	469.4	15.3
30°-40°	539.7	17.6
40°-50°	523.5	17.1
50°-60°	438.3	14.3
60°-70°	315.8	10.3
70°-80°	192.9	6.3
80°-90°	93.7	3.1
90°-100°	37.1	1.2
100°-110°	13.4	0.4
110°-120°	4.7	0.2
120°-130°	1.9	0.1
130°-140°	0.2	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	899.4	29.4
0°-40°	1439.1	47.0
0°-60°	2400.9	78.4
0°-90°	3003.3	98.1
90°-120°	55.2	1.8
90°-150°	57.4	1.9
90°-180°	57.0	1.9
0°-180°	3060.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1187	1187	1187	1187	1187	
5°	1169	1190	1179	1181	1189	111
15°	1118	1135	1125	1130	1139	315
25°	1010	1026	1023	1018	1024	465
35°	860	873	865	857	857	539
45°	689	696	684	664	654	531
55°	508	515	496	466	451	456
65°	335	337	320	297	288	334
75°	181	181	184	179	176	194
85°	55	67	92	99	99	58
90°	5	33	60	70	72	6
95°	17	15	35	47	49	14
105°	17	7	8	15	18	18
115°	12	5	3	3	3	11
125°	7	3	2	0	0	6
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P644478

CATALOG NUMBER: CRQ4DP-SR4F0-75D835-FLL-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1187.2	1187.2	1187.2	1187.2	1187.2
2.5°	1176.5	1193.5	1183.2	1185.9	1187.2
5°	1168.8	1190.1	1178.8	1180.7	1188.9
7.5°	1158.0	1177.7	1167.8	1170.0	1179.5
10°	1148.6	1168.3	1157.0	1160.6	1168.8
12.5°	1136.6	1154.9	1146.3	1149.8	1158.0
15°	1118.5	1134.8	1125.2	1130.4	1138.6
17.5°	1091.6	1109.3	1099.0	1101.9	1110.1
20°	1071.5	1087.9	1081.6	1081.7	1089.9
22.5°	1047.4	1065.1	1060.1	1056.3	1065.8
25°	1009.5	1025.9	1022.9	1018.0	1024.5
27.5°	971.9	984.0	978.3	973.3	978.3
30°	942.4	957.1	947.4	942.5	947.4
32.5°	910.2	924.9	915.2	908.9	911.2
35°	860.2	873.3	865.2	856.9	856.9
37.5°	812.9	821.5	815.9	801.8	798.2
40°	778.1	787.9	779.7	762.8	757.9
42.5°	741.8	751.7	742.2	723.9	716.3
45°	689.2	695.7	684.2	663.8	654.0
47.5°	634.9	641.7	625.8	603.4	591.6
50°	598.6	606.8	586.9	563.1	550.0
52.5°	563.8	569.3	550.7	522.9	511.1
55°	508.1	514.6	496.3	465.8	451.1
57.5°	456.1	462.3	440.7	411.6	400.1
60°	422.6	427.5	405.8	375.4	363.9
62.5°	385.0	389.9	369.6	343.2	331.7
65°	335.4	337.0	320.3	296.6	288.4
67.5°	288.8	288.8	274.7	257.1	250.5
70°	256.6	256.6	246.5	232.9	226.4
72.5°	227.0	225.7	219.7	210.2	204.9
75°	181.1	181.1	184.5	179.3	176.1
77.5°	140.9	138.2	152.6	151.9	150.2
80°	114.0	114.0	132.5	135.8	134.1
82.5°	89.9	92.5	116.4	121.0	119.4
85°	55.3	66.8	92.2	98.9	98.9
87.5°	25.2	45.2	72.4	81.2	81.5
90°	5.0	32.9	60.4	70.5	72.1
92.5°	10.4	25.2	49.6	59.8	62.7
95°	16.8	15.1	35.2	47.0	48.6
97.5°	20.1	10.0	25.5	35.3	37.2
100°	20.1	8.6	20.1	28.6	31.9
102.5°	18.8	7.3	14.8	23.2	25.2
105°	16.8	6.9	8.4	15.2	18.4
107.5°	14.8	5.2	4.7	9.4	11.1
110°	13.4	5.2	3.4	6.7	8.4



TEST NUMBER: P644478

CATALOG NUMBER: CRQ4DP-SR4F0-75D835-FLL-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	13.4	5.2	3.4	4.1	5.7
115°	11.7	5.2	3.4	3.4	3.4
117.5°	9.7	5.1	3.0	1.3	1.3
120°	8.4	5.1	1.7	0.0	0.0
122.5°	8.4	3.8	1.7	0.0	0.0
125°	6.7	3.4	1.7	0.0	0.0
127.5°	4.7	3.4	1.7	0.0	0.0
130°	3.4	3.4	1.7	0.0	0.0
132.5°	0.7	0.7	0.3	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)