

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930925

Luminaire Tested: DFN2DS-SQ3F0-050DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930925
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-050DS840-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4955.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930925

CATALOG NUMBER: DFN2DS-SQ3F0-050DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930925

CATALOG NUMBER: DFN2DS-SQ3F0-050DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2231	2231	2231
5°	2240	2208	2221
10°	2227	2185	2196
15°	2199	2157	2155
20°	2160	2114	2112
25°	2121	2062	2062
30°	2071	2014	1997
35°	2025	1957	1928
40°	1966	1899	1863
45°	1909	1842	1796
50°	1846	1783	1719
55°	1781	1713	1650
60°	1708	1631	1571
65°	1630	1549	1477
70°	1531	1449	1381
75°	1392	1334	1302
80°	1237	1198	1137
85°	1008	961	862

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1909 cd/sqm

TEST NUMBER: P930925

CATALOG NUMBER: DFN2DS-SQ3F0-050DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	3.7
10°-20°	515.7	10.4
20°-30°	757.9	15.3
30°-40°	880.3	17.8
40°-50°	879.2	17.7
50°-60°	766.6	15.5
60°-70°	566.7	11.4
70°-80°	320.6	6.5
80°-90°	84.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.9	29.4
0°-40°	2337.2	47.2
0°-60°	3983.0	80.4
0°-90°	4955.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4955.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1940	1919	1934	1931	185
15°	1854	1843	1818	1826	1816	522
25°	1678	1663	1631	1635	1631	772
35°	1448	1429	1399	1388	1378	904
45°	1178	1165	1137	1116	1109	909
55°	892	880	858	835	826	797
65°	601	590	571	554	545	594
75°	314	311	301	290	294	336
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P930925

CATALOG NUMBER: DFN2DS-SQ3F0-050DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.4	1947.4	1947.4	1947.4	1947.4
2.5°	1958.8	1949.4	1928.8	1947.4	1943.9
5°	1947.4	1940.1	1919.4	1934.3	1930.8
7.5°	1934.3	1923.2	1902.6	1917.7	1913.9
10°	1913.9	1900.8	1878.4	1893.2	1887.7
12.5°	1885.7	1874.6	1852.2	1861.5	1857.7
15°	1853.9	1842.7	1818.3	1825.9	1816.5
17.5°	1814.5	1803.4	1779.0	1788.3	1779.0
20°	1771.5	1760.4	1734.1	1739.6	1732.3
22.5°	1728.5	1711.6	1687.2	1687.2	1683.4
25°	1677.9	1663.0	1631.1	1634.7	1631.1
27.5°	1621.6	1608.5	1584.3	1578.7	1569.4
30°	1565.6	1550.5	1522.5	1516.9	1509.4
32.5°	1505.6	1494.5	1464.5	1453.2	1445.6
35°	1447.5	1428.9	1398.9	1387.6	1378.3
37.5°	1382.0	1365.2	1335.1	1322.0	1312.7
40°	1314.7	1299.6	1269.6	1252.9	1245.3
42.5°	1249.1	1234.0	1204.2	1185.3	1174.2
45°	1178.0	1164.9	1136.6	1116.2	1108.6
47.5°	1108.6	1095.5	1065.6	1044.8	1033.7
50°	1035.5	1026.2	1000.0	973.8	964.4
52.5°	964.4	951.3	927.0	906.4	893.3
55°	891.5	880.2	857.7	835.2	825.9
57.5°	818.3	809.0	784.6	762.2	754.6
60°	745.2	737.9	711.7	691.0	685.5
62.5°	674.2	661.1	642.3	623.6	616.1
65°	601.2	589.9	571.2	554.4	544.9
67.5°	526.3	516.8	500.1	487.0	479.4
70°	457.0	449.4	432.5	419.4	412.1
72.5°	385.9	378.3	369.0	355.9	350.2
75°	314.5	310.9	301.4	290.3	294.1
77.5°	251.0	243.3	239.6	234.0	228.5
80°	187.4	185.4	181.6	176.1	172.3
82.5°	127.3	127.3	125.5	118.0	118.0
85°	76.7	74.9	73.1	67.4	65.6
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930925

CATALOG NUMBER: DFN2DS-SQ3F0-050DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.07	15.68	14.44	16.00	16.31	13.63	15.24	13.99	15.55	15.87
	3H	15.82	17.28	16.20	17.60	17.96	15.33	16.78	15.71	17.11	17.47
	4H	16.47	17.84	16.87	18.18	18.56	15.97	17.34	16.37	17.69	18.07
	6H	16.94	18.21	17.35	18.57	18.96	16.44	17.70	16.85	18.07	18.46
	8H	17.08	18.29	17.50	18.68	19.08	16.58	17.79	17.00	18.18	18.58
	12H	17.17	18.33	17.60	18.71	19.14	16.66	17.82	17.09	18.20	18.63
4H	2H	14.63	16.00	15.03	16.35	16.72	14.28	15.65	14.68	16.00	16.37
	3H	16.61	17.75	17.02	18.15	18.55	16.20	17.35	16.61	17.74	18.14
	4H	17.38	18.42	17.81	18.83	19.27	16.96	18.00	17.39	18.41	18.85
	6H	17.98	18.88	18.43	19.33	19.78	17.55	18.45	18.00	18.89	19.35
	8H	18.17	19.02	18.63	19.46	19.92	17.73	18.58	18.19	19.02	19.49
	12H	18.30	19.06	18.78	19.54	20.01	17.85	18.61	18.33	19.09	19.55
8H	4H	17.66	18.50	18.12	18.95	19.41	17.28	18.13	17.74	18.57	19.04
	6H	18.37	19.07	18.86	19.56	20.04	17.99	18.69	18.48	19.18	19.66
	8H	18.63	19.26	19.14	19.77	20.25	18.24	18.87	18.75	19.38	19.86
	12H	18.83	19.39	19.34	19.88	20.44	18.42	18.97	18.92	19.47	20.03
12H	4H	17.68	18.44	18.16	18.92	19.39	17.32	18.08	17.80	18.55	19.02
	6H	18.42	19.05	18.93	19.55	20.04	18.05	18.68	18.56	19.19	19.67
	8H	18.73	19.29	19.24	19.78	20.34	18.35	18.91	18.86	19.40	19.96