

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930911

Luminaire Tested: DFN2DS-SQ3F0-040DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930911
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-040DS927-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3136.3 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930911

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930911

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1412	1412	1412
5°	1418	1397	1406
10°	1409	1383	1390
15°	1392	1365	1364
20°	1367	1338	1337
25°	1343	1305	1305
30°	1311	1275	1264
35°	1282	1239	1220
40°	1245	1202	1179
45°	1208	1166	1137
50°	1168	1128	1088
55°	1127	1085	1044
60°	1081	1032	994
65°	1032	980	935
70°	969	917	874
75°	881	845	824
80°	783	758	720
85°	638	609	546

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1208 cd/sqm

TEST NUMBER: P930911

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	3.7
10°-20°	326.4	10.4
20°-30°	479.7	15.3
30°-40°	557.2	17.8
40°-50°	556.5	17.7
50°-60°	485.2	15.5
60°-70°	358.7	11.4
70°-80°	202.9	6.5
80°-90°	53.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.2	29.4
0°-40°	1479.4	47.2
0°-60°	2521.1	80.4
0°-90°	3136.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3136.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1224	1222	117
15°	1173	1166	1151	1156	1150	330
25°	1062	1053	1032	1035	1032	489
35°	916	904	886	878	872	572
45°	746	737	720	706	702	575
55°	564	557	543	529	523	504
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	48	47	46	43	42	57
90°	0	0	0	0	0	

TEST NUMBER: P930911

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.7	1232.7	1232.7	1232.7	1232.7
2.5°	1239.9	1233.9	1220.9	1232.7	1230.5
5°	1232.7	1228.0	1214.9	1224.4	1222.1
7.5°	1224.4	1217.3	1204.2	1213.8	1211.4
10°	1211.4	1203.1	1189.0	1198.4	1194.8
12.5°	1193.5	1186.5	1172.3	1178.3	1175.8
15°	1173.4	1166.4	1150.9	1155.7	1149.8
17.5°	1148.6	1141.5	1126.1	1131.9	1126.1
20°	1121.2	1114.2	1097.6	1101.1	1096.5
22.5°	1094.1	1083.4	1067.9	1067.9	1065.6
25°	1062.0	1052.6	1032.5	1034.7	1032.5
27.5°	1026.4	1018.1	1002.8	999.3	993.4
30°	991.0	981.4	963.7	960.1	955.4
32.5°	953.0	946.0	927.0	919.8	915.0
35°	916.3	904.5	885.5	878.3	872.4
37.5°	874.8	864.1	845.1	836.8	830.9
40°	832.2	822.6	803.6	793.0	788.3
42.5°	790.7	781.1	762.2	750.3	743.2
45°	745.6	737.4	719.5	706.5	701.7
47.5°	701.7	693.4	674.5	661.4	654.4
50°	655.5	649.5	633.0	616.3	610.4
52.5°	610.4	602.2	586.8	573.7	565.4
55°	564.3	557.1	542.9	528.7	522.8
57.5°	518.0	512.1	496.6	482.4	477.7
60°	471.7	467.0	450.5	437.4	433.9
62.5°	426.7	418.4	406.6	394.7	390.0
65°	380.6	373.3	361.5	350.9	345.0
67.5°	333.1	327.1	316.6	308.2	303.5
70°	289.2	284.5	273.8	265.5	260.8
72.5°	244.3	239.4	233.6	225.2	221.7
75°	199.1	196.8	190.8	183.7	186.1
77.5°	158.8	154.0	151.7	148.1	144.6
80°	118.6	117.3	114.9	111.4	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.5	47.4	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930911

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.48	14.09	12.85	14.41	14.72	12.04	13.65	12.40	13.96	14.28
	3H	14.23	15.69	14.61	16.01	16.37	13.74	15.20	14.12	15.52	15.88
	4H	14.88	16.25	15.28	16.60	16.97	14.38	15.75	14.78	16.10	16.48
	6H	15.35	16.62	15.76	16.98	17.37	14.85	16.11	15.26	16.48	16.87
	8H	15.49	16.70	15.92	17.09	17.49	14.99	16.20	15.41	16.59	16.99
	12H	15.58	16.74	16.01	17.12	17.55	15.07	16.23	15.50	16.61	17.04
4H	2H	13.04	14.41	13.44	14.76	15.14	12.69	14.06	13.09	14.41	14.78
	3H	15.02	16.16	15.43	16.56	16.96	14.61	15.76	15.02	16.15	16.56
	4H	15.79	16.83	16.23	17.24	17.68	15.37	16.41	15.80	16.82	17.26
	6H	16.39	17.30	16.84	17.74	18.19	15.96	16.86	16.41	17.30	17.76
	8H	16.58	17.43	17.04	17.87	18.33	16.14	16.99	16.60	17.43	17.90
	12H	16.71	17.47	17.19	17.95	18.42	16.26	17.02	16.74	17.50	17.97
8H	4H	16.07	16.91	16.53	17.36	17.82	15.69	16.54	16.15	16.98	17.45
	6H	16.78	17.48	17.28	17.97	18.45	16.40	17.10	16.89	17.59	18.07
	8H	17.04	17.67	17.55	18.18	18.66	16.65	17.28	17.16	17.79	18.27
	12H	17.24	17.80	17.75	18.29	18.85	16.83	17.39	17.33	17.88	18.44
12H	4H	16.09	16.85	16.57	17.33	17.80	15.73	16.49	16.21	16.96	17.43
	6H	16.83	17.46	17.34	17.97	18.45	16.46	17.09	16.97	17.60	18.08
	8H	17.14	17.70	17.65	18.19	18.75	16.76	17.32	17.27	17.81	18.37