

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930912

Luminaire Tested: DFN2DS-SQ3F0-040DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-040DS927-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2692.8 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930912

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930912

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1500	1500	1500
5°	1506	1481	1490
10°	1494	1457	1445
15°	1477	1414	1373
20°	1453	1352	1284
25°	1429	1282	1198
30°	1395	1210	1088
35°	1363	1132	991
40°	1329	1051	879
45°	1290	960	778
50°	1250	868	678
55°	1210	769	582
60°	1162	665	484
65°	1108	559	440
70°	1044	460	405
75°	965	420	378
80°	852	375	344
85°	669	296	296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1290 cd/sqm

TEST NUMBER: P930912

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	4.6
10°-20°	336.9	12.5
20°-30°	473.0	17.6
30°-40°	515.5	19.1
40°-50°	473.8	17.6
50°-60°	372.1	13.8
60°-70°	242.2	9.0
70°-80°	124.7	4.6
80°-90°	31.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.5	34.6
0°-40°	1448.1	53.8
0°-60°	2294.1	85.2
0°-90°	2692.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2692.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1309	1303	1288	1299	1295	124
15°	1245	1232	1192	1170	1158	351
25°	1130	1092	1014	966	948	520
35°	974	914	809	735	708	610
45°	796	717	592	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	61
90°	0	0	0	0	0	

TEST NUMBER: P930912

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.3	1309.3	1309.3	1309.3	1309.3
2.5°	1315.3	1309.3	1296.3	1308.2	1305.8
5°	1309.3	1303.4	1288.0	1298.6	1295.2
7.5°	1298.6	1291.6	1275.0	1279.6	1273.8
10°	1284.5	1276.1	1252.5	1248.8	1241.9
12.5°	1266.7	1256.0	1224.0	1216.9	1203.8
15°	1245.3	1232.3	1192.0	1169.5	1157.7
17.5°	1220.5	1201.5	1151.6	1125.7	1106.7
20°	1192.0	1168.3	1109.0	1079.5	1053.4
22.5°	1161.2	1134.0	1065.2	1024.9	1007.3
25°	1130.4	1092.5	1014.2	965.8	947.9
27.5°	1093.8	1053.4	966.9	911.2	883.9
30°	1054.6	1009.5	914.7	854.3	822.3
32.5°	1016.7	962.1	865.0	793.9	764.2
35°	974.1	913.6	809.3	734.7	708.5
37.5°	932.6	867.3	757.2	675.3	645.8
40°	888.7	817.7	702.7	618.6	587.7
42.5°	843.6	767.8	648.2	560.4	530.9
45°	796.3	716.8	592.5	508.3	479.9
47.5°	751.3	667.2	539.2	455.0	428.9
50°	701.5	617.4	487.0	405.2	380.4
52.5°	652.8	564.0	437.3	359.0	336.5
55°	605.5	513.1	385.1	314.0	291.5
57.5°	556.9	462.1	338.9	272.5	253.6
60°	507.1	412.3	290.3	229.9	211.0
62.5°	458.6	363.8	248.8	192.0	182.6
65°	408.8	312.8	206.2	165.9	162.3
67.5°	361.5	265.4	165.9	145.7	142.2
70°	311.7	219.2	137.4	125.6	120.8
72.5°	264.3	176.5	114.9	105.5	103.1
75°	218.0	135.0	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.7	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930912

CATALOG NUMBER: DFN2DS-SQ3F0-040DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.64	14.17	13.01	14.48	14.79	8.60	10.13	8.97	10.44	10.75
	3H	14.41	15.77	14.79	16.10	16.46	9.87	11.23	10.25	11.56	11.92
	4H	15.08	16.36	15.48	16.70	17.08	10.37	11.65	10.77	12.00	12.38
	6H	15.56	16.75	15.98	17.11	17.51	10.75	11.94	11.16	12.30	12.69
	8H	15.73	16.86	16.16	17.25	17.65	10.88	12.00	11.30	12.39	12.79
	12H	15.83	16.91	16.26	17.29	17.72	10.96	12.04	11.39	12.42	12.85
4H	2H	12.75	14.03	13.15	14.38	14.76	9.30	10.58	9.70	10.93	11.31
	3H	14.68	15.74	15.09	16.14	16.55	10.74	11.81	11.15	12.21	12.61
	4H	15.43	16.39	15.86	16.80	17.24	11.34	12.30	11.78	12.71	13.15
	6H	16.02	16.85	16.48	17.30	17.76	11.83	12.66	12.29	13.11	13.57
	8H	16.24	17.01	16.70	17.46	17.93	11.99	12.77	12.46	13.21	13.68
	12H	16.39	17.09	16.87	17.56	18.03	12.11	12.80	12.59	13.28	13.75
8H	4H	15.45	16.23	15.92	16.68	17.14	11.70	12.47	12.16	12.92	13.39
	6H	16.09	16.73	16.59	17.23	17.70	12.28	12.93	12.78	13.42	13.89
	8H	16.34	16.92	16.86	17.43	17.92	12.50	13.08	13.02	13.59	14.08
	12H	16.55	17.06	17.06	17.55	18.11	12.68	13.19	13.19	13.69	14.25
12H	4H	15.44	16.13	15.92	16.61	17.08	11.74	12.43	12.22	12.91	13.38
	6H	16.07	16.65	16.59	17.16	17.65	12.35	12.92	12.86	13.43	13.92
	8H	16.36	16.87	16.87	17.36	17.92	12.62	13.13	13.13	13.62	14.19