

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930929

Luminaire Tested: DFN2DS-SQ3F0-050DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-050DS927-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3920.4 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930929

CATALOG NUMBER: DFN2DS-SQ3F0-050DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930929

CATALOG NUMBER: DFN2DS-SQ3F0-050DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1765	1765	1765
5°	1772	1747	1757
10°	1762	1729	1738
15°	1740	1707	1705
20°	1709	1673	1671
25°	1678	1632	1632
30°	1639	1594	1580
35°	1602	1548	1525
40°	1556	1502	1474
45°	1510	1457	1421
50°	1460	1410	1360
55°	1409	1356	1305
60°	1351	1290	1243
65°	1290	1225	1169
70°	1211	1146	1092
75°	1101	1056	1030
80°	979	948	899
85°	798	760	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1510 cd/sqm

TEST NUMBER: P930929

CATALOG NUMBER: DFN2DS-SQ3F0-050DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	3.7
10°-20°	408.0	10.4
20°-30°	599.7	15.3
30°-40°	696.5	17.8
40°-50°	695.6	17.7
50°-60°	606.6	15.5
60°-70°	448.4	11.4
70°-80°	253.7	6.5
80°-90°	67.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1152.7	29.4
0°-40°	1849.2	47.2
0°-60°	3151.4	80.4
0°-90°	3920.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3920.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1530	1528	146
15°	1467	1458	1439	1445	1437	413
25°	1328	1316	1291	1293	1291	611
35°	1145	1131	1107	1098	1090	715
45°	932	922	899	883	877	719
55°	705	696	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	71
90°	0	0	0	0	0	

TEST NUMBER: P930929

CATALOG NUMBER: DFN2DS-SQ3F0-050DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1540.8	1540.8	1540.8	1540.8	1540.8
2.5°	1549.8	1542.4	1526.1	1540.8	1538.1
5°	1540.8	1535.1	1518.7	1530.5	1527.7
7.5°	1530.5	1521.7	1505.4	1517.3	1514.3
10°	1514.3	1503.9	1486.2	1497.9	1493.6
12.5°	1492.0	1483.2	1465.4	1472.8	1469.8
15°	1466.8	1458.0	1438.7	1444.7	1437.2
17.5°	1435.7	1426.9	1407.5	1414.9	1407.5
20°	1401.6	1392.8	1372.1	1376.4	1370.6
22.5°	1367.6	1354.2	1334.9	1334.9	1331.9
25°	1327.6	1315.7	1290.6	1293.4	1290.6
27.5°	1283.0	1272.7	1253.5	1249.1	1241.7
30°	1238.7	1226.8	1204.6	1200.2	1194.3
32.5°	1191.2	1182.5	1158.7	1149.7	1143.8
35°	1145.3	1130.6	1106.8	1097.9	1090.5
37.5°	1093.4	1080.1	1056.4	1046.0	1038.6
40°	1040.2	1028.3	1004.5	991.3	985.3
42.5°	988.3	976.4	952.8	937.8	929.0
45°	932.0	921.7	899.3	883.2	877.1
47.5°	877.1	866.8	843.1	826.7	817.9
50°	819.3	812.0	791.2	770.5	763.0
52.5°	763.0	752.6	733.5	717.2	706.8
55°	705.4	696.4	678.6	660.8	653.5
57.5°	647.5	640.1	620.8	603.0	597.0
60°	589.6	583.9	563.1	546.7	542.4
62.5°	533.4	523.0	508.2	493.4	487.5
65°	475.7	466.7	451.9	438.6	431.2
67.5°	416.4	408.9	395.7	385.3	379.3
70°	361.5	355.6	342.2	331.8	326.1
72.5°	305.3	299.3	291.9	281.6	277.1
75°	248.8	246.0	238.5	229.7	232.7
77.5°	198.6	192.5	189.6	185.2	180.8
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.7	100.7	99.3	93.4	93.4
85°	60.7	59.2	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930929

CATALOG NUMBER: DFN2DS-SQ3F0-050DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.26	14.87	13.62	15.18	15.50	12.81	14.42	13.18	14.74	15.05
	3H	15.01	16.46	15.38	16.79	17.15	14.52	15.97	14.89	16.30	16.66
	4H	15.65	17.02	16.05	17.37	17.75	15.16	16.53	15.56	16.88	17.25
	6H	16.12	17.39	16.53	17.76	18.15	15.62	16.89	16.03	17.25	17.65
	8H	16.27	17.48	16.69	17.87	18.27	15.76	16.97	16.19	17.36	17.76
	12H	16.36	17.52	16.79	17.90	18.33	15.84	17.00	16.27	17.39	17.81
4H	2H	13.82	15.19	14.22	15.53	15.91	13.46	14.83	13.86	15.18	15.56
	3H	15.79	16.94	16.20	17.34	17.74	15.39	16.53	15.80	16.93	17.33
	4H	16.57	17.61	17.00	18.02	18.46	16.15	17.18	16.58	17.60	18.03
	6H	17.17	18.07	17.62	18.51	18.97	16.73	17.64	17.19	18.08	18.54
	8H	17.36	18.20	17.82	18.64	19.11	16.92	17.76	17.38	18.21	18.67
	12H	17.49	18.25	17.97	18.72	19.19	17.04	17.80	17.52	18.27	18.74
8H	4H	16.84	17.69	17.30	18.13	18.60	16.47	17.32	16.93	17.76	18.22
	6H	17.56	18.26	18.05	18.75	19.22	17.18	17.88	17.67	18.37	18.84
	8H	17.82	18.45	18.33	18.95	19.44	17.43	18.06	17.93	18.56	19.05
	12H	18.02	18.57	18.52	19.06	19.63	17.60	18.16	18.11	18.65	19.21
12H	4H	16.87	17.63	17.35	18.10	18.57	16.50	17.26	16.98	17.74	18.21
	6H	17.60	18.23	18.11	18.74	19.23	17.23	17.87	17.74	18.37	18.86
	8H	17.92	18.47	18.42	18.96	19.53	17.54	18.10	18.05	18.59	19.15