

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930966

Luminaire Tested: DFN2DS-SQ3F0-070DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-070DS927-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4712.4 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930966

CATALOG NUMBER: DFN2DS-SQ3F0-070DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930966

CATALOG NUMBER: DFN2DS-SQ3F0-070DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2625	2625	2625
5°	2635	2593	2607
10°	2615	2550	2528
15°	2585	2474	2403
20°	2544	2367	2248
25°	2501	2244	2097
30°	2442	2118	1904
35°	2384	1981	1734
40°	2326	1839	1538
45°	2258	1680	1361
50°	2188	1519	1187
55°	2117	1346	1019
60°	2034	1164	846
65°	1940	978	770
70°	1827	806	708
75°	1689	734	661
80°	1491	657	602
85°	1171	518	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2258 cd/sqm

TEST NUMBER: P930966

CATALOG NUMBER: DFN2DS-SQ3F0-070DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.7	4.6
10°-20°	589.5	12.5
20°-30°	827.7	17.6
30°-40°	902.2	19.1
40°-50°	829.2	17.6
50°-60°	651.2	13.8
60°-70°	423.9	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.9	34.6
0°-40°	2534.1	53.8
0°-60°	4014.6	85.2
0°-90°	4712.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4712.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2291	2291	2291	2291	2291	
5°	2291	2281	2254	2273	2266	217
15°	2179	2156	2086	2047	2026	614
25°	1978	1912	1775	1690	1659	910
35°	1704	1599	1416	1286	1240	1067
45°	1394	1254	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	715	547	361	290	284	709
75°	382	236	166	151	149	403
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P930966

CATALOG NUMBER: DFN2DS-SQ3F0-070DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.3	2291.3	2291.3	2291.3	2291.3
2.5°	2301.6	2291.3	2268.4	2289.4	2285.2
5°	2291.3	2281.0	2254.0	2272.6	2266.5
7.5°	2272.6	2260.3	2231.3	2239.4	2229.1
10°	2247.8	2233.3	2191.9	2185.5	2173.2
12.5°	2216.7	2198.0	2142.0	2129.6	2106.7
15°	2179.3	2156.5	2086.0	2046.7	2026.0
17.5°	2135.8	2102.6	2015.5	1969.9	1936.7
20°	2086.0	2044.5	1940.9	1889.2	1843.4
22.5°	2032.2	1984.4	1864.1	1793.6	1762.7
25°	1978.3	1911.8	1775.0	1690.0	1658.8
27.5°	1914.0	1843.4	1692.0	1594.6	1546.9
30°	1845.6	1766.6	1600.7	1495.1	1439.1
32.5°	1779.1	1683.7	1513.8	1389.3	1337.4
35°	1704.5	1598.7	1416.4	1285.7	1240.0
37.5°	1632.0	1517.8	1325.1	1181.8	1130.2
40°	1555.2	1430.9	1229.6	1082.4	1028.5
42.5°	1476.4	1343.8	1134.3	980.7	929.1
45°	1393.5	1254.4	1036.9	889.5	839.8
47.5°	1314.7	1167.6	943.6	796.2	750.7
50°	1227.6	1080.4	852.3	709.1	665.8
52.5°	1142.5	986.9	765.2	628.3	588.9
55°	1059.5	897.8	673.8	549.6	510.2
57.5°	974.6	808.7	593.1	476.9	443.8
60°	887.5	721.6	508.0	402.4	369.2
62.5°	802.5	636.7	435.4	336.0	319.4
65°	715.4	547.4	360.8	290.4	284.0
67.5°	632.5	464.4	290.4	254.9	248.8
70°	545.4	383.6	240.5	219.8	211.4
72.5°	462.4	308.9	201.1	184.6	180.4
75°	381.5	236.3	165.8	151.4	149.4
77.5°	300.7	167.8	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.5	80.9	68.4	64.2	64.2
85°	89.1	45.5	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930966

CATALOG NUMBER: DFN2DS-SQ3F0-070DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.59	16.11	14.95	16.42	16.74	10.55	12.07	10.91	12.38	12.70
	3H	16.35	17.72	16.73	18.05	18.41	11.81	13.18	12.19	13.51	13.87
	4H	17.02	18.30	17.42	18.65	19.03	12.32	13.60	12.72	13.94	14.32
	6H	17.51	18.69	17.92	19.06	19.45	12.70	13.88	13.11	14.25	14.64
	8H	17.67	18.80	18.10	19.19	19.59	12.82	13.95	13.25	14.34	14.74
	12H	17.78	18.86	18.21	19.24	19.67	12.90	13.98	13.33	14.36	14.79
4H	2H	14.69	15.97	15.09	16.32	16.70	11.24	12.52	11.64	12.87	13.25
	3H	16.63	17.69	17.04	18.09	18.49	12.69	13.75	13.10	14.15	14.55
	4H	17.37	18.33	17.81	18.75	19.19	13.29	14.24	13.72	14.66	15.10
	6H	17.97	18.80	18.42	19.24	19.70	13.78	14.61	14.23	15.05	15.51
	8H	18.18	18.96	18.64	19.40	19.87	13.94	14.71	14.40	15.16	15.63
	12H	18.33	19.03	18.82	19.51	19.98	14.05	14.75	14.54	15.23	15.70
8H	4H	17.40	18.18	17.86	18.62	19.09	13.64	14.42	14.10	14.86	15.33
	6H	18.04	18.68	18.53	19.17	19.65	14.23	14.87	14.72	15.36	15.84
	8H	18.29	18.86	18.80	19.37	19.86	14.45	15.02	14.96	15.53	16.02
	12H	18.49	19.00	19.00	19.49	20.06	14.63	15.14	15.14	15.63	16.19
12H	4H	17.38	18.08	17.87	18.56	19.03	13.68	14.38	14.17	14.86	15.33
	6H	18.02	18.59	18.53	19.10	19.59	14.29	14.87	14.80	15.38	15.87
	8H	18.30	18.81	18.81	19.30	19.87	14.56	15.07	15.07	15.57	16.13