

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331312-927

Luminaire Tested: **S122DIP-S485D925U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331312-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D925U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4630.9 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27				
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28	23				
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20				
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18				
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14				
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13				
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14	12				
10	46	34	27	23	42	32	26	21	26	22	18	22	18	16	17	14	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	1.6
10°-20°	213.1	4.6
20°-30°	309.3	6.7
30°-40°	326.4	7.0
40°-50°	289.0	6.2
50°-60°	230.6	5.0
60°-70°	156.8	3.4
70°-80°	80.4	1.7
80°-90°	21.8	0.5
90°-100°	33.4	0.7
100°-110°	122.3	2.6
110°-120°	326.9	7.1
120°-130°	539.7	11.7
130°-140°	574.0	12.4
140°-150°	533.5	11.5
150°-160°	428.9	9.3
160°-170°	276.4	6.0
170°-180°	95.1	2.1
0°-30°	595.8	12.9
0°-40°	922.2	19.9
0°-60°	1441.8	31.1
0°-90°	1700.8	36.7
90°-120°	482.6	10.4
90°-150°	2129.7	46.0
90°-180°	2930.0	63.3
0°-180°	4630.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	20	1	20	1	20	9
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	416	59	416	59	149
125°	619	588	619	588	619	535
135°	752	728	752	728	752	579
145°	857	844	857	844	857	536
155°	930	930	930	930	930	429
165°	978	980	978	980	978	276
175°	996	1002	996	1002	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	10.1	10.0	10.1	9.9	9.8	9.9	9.7	9.3	9.4	9.5	9.5
90°	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1	15.3	14.5	13.2
92.5°	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6	17.2	16.8	16.2
95°	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8	29.0	28.2	27.1
97.5°	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1	38.4	37.8	35.2
100°	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8	42.5	41.3	38.5
102.5°	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7	44.0	42.4	65.3
105°	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7	45.9	44.1	88.0
107.5°	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1	60.0	61.8	114.4
110°	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4	110.5	126.6	173.1



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1	260.7	319.3	330.8
115°	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5	371.9	446.4	442.4
117.5°	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4	476.4	494.4	491.7
120°	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2	532.3	530.3	527.4
122.5°	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8	565.6	564.5	561.3
125°	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6	612.5	611.3	608.3
127.5°	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9	655.2	653.6	651.3
130°	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4	682.5	680.8	679.1
132.5°	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1	709.6	708.0	706.2
135°	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2	747.5	745.9	744.5
137.5°	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5	782.9	781.4	779.7
140°	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4	806.0	804.5	802.8
142.5°	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5	827.3	825.9	823.9
145°	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2	857.0	855.9	853.2
147.5°	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9	883.0	882.3	879.6
150°	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8	898.8	897.9	895.3
152.5°	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3	913.3	912.4	909.9
155°	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8	932.8	931.8	929.9
157.5°	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2	949.2	948.1	946.7
160°	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8	958.9	957.9	957.0
162.5°	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8	967.7	966.6	965.7
165°	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7	978.6	977.5	977.0
167.5°	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8	987.7	986.6	986.1
170°	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5	992.3	991.2	990.9
172.5°	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9	995.8	994.7	994.3
175°	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7	999.6	998.4	998.1
177.5°	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1	1000.2	999.3	999.2
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	9.5	9.2	9.0	9.1	8.1	7.7	6.4	5.4	5.5	5.6	5.5
90°	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7	2.5	4.3	6.0
92.5°	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6	14.4	14.3	14.1
95°	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1	41.7	36.4	31.1
97.5°	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3	78.3	63.5	48.5
100°	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1	106.0	84.0	61.9
102.5°	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3	161.6	156.9	152.3
105°	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9	224.7	229.6	234.4
107.5°	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1	285.0	288.9	292.8
110°	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5	323.9	327.3	330.7



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5	360.5	363.5	366.5
115°	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0	418.7	421.4	424.2
117.5°	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3	471.3	474.4	477.4
120°	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4	508.8	511.3	513.7
122.5°	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8	541.4	543.9	546.4
125°	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2	590.3	592.4	594.5
127.5°	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9	635.3	637.5	639.8
130°	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3	663.8	666.4	669.0
132.5°	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2	692.4	694.6	696.8
135°	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9	730.4	733.0	735.5
137.5°	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9	767.7	769.5	771.3
140°	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8	792.1	793.4	794.6
142.5°	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6	812.8	814.0	815.1
145°	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3	844.1	844.0	843.8
147.5°	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8	872.2	871.6	871.0
150°	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4	890.3	889.1	888.0
152.5°	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0	905.7	904.4	903.2
155°	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7	928.3	926.8	925.3
157.5°	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5	946.3	945.1	943.8
160°	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	957.0	956.0	955.0
162.5°	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2	966.2	965.3	964.2
165°	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6	978.7	977.7	976.7
167.5°	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9	987.9	987.0	986.0
170°	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1	993.1	992.1	991.2
172.5°	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5	996.6	995.6	994.7
175°	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0	1000.9	999.8	998.6
177.5°	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7	1001.9	1001.0	1000.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	5.5	5.6	5.7	5.9	5.9	5.9	5.9	6.0	6.2	5.9	6.0
90°	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6	18.1	18.5	18.8
95°	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8	30.7	31.4	31.8
97.5°	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1	39.7	40.3	40.7
100°	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8	45.1	46.4	47.2
102.5°	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7	47.5	49.1	50.1
105°	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7	49.4	51.2	52.4
107.5°	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1	56.4	54.6	54.0
110°	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4	78.3	62.3	54.6



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1	143.4	84.8	55.7
115°	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5	223.1	148.6	105.6
117.5°	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4	440.5	422.4	394.3
120°	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2	536.1	538.1	528.1
122.5°	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8	567.9	569.1	567.6
125°	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6	614.7	615.8	616.6
127.5°	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9	658.5	660.2	661.0
130°	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4	686.1	687.9	688.7
132.5°	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1	712.6	714.1	714.7
135°	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2	750.8	752.3	753.0
137.5°	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5	786.1	787.7	788.2
140°	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4	808.9	810.3	810.6
142.5°	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5	829.9	831.2	831.5
145°	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2	859.3	860.4	860.5
147.5°	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9	884.7	885.6	885.7
150°	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8	900.8	901.7	901.8
152.5°	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3	915.2	916.2	916.2
155°	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8	934.8	935.7	935.6
157.5°	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2	951.3	952.4	952.4
160°	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8	960.8	961.8	961.7
162.5°	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8	969.9	971.0	970.8
165°	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7	980.8	981.9	981.9
167.5°	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8	989.9	991.1	990.9
170°	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5	994.6	995.7	995.5
172.5°	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9	998.1	999.2	999.0
175°	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7	1001.8	1002.9	1002.7
177.5°	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1	1002.0	1002.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	6.1	5.9	5.9	5.8	5.9	5.9	6.1	6.0	5.9	6.2	6.0
90°	18.5	18.9	19.3	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1
92.5°	18.9	19.2	19.3	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6
95°	31.6	31.4	31.3	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8
97.5°	41.0	41.1	41.4	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1
100°	47.5	47.8	48.2	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8
102.5°	50.6	51.0	51.5	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7
105°	53.1	53.7	54.3	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7
107.5°	54.7	55.3	55.9	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1
110°	55.2	55.8	56.5	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.2	56.7	57.2	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1
115°	94.0	82.5	70.9	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5
117.5°	356.3	318.3	280.3	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4
120°	506.4	484.7	463.0	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2
122.5°	563.4	559.1	554.9	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8
125°	617.1	617.6	618.1	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6
127.5°	661.2	661.2	661.3	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9
130°	688.6	688.3	688.2	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4
132.5°	714.5	714.4	714.2	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1
135°	752.7	752.3	752.0	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2
137.5°	787.7	787.1	786.6	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5
140°	809.8	809.1	808.3	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4
142.5°	830.7	829.9	829.1	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5
145°	859.8	859.0	858.2	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2
147.5°	884.9	884.3	883.6	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9
150°	901.0	900.2	899.4	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8
152.5°	915.0	914.0	913.0	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3
155°	934.3	933.0	931.7	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8
157.5°	951.1	949.8	948.6	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2
160°	960.5	959.4	958.3	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8
162.5°	969.5	968.0	966.7	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8
165°	980.8	979.7	978.6	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7
167.5°	989.4	988.0	986.6	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8
170°	994.1	992.6	991.2	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5
172.5°	997.5	996.1	994.7	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9
175°	1001.1	999.5	997.8	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7
177.5°	1001.6	1000.4	999.3	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	5.9	5.9	5.9	5.9	5.7	5.6	5.5	5.5	5.6	5.5	5.4
90°	15.3	14.5	13.2	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6
95°	29.0	28.2	27.1	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1
97.5°	38.4	37.8	35.2	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3
100°	42.5	41.3	38.5	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1
102.5°	44.0	42.4	65.3	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3
105°	45.9	44.1	88.0	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9
107.5°	60.0	61.8	114.4	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1
110°	110.5	126.6	173.1	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.7	319.3	330.8	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5
115°	371.9	446.4	442.4	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0
117.5°	476.4	494.4	491.7	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3
120°	532.3	530.3	527.4	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4
122.5°	565.6	564.5	561.3	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8
125°	612.5	611.3	608.3	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2
127.5°	655.2	653.6	651.3	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9
130°	682.5	680.8	679.1	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3
132.5°	709.6	708.0	706.2	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2
135°	747.5	745.9	744.5	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9
137.5°	782.9	781.4	779.7	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9
140°	806.0	804.5	802.8	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8
142.5°	827.3	825.9	823.9	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6
145°	857.0	855.9	853.2	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3
147.5°	883.0	882.3	879.6	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8
150°	898.8	897.9	895.3	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4
152.5°	913.3	912.4	909.9	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0
155°	932.8	931.8	929.9	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7
157.5°	949.2	948.1	946.7	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5
160°	958.9	957.9	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9
162.5°	967.7	966.6	965.7	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2
165°	978.6	977.5	977.0	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6
167.5°	987.7	986.6	986.1	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9
170°	992.3	991.2	990.9	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1
172.5°	995.8	994.7	994.3	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5
175°	999.6	998.4	998.1	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0
177.5°	1000.2	999.3	999.2	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.4	7.7	8.1	9.1	9.0	9.2	9.5	9.5	9.5	9.4	9.3
90°	2.5	4.3	6.0	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1
92.5°	14.4	14.3	14.1	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.5	48.5	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1
100°	106.0	84.0	61.9	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8
102.5°	161.6	156.9	152.3	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7
105°	224.7	229.6	234.4	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7
107.5°	285.0	288.9	292.8	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1
110°	323.9	327.3	330.7	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.5	363.5	366.5	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1
115°	418.7	421.4	424.2	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5
117.5°	471.3	474.4	477.4	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4
120°	508.8	511.3	513.7	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2
122.5°	541.4	543.9	546.4	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8
125°	590.3	592.4	594.5	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6
127.5°	635.3	637.5	639.8	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9
130°	663.8	666.4	669.0	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4
132.5°	692.4	694.6	696.8	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1
135°	730.4	733.0	735.5	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2
137.5°	767.7	769.5	771.3	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5
140°	792.1	793.4	794.6	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4
142.5°	812.8	814.0	815.1	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5
145°	844.1	844.0	843.8	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2
147.5°	872.2	871.6	871.0	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9
150°	890.3	889.1	888.0	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8
152.5°	905.7	904.4	903.2	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3
155°	928.3	926.8	925.3	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8
157.5°	946.3	945.1	943.8	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2
160°	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8
162.5°	966.2	965.3	964.2	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8
165°	978.7	977.7	976.7	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7
167.5°	987.9	987.0	986.0	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8
170°	993.1	992.1	991.2	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5
172.5°	996.6	995.6	994.7	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9
175°	1000.9	999.8	998.6	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7
177.5°	1001.9	1001.0	1000.1	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	9.7	9.9	9.8	9.9	10.1	10.0	10.1
90°	16.9	17.7	18.2	18.5	18.9	19.3	19.6
92.5°	18.1	18.5	18.8	18.9	19.2	19.3	19.6
95°	30.7	31.4	31.8	31.6	31.4	31.3	31.1
97.5°	39.7	40.3	40.7	41.0	41.1	41.4	41.5
100°	45.1	46.4	47.2	47.5	47.8	48.2	48.5
102.5°	47.5	49.1	50.1	50.6	51.0	51.5	52.0
105°	49.4	51.2	52.4	53.1	53.7	54.3	55.0
107.5°	56.4	54.6	54.0	54.7	55.3	55.9	56.6
110°	78.3	62.3	54.6	55.2	55.8	56.5	57.2



TEST NUMBER: P331312-927

CATALOG NUMBER: S122DIP-S485D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.4	84.8	55.7	56.2	56.7	57.2	57.8
115°	223.1	148.6	105.6	94.0	82.5	70.9	59.3
117.5°	440.5	422.4	394.3	356.3	318.3	280.3	242.2
120°	536.1	538.1	528.1	506.4	484.7	463.0	441.3
122.5°	567.9	569.1	567.6	563.4	559.1	554.9	550.7
125°	614.7	615.8	616.6	617.1	617.6	618.1	618.6
127.5°	658.5	660.2	661.0	661.2	661.2	661.3	661.4
130°	686.1	687.9	688.7	688.6	688.3	688.2	688.0
132.5°	712.6	714.1	714.7	714.5	714.4	714.2	714.1
135°	750.8	752.3	753.0	752.7	752.3	752.0	751.7
137.5°	786.1	787.7	788.2	787.7	787.1	786.6	786.0
140°	808.9	810.3	810.6	809.8	809.1	808.3	807.4
142.5°	829.9	831.2	831.5	830.7	829.9	829.1	828.2
145°	859.3	860.4	860.5	859.8	859.0	858.2	857.4
147.5°	884.7	885.6	885.7	884.9	884.3	883.6	883.0
150°	900.8	901.7	901.8	901.0	900.2	899.4	898.6
152.5°	915.2	916.2	916.2	915.0	914.0	913.0	911.9
155°	934.8	935.7	935.6	934.3	933.0	931.7	930.4
157.5°	951.3	952.4	952.4	951.1	949.8	948.6	947.4
160°	960.8	961.8	961.7	960.5	959.4	958.3	957.2
162.5°	969.9	971.0	970.8	969.5	968.0	966.7	965.3
165°	980.8	981.9	981.9	980.8	979.7	978.6	977.5
167.5°	989.9	991.1	990.9	989.4	988.0	986.6	985.1
170°	994.6	995.7	995.5	994.1	992.6	991.2	989.8
172.5°	998.1	999.2	999.0	997.5	996.1	994.7	993.2
175°	1001.8	1002.9	1002.7	1001.1	999.5	997.8	996.2
177.5°	1002.0	1002.9	1002.7	1001.6	1000.4	999.3	998.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9

(END OF REPORT)